



Radial gripper HGRT-16-A-G2

Part number: 563905

FESTO



Data sheet

Feature	Value
Size	16
Max. interchangeability	≤0.2 mm
Max. gripper jaw angular play ax, ay	≤0.1 deg
Max. opening angle	180 deg
Rotational symmetry	≤0.2 mm
Pneumatic gripper repetition accuracy	≤0.02 mm
Type code	HGRT
Number of gripper jaws	2
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Radial
Structural design	Positively driven motion sequence
Position sensing	For proximity sensor For inductive proximity sensors
Symbol	00991895
Operating pressure	4 bar ... 8 bar
Max. operating frequency of pneumatic gripper	≤3 Hz
Min. opening time at 6 bar	233 ms
Min. closing time at 6 bar	185 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	5 °C ... 60 °C
Mass moment of inertia	0.21 kgcm ²
Maximum force on gripper jaw Fz, static	50 N
Maximum torque on gripper jaw, My static	3.9 Nm
Maximum torque on gripper jaw, Mz static	0.3 Nm
Relubrication interval for guidance elements	10 MioCyc
Product weight	150 g
Type of mounting	With internal thread and centering sleeve
Pneumatic connection	M3
Note on materials	Free of copper and PTFE RoHS-compliant
Housing material	Aluminum Smooth anodized
Gripper jaw material	Steel Hardened