



Air solenoid valve MHJ10-S-2,5-QS-6-HF

Part number: 567503

FESTO



Data sheet

Feature	Value
Valve function	2/2, closed, monostable
Actuation type	Electrical
Width	10 mm
Standard nominal flow rate	160 l/min
Pneumatic working port	QS-6
Operating voltage	24V DC
Operating pressure	0.05 MPa ... 0.6 MPa
Operating pressure	0.5 bar ... 6 bar
Structural design	Poppet valve without return spring
Reset method	Pneumatic spring
Degree of protection	IP65
Certification	RCM compliance mark
KC characters	KC EMC
CE marking (see declaration of conformity)	As per EU EMC directive
Width dimension	10.5 mm
Type code	MHJ10
Operating conditions to DIN VDE 0580	S3 50% 20min. for single pneumatic valve S3 25% 20 min for block assembly
Information on operation	Power supply unit must be able to supply at least 1.7 A without voltage drop. Do not operate without flow.
Sealing principle	Hard
Mounting position	Any
Manual override	None
Type of control	Direct
Flow direction	Non-reversible
Symbol	00992259
Reverse polarity protection	for operating voltage
Additional functions	Spark suppression Holding current reduction with energy recovery Safety shut-down
b-value	0.36
C value	0.66 l/sbar
Max. switching frequency	500 Hz
Switching time on at 4 bar and 24 V in new condition	1.2 ms
Switching time off at 4 bar and 24 V in new condition	0.6 ms
Switching time on at 0.5 bar and 24 V in new condition	1 ms

Feature	Value
Switching time off at 0.5 bar and 24 V in new condition	0.8 ms
Switching time on at 6 bar and 24 V in new condition	1.3 ms
Switching time off at 6 bar and 24 V in new condition	0.6 ms
Tolerance for switching time off	+15 %/-25 %
Tolerance for ON switching time	+/-15 %
DC operating voltage range	21.6 V ... 26.4 V
Input resistance	34 kOhm
Coil characteristics	24 V DC: low-current phase 3.2 W, high-current phase 14.5 W
Trigger signal range DC	3 V ... 30 V
Note on input current	Linear increase 0.09-0.44 mA for a trigger signal of 3-15 V 0.44-15.44 mA for a trigger signal of 15-30 V
Permissible voltage fluctuations	+/- 10 %
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Restricted ambient and media temperature	Depending on the switching frequency (see diagram)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Storage temperature	-20 °C ... 50 °C
Permissible solenoid surface temperature	120 °C
Temperature of medium	-5 °C ... 60 °C
Ambient temperature	-5 °C ... 60 °C
Product weight	85 g
Electrical connection	3-wire Cable
Cable length	2.5 m
Type of mounting	Optionally: Line installation With through-hole
Pneumatic connection 1	QS-6
Pneumatic connection 2	QS-6
Note on materials	RoHS-compliant
Seals material	HNBR
Housing material	PA-reinforced PPS-reinforced
Material of cable sheath	PUR
Material of screws	Steel