



Air solenoid valve VMPA1-M1H-MS-PI

FESTO

Part number: 571334



Data sheet

| Feature | Value |
|--|--|
| Valve function | 5/2, monostable |
| Actuation type | Electrical |
| Valve size | 10 mm |
| Standard nominal flow rate | 360 l/min |
| Operating voltage | 24V DC |
| Operating pressure | -0.09 MPa ... 0.8 MPa |
| Operating pressure | -0.9 bar ... 8 bar |
| Structural design | Piston gate valve |
| Reset method | Mechanical spring |
| Certification | c UL us - Recognized (OL) |
| CE marking (see declaration of conformity) | As per EU EMC directive |
| Degree of protection | IP65 In mounted state as per IEC 60529 |
| Type code | VMPA1 |
| Sealing principle | Soft |
| Mounting position | Any |
| Manual override | Detenting Non-detenting |
| Type of control | Pilot-controlled |
| Flow direction | Reversible |
| Symbol | 00991190 |
| Lap | Overlap |
| Signal status display | yes |
| Pilot pressure MPa | 0.3 MPa ... 0.8 MPa |
| Pilot pressure | 3 bar ... 8 bar |
| Suitability for vacuum | yes |
| Standard nominal flow rate with QS-6 | 360 l/min |
| Max. switching frequency | 2 Hz |
| Switching time off | 27 ms |
| On switching time | 10 ms |
| Max. positive test pulse with 0 signal | 400 µs |
| Max. negative test pulse on 1 signal | 200 µs |
| Permissible voltage fluctuations | +/- 25 % |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |

| Feature | Value |
|---|--|
| Vibration resistance | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Storage temperature | -20 °C ... 40 °C |
| Temperature of medium | -5 °C ... 50 °C |
| Relative air humidity | Max. 90 % at 40 °C |
| Ambient temperature | -5 °C ... 50 °C |
| Max. tightening torque for valve mounting | 0.25 Nm |
| Product weight | 56 g |
| Type of mounting | With through-hole |
| Note on materials | RoHS-compliant |
| Seals material | NBR |
| Housing material | Die-cast aluminum |