


# Air solenoid valve VUVG-B10-T32U-MZT-F-1T1L

**FESTO**

Part number: 573414



## Data sheet

| Feature                                | Value                                         |
|----------------------------------------|-----------------------------------------------|
| Valve function                         | 2x3/2, open, monostable                       |
| Actuation type                         | Electrical                                    |
| Valve size                             | 10 mm                                         |
| Standard nominal flow rate             | 130 l/min                                     |
| Pneumatic working port                 | Flange                                        |
| Operating voltage                      | 24V DC                                        |
| Operating pressure                     | -0.09 MPa ... 1 MPa                           |
| Operating pressure                     | -0.9 bar ... 10 bar                           |
| Structural design                      | Piston gate valve                             |
| Reset method                           | Mechanical spring                             |
| Certification                          | c UL us - Recognized (OL)                     |
| Degree of protection                   | IP65<br>IP67                                  |
| Type code                              | VUVG                                          |
| Exhaust air function                   | With flow control option                      |
| Sealing principle                      | Soft                                          |
| Mounting position                      | Any                                           |
| Manual override                        | Detenting<br>Non-detenting                    |
| Type of control                        | Pilot-controlled                              |
| Pilot air supply port                  | External                                      |
| Flow direction                         | Reversible                                    |
| Symbol                                 | 00992946                                      |
| Lap                                    | Overlap                                       |
| Signal status display                  | LED                                           |
| Pilot pressure MPa                     | 0.2 MPa ... 0.8 MPa                           |
| Pilot pressure                         | 2 bar ... 8 bar                               |
| Max. switching frequency               | 3 Hz                                          |
| Switching time off                     | 20 ms                                         |
| On switching time                      | 10 ms                                         |
| Duty cycle                             | 100%                                          |
| Max. positive test pulse with 0 signal | 1600 µs                                       |
| Max. negative test pulse on 1 signal   | 3000 µs                                       |
| Coil characteristics                   | 22 V DC: 1.0 W                                |
| Permissible voltage fluctuations       | +/- 10 %                                      |
| Operating medium                       | Compressed air as per ISO 8573-1:2010 [7:4:4] |

| Feature                                  | Value                                                                                |
|------------------------------------------|--------------------------------------------------------------------------------------|
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use)                   |
| Vibration resistance                     | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Shock resistance                         | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27                |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                                        |
| Temperature of medium                    | -5 °C ... 60 °C                                                                      |
| Pilot medium                             | Compressed air as per ISO 8573-1:2010 [7:4:4]                                        |
| Ambient temperature                      | -5 °C ... 60 °C                                                                      |
| Product weight                           | 59 g                                                                                 |
| Electrical connection                    | Via sub-base                                                                         |
| Type of mounting                         | On terminal strip                                                                    |
| Note on materials                        | RoHS-compliant                                                                       |
| Seals material                           | HNBR<br>NBR                                                                          |
| Housing material                         | Wrought aluminum alloy                                                               |