



Motor cable NEBM-M12G4-RS-15-N-LE4

Part number: 571907

FESTO



Data sheet

Feature	Value
Type code	NEBM
Conforms to standard	DIN 47100 EN 61984
Cable designation	Without label holder
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw-type lock with AF 14
Electrical connection for input 1, connection pattern	00995385
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
DC operating voltage range	0 V ... 250 V
Operating voltage range AC	0 V ... 250 V
Current rating at 40°C	4 A
Cable length	15 m
Cable characteristic	Suitable for robot applications
Bending radius, flexible cable installation	≥60 mm
Cable diameter	5.9 mm
Cable design	4 x 0.34 mm ² Shielded
Nominal conductor cross section	0.34 mm ²
Wire ends	Cable end sleeve
Degree of protection	IP67
Note on degree of protection	In mounted state
Ambient temperature	-25 °C ... 80 °C
Ambient temperature with flexible cable installation	0 °C ... 40 °C
Note on materials	RoHS-compliant

Feature	Value
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Black
Housing material	TPE-U(PUR)
Seals material	NBR
Insulating sheath material	TPE-E