



Encoder cable NEBM-M12G12-RS-15-N-S1G15

Part number: 571915

FESTO



Data sheet

Feature	Value
Type code	NEBM
Conforms to standard	DIN 47100 EN 61984
Cable designation	Without label holder
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical connection 1, number of pins/wires	12
Electrical connection 1, occupied pins/wires	11
Electrical connection 1, type of mounting	Screw-type lock with AF 14
Electrical connection for input 1, connection pattern	00995668
Electrical connection 2, function	Control side
Electrical connection 2, design	Rectangular
Electrical connection 2, connection type	Plug
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connection technology	Sub-D
Electrical connection 2, number of pins/wires	15
Electrical connection 2, occupied pins/wires	11
Electrical connection 2, type of mounting	Screw-type lock with hexagon, AF 18
Electrical connection 2, connection pattern	00995641
DC operating voltage range	0 V ... 30 V
Nominal operating voltage DC	24 V
Operating voltage range AC	0 V ... 30 V
Nominal operating voltage AC	24 V
Current rating at 40°C	1 A
Cable length	15 m
Cable characteristic	Suitable for robot applications
Bending radius, flexible cable installation	≥70 mm
Cable diameter	7 mm
Cable design	12 x 0.14 mm ² Shielded
Nominal conductor cross section	0.14 mm ²

Feature	Value
Degree of protection	IP67
Note on degree of protection	IP50 for Sub-D plug In mounted state
Ambient temperature	-25 °C ... 80 °C
Ambient temperature with flexible cable installation	0 °C ... 40 °C
Note on materials	RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Black
Housing material	TPE-U(PUR)
Material of union nut	Die-cast zinc, nickel-plated
Seals material	NBR
Insulating sheath material	TPE-E