


Compact air cylinder ADN-100-20-A-PPS-A

Part number: 577201

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 20 mm |
| Piston diameter | 100 mm |
| Piston rod thread | M16x1.5 |
| Type code | ADN |
| Cushioning | Self-adjusting pneumatic end-position cushioning |
| Mounting position | Any |
| Conforms to standard | ISO 21287 |
| Piston rod end | External thread |
| Position sensing | For proximity sensor |
| Symbol | 00991217 |
| Variants | Piston rod at one end |
| Operating pressure | 0.1 MPa ... 1 MPa |
| Operating pressure | 1 bar ... 10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in the end positions | 2.5 J |
| Cushioning length | 10 mm |
| Theoretical force at 6 bar, retracting | 4524 N |
| Theoretical force at 6 bar, advancing | 4712 N |
| Moving mass at 0 mm stroke | 570 g |
| Additional weight per 10 mm stroke | 98 g |
| Basic weight with 0 mm stroke | 2154 g |
| Additional moving mass per 10 mm stroke | 25 g |
| Type of mounting | Optionally: With through-hole With internal thread With accessories |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Cover material | Die-cast aluminum, coated |
| Seals material | TPE-U(PUR) |
| Piston rod material | High-alloy steel |

| Feature | Value |
|-----------------------------|---|
| Material of cylinder barrel | Wrought aluminum alloy Smooth anodized |