

Input module CTMM-S1-D-8E-M8-3

Part number: 8047505

FESTO



Data sheet

Feature	Value
Dimensions W x L x H	27 mm x 123 mm x 40 mm
Width dimension	28 mm
Type code	CTMM
No. of outputs	0
No. of inputs	8
Diagnostics via LED	Faults per module Status per channel
Input debounce time	0.1 ms
Fuse protection (short circuit)	Internal electronic fuse
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 12 mA
Nominal operating voltage DC for electronics/sensors	24 V
Nominal operating voltage DC	24 V
Electrical isolation between channel and internal bus	no
Electrical isolation between channels	no
Switching level	Signal 0: ≤ 5 V Signal 1: ≥ 11 V
Permissible voltage fluctuations for electronics/sensors	± 25 %
CE marking (see declaration of conformity)	As per EU EMC directive
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Storage temperature	-20 °C ... 40 °C
Temperature of medium	-5 °C ... 50 °C
Degree of protection	IP65 IP67
Ambient temperature	-5 °C ... 50 °C
Product weight	75 g
Input characteristics	As per IEC 61131-2, type 3
Max. cable length	30 m
Input switching logic	PNP (positive switching)
Electrical connection input, function	Digital input
Electrical connection input, connection type	8x socket
Electrical input connection, connection technology	M8x1, A-coded as per EN 61076-2-104
Electrical connection, input, number of pins/wires	3
Note on materials	RoHS-compliant

Feature	Value
Housing material	PA-reinforced