



# Air solenoid valve

## VSCS-B-M32-MH-WA-1C1-8

FESTO

Part number: 8040564



### Data sheet

Feature	Value
Valve function	3/2, closed, monostable
Actuation type	Electrical
Width	15 mm
Standard nominal flow rate	13.5 l/min
Pneumatic working port	Sub-base, size 15 mm as per ISO 15218
Operating voltage	24V DC
Operating pressure	0.15 MPa ... 0.8 MPa
Operating pressure	1.5 bar ... 8 bar
Reset method	Mechanical spring
Degree of protection	IP65
Type code	VSCS
Sealing principle	Soft
Mounting position	Any
Conforms to standard	ISO 15218
Manual override	Non-detenting
Type of control	Direct
Flow direction	Non-reversible
Symbol	00991308
Lap	Underlap
Note on forced dynamization	Switching frequency at least once a week
Switching time off	6 ms
On switching time	8 ms
Duty cycle	100%
Coil characteristics	24 V DC: 1.3 W
Permissible voltage fluctuations	+/- 10 %
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Vibration resistance	Transport application test with severity level 1 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 1 as per FN 942017-5 and EN 60068-2-27
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	-5 °C ... 50 °C
Ambient temperature	-5 °C ... 50 °C
Electrical connection	Form C as per DIN EN 175301-803
Pneumatic connection 1	Sub-base

<b>Feature</b>	<b>Value</b>
Pneumatic connection 2	Sub-base
Pneumatic connection 3	Sub-base
Note on materials	RoHS-compliant
Seals material	NBR