


Ball screw linear actuator ELGC-BS-KF-60-800-12P

Part number: 8061497

FESTO



Data sheet

Feature	Value
Working stroke	800 mm
Size	60
Stroke reserve	0 mm
Screw diameter	12 mm
Spindle pitch	12 mm/U
Type code	ELGC
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Electromechanical linear axis with ball screw
Motor type	Stepper motor Servo motor
Spindle type	Ball screw drive
Symbol	00991211
Max. acceleration	15 m/s ²
Max. rotational speed	4000 1/min
Max. speed	0.8 m/s
Repetition accuracy	±0.01 mm
Degree of protection	IP40
Ambient temperature	0 °C ... 50 °C
2nd moment of area I _y	441000 mm ⁴
2nd moment of area I _z	542000 mm ⁴
No-load torque at maximum travel speed	0.246 Nm
No-load torque at minimum travel speed	0.042 Nm
Max. force F _y	600 N
Max. force F _z	1800 N
F _y with theoretical service life of 100 km (from a guide perspective only)	2208 N
F _z with theoretical service life of 100 km (from a guide perspective only)	6624 N
Max. torque M _x	29.1 Nm
Max. torque M _y	31.8 Nm
Max. torque M _z	31.8 Nm
M _x with theoretical service life of 100 km (from a guide perspective only)	107 Nm
M _y with theoretical service life of 100 km (from a guide perspective only)	117 Nm
M _z with theoretical service life of 100 km (from a guide perspective only)	117 Nm
Max. feed force F _x	200 N

Feature	Value
Torsion moment of inertia It	29800 mm ⁴
Mass moment of inertia JH per meter of stroke	0.10779 kgcm ²
Mass moment of inertia JL per kg of payload	0.036476 kgcm ²
Mass moment of inertia JO	0.02235 kgcm ²
Feed constant	12 mm/U
Moving mass	525 g
Additional weight per 10 mm stroke	51 g
Dynamic deflection (load moved)	0.05% of axis length, maximum 0.5 mm
Static deflection (load at standstill)	0.1 % of axis length
Interface code, actuator	T42
Material of end caps	Die cast aluminum, painted
Profile material	Wrought aluminum alloy, anodized
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Cover strip material	High-alloy stainless steel
Drive cover material	Die cast aluminum, painted
Slide carriage material	Steel
Guide rail material	Steel
Slide material	Die-cast aluminum
Spindle nut material	Steel
Spindle material	Steel