

Axial kit EAMM-A-L62-72GA

FESTO

Part number: 8063503



Data sheet

| Feature | Value |
|--------------------------|------------------|
| Type code | EAMM-A |
| Mounting position | Any |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C ... 60 °C |
| Transferable torque | 48 Nm |
| Product weight | 1487 g |
| Interface code, actuator | L62 |
| Interface code, motor in | 72GA |
| Note on materials | RoHS-compliant |