

Axial kit EAMM-A-L95-68GA

Part number: 8063524

FESTO



Data sheet

Feature	Value
Type code	EAMM-A
Mounting position	Any
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Transferable torque	93 Nm
Product weight	2809 g
Interface code, actuator	L95
Interface code, motor in	68GA
Note on materials	RoHS-compliant