


Parallel gripper EHPS-16-A

Part number: 8070832

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | 16 |
| Stroke per gripper jaw | 10 mm |
| Max. interchangeability | ≤0.2 mm |
| Max. gripper jaw angular play ax, ay | 0.4 deg |
| Max. gripper jaw backlash Sz | 0.05 mm |
| Rotational symmetry | ≤0.2 mm |
| Pneumatic gripper repetition accuracy | ≤0.03 mm |
| Type code | EHPS |
| Number of gripper jaws | 2 |
| Mounting position | Any |
| Gripper function | Parallel |
| Structural design | Worm gear T-shape Gear rack/pinion Electric gripper |
| Conforms to standard | IEC 61010-1 |
| Guide | Sliding guide |
| Position sensing | For proximity sensor |
| Symbol | 00992258 |
| Motor type | DC servo motor |
| Control elements | Latching switch |
| Ready status indication | LED |
| Max. cycle rate | 1.1 Hz |
| Max. current consumption | 1000 mA |
| Nominal operating voltage DC | 24 V |
| Permissible voltage fluctuations | +/- 10 % |
| Certification | RCM compliance mark |
| KC characters | KC EMC |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU RoHS directive |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Noise level | ≤70 dB(A) |
| Degree of protection | IP40 |
| Ambient temperature | 5 °C ... 60 °C |
| Mass moment of inertia | 0.78 kgcm ² |
| Maximum force on gripper jaw Fz, static | 200 N |
| Maximum torque on gripper jaw, Mx static | 7 Nm |

| Feature | Value |
|--|---|
| Maximum torque on gripper jaw, My static | 4.4 Nm |
| Maximum torque on gripper jaw, Mz static | 7 Nm |
| Relubrication interval for guidance elements | 2 MioCyc |
| Max. mass per external gripper finger | 100 g |
| Product weight | 296 g |
| Electrical connection | 5-pin Cable with plug M12x1 |
| Type of mounting | Optionally: With internal thread and centering sleeve Via through-hole and centering sleeve |
| Note on materials | RoHS-compliant |
| Housing material | Aluminum, anodized |
| Gripper jaw material | High-alloy stainless steel |