


# Connecting cable NEBC-M12G5-ES-5-LE5-CO

Part number: 8074191

FESTO



## Data sheet

Feature	Value
Type code	NEBC
Protocol	CANopen DeviceNet
Cable designation	With 2x label holders
Contact durability	100
Product weight	310.7 g
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection for input 1, connection pattern	00995384
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	5
Electrical connection 2, occupied pins/wires	5
DC operating voltage range	0 V ... 30 V
Current rating at 40°C	4 A
Surge resistance	2 kV
Cable length	5 m
Cable characteristic	Suitable for energy chains
Connector cable test conditions	Test conditions on request
Bending radius, fixed cable installation	≥35 mm
Bending radius, flexible cable installation	≥70 mm
Cable diameter	6.7 mm
Cable diameter tolerance	± 0.3 mm
Cable design	(2 x 0.34 mm <sup>2</sup> ) + (2 x 0.25 mm <sup>2</sup> ) + 0.34 mm <sup>2</sup> Shielded
Nominal conductor cross section	0.34 mm <sup>2</sup> 0.25 mm <sup>2</sup>

<b>Feature</b>	<b>Value</b>
Wire ends	Stripped
Degree of protection	IP65 IP67
Note on degree of protection	In mounted state
Ambient temperature	-25 °C ... 80 °C
Ambient temperature with flexible cable installation	-20 °C ... 80 °C
Note on materials	RoHS-compliant
Contamination level	3
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Red-purple
Housing material	TPE-U(PUR), reinforced
Housing colour	Black
Material of screw-type lock	Die-cast zinc, nickel-plated
Seals material	NBR
Material of pin contacts	Brass, nickel-plated and gold-plated
Insulating sheath material	PE