


Light barrier SOOD-TB-L-PN

Part number: 8075661

FESTO



Data sheet

Feature	Value
Type code	SOOD
Design	Block design
Conforms to standard	EN 60947-5-2
Symbol	00995974
Certification	RCM compliance mark c UL us - Recognized (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
Certificate issuing authority	UL E232949
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Measuring principle	Optoelectronic
Detection method	Through-beam sensor Transmitter Receiver
Type of light	Laser Red
Max. light spot	20 mm at 10000 mm
Working range	0 mm ... 10000 mm
Ambient temperature	-20 °C ... 60 °C
Switching output	Push-pull
Switching element function	PNP, dark-switching NPN, bright-switching
Max. switching frequency	2000 Hz
Max. output current	50 mA
Voltage drop	0 V ... 1.5 V
Short-circuit protection	Pulsed
DC operating voltage range	10 V ... 30 V
Residual ripple	10%
Idle current	11 mA
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Cable with plug
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	3
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection for input 1, connection pattern	00991155

Feature	Value
Material of pin contacts	Brass, gold-plated
Cable length	0.15 m
Cable characteristic	Standard
Material of cable sheath	TPE-U(PUR)
Type of mounting	With through-hole
Tightening torque	0.5 Nm
Mounting position	Any
Product weight	20 g
Housing material	ABS PC TPE-U(PU)
Ready status indication	LED green
Switching status indication	LED yellow
Function reserve indication	LED yellow, flashing
Degree of protection	IP65 IP67
Insulation voltage	500 V
Surge resistance	1 kV
Corrosion resistance class (CRC)	1 - Low corrosion stress
Laser safety class	1
Contamination level	3