


Mini slide DGST-6-40-E1A

Part number: 8078831

FESTO



Data sheet

Feature	Value
Stroke	40 mm
Piston diameter	6 mm
Type code	DGST
Drive unit operating mode	Yoke
Cushioning	Elastomer cushioning, at both ends, stroke not adjustable
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Twin piston Yoke Piston rod Slide
Position sensing	For proximity sensor
Symbol	00991249
Operating pressure	0.15 MPa ... 0.8 MPa
Operating pressure	1.5 bar ... 8 bar
Operating pressure	21.75 psi ... 116 psi
Max. speed	0.5 m/s
Repetition accuracy	≤ 0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Impact energy in the end positions	0.012 J
Cushioning length	0.9 mm
Max. force Fy	260 N
Max. force Fz	260 N
Max. torque Mx	1.2 Nm
Max. torque My	1.2 Nm
Max. torque Mz	1.2 Nm
Theoretical force at 6 bar, retracting	25 N
Theoretical force at 6 bar, advancing	34 N
Moving mass	73 g
Product weight	140 g
Type of mounting	With through-hole
Pneumatic connection	M3

Feature	Value
Note on materials	Free of copper and PTFE RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	HNBR
Guide material	POM TPE-E High-alloy steel
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel