


Mini slide DGST-20-30-E1A

Part number: 8078864

FESTO



Data sheet

Feature	Value
Stroke	30 mm
Piston diameter	20 mm
Type code	DGST
Drive unit operating mode	Yoke
Cushioning	Elastomer cushioning, at both ends, stroke not adjustable
Mounting position	Any
Guide	Ball bearing cage guide
Structural design	Twin piston Yoke Piston rod Slide
Position sensing	For proximity sensor
Symbol	00991249
Operating pressure	0.1 MPa ... 0.8 MPa
Operating pressure	1 bar ... 8 bar
Operating pressure	14.5 psi ... 116 psi
Max. speed	0.5 m/s
Repetition accuracy	≤ 0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Impact energy in the end positions	0.2 J
Cushioning length	1 mm
Max. force F _y	1110 N
Max. force F _z	1110 N
Max. torque M _x	11 Nm
Max. torque M _y	12 Nm
Max. torque M _z	12 Nm
Theoretical force at 6 bar, retracting	317 N
Theoretical force at 6 bar, advancing	377 N
Moving mass	455 g
Product weight	994 g
Type of mounting	With through-hole
Pneumatic connection	G1/8

Feature	Value
Note on materials	Free of copper and PTFE RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	HNBR
Guide material	POM TPE-E High-alloy steel
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel