



Cantilever linear actuator ELCC-TB-KF-60-1000-0H-P0-CR

Part number: 8082391

FESTO



Data sheet

Feature	Value
Drive pinion effective diameter	30.558 mm
Working stroke	1000 mm
Size	60
Stroke reserve	0 mm
Toothed belt pitch	3 mm
Type code	ELCC
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Electromechanical cantilever axis
Symbol	00991210
Max. acceleration	50 m/s ²
Max. speed	5 m/s
Repetition accuracy	±0.05 mm
Corrosion resistance class (CRC)	0 - No corrosion stress
Degree of protection	IP20
Ambient temperature	-10 °C ... 60 °C
2nd moment of area I _y	240600 mm ⁴
2nd moment of area I _z	304210 mm ⁴
Max. driving torque	5.7 Nm
Max. force F _y	4216 N
Max. force F _z	4119 N
Max. torque M _x	36 Nm
Max. torque M _y	293 Nm
Max. torque M _z	288 Nm
Max. feed force F _x	300 N
Mass moment of inertia J _H per meter of stroke	8.9 kgcm ²
Mass moment of inertia J _L per kg of payload	2.3 kgcm ²
Mass moment of inertia J _O	5.9 kgcm ²
Feed constant	96 mm/U
Reference value, running performance	5000 km
Lubrication interval, distance dependent	1000 km
Moving mass at 0 mm stroke	1636 g
Additional weight per 10 mm stroke	38 g
Basic weight with 0 mm stroke	4146 g
Additional moving mass per 10 mm stroke	38 g
Material of end caps	Wrought aluminum alloy, anodized

Feature	Value
Profile material	Wrought aluminum alloy, anodized
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Drive head material	Wrought aluminum alloy, anodized
Guide rail material	Rolled steel, Corrotect coated
Housing material	High-alloy stainless steel
Slide material	Cast aluminum, anodized
Toothed belt clamping component material	Wrought aluminum alloy, anodized
Toothed belt material	Polychloroprene with glass cord and nylon coating