


Mini slide DGST-25-125-Y12A

Part number: 8085196

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 125 mm |
| Adjustable end-position range/front length | 32 mm |
| Adjustable end-position range/rear length | 30.4 mm |
| Piston diameter | 25 mm |
| Type code | DGST |
| Drive unit operating mode | Yoke |
| Cushioning | External hydraulic cushioning |
| Mounting position | Any |
| Guide | Ball bearing cage guide |
| Structural design | Twin piston Yoke Piston rod Slide |
| Position sensing | For proximity sensor |
| Symbol | 00991249 |
| Operating pressure | 0.1 MPa ... 0.8 MPa |
| Operating pressure | 1 bar ... 8 bar |
| Operating pressure | 14.5 psi ... 116 psi |
| Max. speed | 0.8 m/s |
| Repetition accuracy | ≤ 0.02 mm |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Ambient temperature | -10 °C ... 60 °C |
| Impact energy in the end positions | 6 J |
| Cushioning length | 10 mm |
| Max. force F _y | 1380 N |
| Max. force F _z | 1380 N |
| Max. torque M _x | 20 Nm |
| Max. torque M _y | 17 Nm |
| Max. torque M _z | 17 Nm |
| Theoretical force at 6 bar, retracting | 495 N |
| Theoretical force at 6 bar, advancing | 589 N |
| Moving mass | 1808 g |
| Product weight | 3717 g |

| Feature | Value |
|----------------------|---|
| Type of mounting | With through-hole |
| Pneumatic connection | G1/8 |
| Note on materials | Free of copper and PTFE RoHS-compliant |
| Cover material | Wrought aluminum alloy |
| Seals material | HNBR |
| Guide material | POM TPE-E High-alloy steel |
| Housing material | Wrought aluminum alloy |
| Piston rod material | High-alloy stainless steel |