



Cut



Medium Duty

Ergonomically designed cut-resistant gloves, providing comfort and dexterity

- **Advanced protection:** INTERCEPT™ Cut Resistance Technology and DuPont™ Kevlar® Stretch Armor mean HyFlex® 11-501 safety gloves meet ANSI A5/EN ISO D cut resistance levels
- **Elevated comfort:** Ergonomically designed for a barehand feel, HyFlex® 11-501 industrial gloves deliver ultimate comfort with reduced hand fatigue
- **Enhanced grip:** HyFlex® 11-501 PPE gloves' nitrile foam coating offers improved grip in dry and slightly oily conditions
- **Increased tactile sensitivity:** Foam coating also grants these industrial safety gloves increased tactile sensitivity
- **Heat resistance:** Beyond cut and abrasion protection, the 11-501 offers EN 407 level 1 contact heat resistance



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical

Applications

- Press injection molding
- Chassis assembly, body trimming
- Seizing and finishing structural parts
- Adjusting systems and screwing
- Applying finish to materials, products
- Loading and unloading trucks and vehicles
- Handling incoming goods
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Opening furnaces draining pumps valves or lines and crackers BTX process

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

11-501

INTERCEPT TECHNOLOGY[®] with
DuPont™ Kevlar[®] Stretch Armor

Key Features

- **INTERCEPT™ Cut Resistance Technology:** ANSI A5/EN ISO D cut protection
- **Ergonomic design:** Barehand feel and minimized hand fatigue
- **Nitrile foam coating:** Added tactile sensitivity and heightened grip

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex [®] 11-501	Finishing: Palm Coated Coating Material: Nitrile Liner Material: Kevlar [®] , Stainless steel, Spandex Cuff Style: Knitwrist	13	6, 7, 8, 9, 10	206-260 mm; 8.11-10.23 inches	Blue	<ul style="list-style-type: none"> • 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

