



SAFETY DATA SHEET

1. Identification

Product identifier HydroForce® Foaming Degreaser - 15 oz

Other means of identification

Product Code No. 14428 (Item# 1004980)

Recommended use General purpose degreaser

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Manufactured or sold by:

Company name CRC Industries, Inc.

Address 885 Louis Dr.
Warminster, PA 18974 US

Telephone

General Information 215-674-4300

Technical Assistance 800-521-3168

Customer Service 800-272-4620

**24-Hour Emergency
(CHEMTREC)** 800-424-9300 (US)

Website www.crcindustries.com

2. Hazard(s) identification

Physical hazards Gases under pressure Liquefied gas

Health hazards Serious eye damage/eye irritation Category 2A

Environmental hazards Hazardous to the aquatic environment, acute hazard Category 3

OSHA defined hazards Not classified.

Label elements



Signal word Warning

Hazard statement Contains gas under pressure; may explode if heated. Causes serious eye irritation. Harmful to aquatic life.

Precautionary statement

Prevention Do not puncture or incinerate container. Do not expose to heat or store at temperatures above 49 °C/120 °F. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Wash thoroughly after handling. Wear eye protection/face protection. Avoid release to the environment.

Response If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

Storage Protect from sunlight. Store in a well-ventilated place. Exposure to high temperature may cause can to burst.

Disposal Dispose of contents/container in accordance with local/regional/national regulations.

Hazard(s) not otherwise classified (HNOC) None known.

Supplemental information When exposed to extreme heat or hot surfaces, vapors may decompose to harmful or fatal corrosive gases such as hydrogen chloride and possibly phosgene.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
water		7732-18-5	70 - 80
2-butoxyethanol		111-76-2	3 - 5
alcohols, C9-11, ethoxylated		68439-46-3	3 - 5
quaternary coco alkylamine ethoxylate		61791-10-4	1 - 3

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Wash off with soap and water. Get medical attention if irritation develops and persists.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Ingestion	In the unlikely event of swallowing contact a physician or poison control center. Rinse mouth.
Most important symptoms/effects, acute and delayed	Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	Pressurized container may rupture when exposed to heat or flame. When exposed to extreme heat or hot surfaces, vapors may decompose to harmful or fatal corrosive gases such as hydrogen chloride and possibly phosgene. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire-fighting equipment/instructions	In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Containers should be cooled with water to prevent vapor pressure build up. Cool containers exposed to flames with water until well after the fire is out.
General fire hazards	Contents under pressure. Pressurized container may rupture when exposed to heat or flame.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothing during clean-up. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. This product is miscible in water. Prevent product from entering drains. Stop the flow of material, if this is without risk. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling

Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Do not get in eyes, on skin, or on clothing. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.

Conditions for safe storage, including any incompatibilities

Level 1 Aerosol.

Contents under pressure. Do not expose to heat or store at temperatures above 120°F/49°C as can may burst. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. Store in tightly closed container. Store in a well-ventilated place. Stored containers should be periodically checked for general condition and leakage. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
2-butoxyethanol (CAS 111-76-2)	PEL	240 mg/m3
		50 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
2-butoxyethanol (CAS 111-76-2)	TWA	20 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
2-butoxyethanol (CAS 111-76-2)	TWA	24 mg/m3
		5 ppm

Biological limit values

ACGIH Biological Exposure Indices

Components	Value	Determinant	Specimen	Sampling Time
2-butoxyethanol (CAS 111-76-2)	200 mg/g	Butoxyacetic acid (BAA), with hydrolysis	Creatinine in urine	*

* - For sampling details, please see the source document.

Exposure guidelines

US - California OELs: Skin designation

2-butoxyethanol (CAS 111-76-2) Can be absorbed through the skin.

US - Minnesota Haz Subs: Skin designation applies

2-butoxyethanol (CAS 111-76-2) Skin designation applies.

US - Tennessee OELs: Skin designation

2-butoxyethanol (CAS 111-76-2) Can be absorbed through the skin.

US NIOSH Pocket Guide to Chemical Hazards: Skin designation

2-butoxyethanol (CAS 111-76-2) Can be absorbed through the skin.

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

2-butoxyethanol (CAS 111-76-2) Can be absorbed through the skin.

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station.

Individual protection measures, such as personal protective equipment

Eye/face protection	Wear safety glasses with side shields (or goggles).
Skin protection	
Hand protection	Wear protective gloves such as: Neoprene. Nitrile.
Other	Wear appropriate chemical resistant clothing.
Respiratory protection	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
General hygiene considerations	When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties**Appearance**

Physical state	Liquid.
Form	Aerosol.
Color	Light yellow.
Odor	Mild.
Odor threshold	Not available.
pH	9.9
Melting point/freezing point	-103 °F (-75 °C) estimated
Initial boiling point and boiling range	212 °F (100 °C) estimated
Flash point	None.
Evaporation rate	Slow.
Flammability (solid, gas)	Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%)	1.3 % estimated
Flammability limit - upper (%)	12.6 % estimated
Vapor pressure	289.4 hPa estimated
Vapor density	Not available.
Relative density	1 estimated
Solubility(ies)	
Solubility (water)	Soluble.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	302 °F (150 °C) estimated
Decomposition temperature	Not available.
Percent volatile	88.5 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. When exposed to extreme heat or hot surfaces, vapors may decompose to harmful or fatal corrosive gases such as hydrogen chloride and possibly phosgene. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful.
Skin contact	2-Butoxy ethanol may be absorbed through the skin in toxic amounts if contact is repeated and prolonged. These effects have not been observed in humans.
Eye contact	Causes serious eye irritation.
Ingestion	Expected to be a low ingestion hazard.

Symptoms related to the physical, chemical and toxicological characteristics

Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.

Information on toxicological effects

Acute toxicity Not known.

Components	Species	Test Results
2-butoxyethanol (CAS 111-76-2)		
Acute		
Dermal		
LD50	Rabbit	220 mg/kg
Oral		
LD50	Rat	470 mg/kg
alcohols, C9-11, ethoxylated (CAS 68439-46-3)		
Acute		
Dermal		
LD50	Rabbit	5000 mg/kg
Oral		
LD50	Rat	1378 mg/kg
quaternary coco alkylamine ethoxylate (CAS 61791-10-4)		
Acute		
Oral		
LD50	Rat	580 mg/kg

Skin corrosion/irritation Prolonged skin contact may cause temporary irritation.

Serious eye damage/eye irritation Causes serious eye irritation.

Respiratory or skin sensitization

Respiratory sensitization Not a respiratory sensitizer.

Skin sensitization This product is not expected to cause skin sensitization.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity Not classifiable as to carcinogenicity to humans.

IARC Monographs. Overall Evaluation of Carcinogenicity

2-butoxyethanol (CAS 111-76-2) 3 Not classifiable as to carcinogenicity to humans.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity This product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity - single exposure Not classified.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard	Not an aspiration hazard.
Chronic effects	Prolonged inhalation may be harmful. May be harmful if absorbed through skin. 2-Butoxy ethanol may be absorbed through the skin in toxic amounts if contact is repeated and prolonged. These effects have not been observed in humans.

12. Ecological information

Ecotoxicity	Harmful to aquatic life.		
Components	Species		Test Results
2-butoxyethanol (CAS 111-76-2)			
Aquatic			
Fish	LC50	Inland silverside (Menidia beryllina)	1250 mg/l, 96 hours
alcohols, C9-11, ethoxylated (CAS 68439-46-3)			
Aquatic			
Acute			
Crustacea	EC50	Daphnia	1 - 10 mg/l, 48 hours
Fish	LC50	Fish	1 - 10 mg/l, 96 hours
quaternary coco alkylamine ethoxylate (CAS 61791-10-4)			
Aquatic			
Acute			
Fish	LC50	Trout family (Salmonidae)	24 mg/l, 96 hours
Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.		
Bioaccumulative potential			
Partition coefficient n-octanol / water (log Kow)			
2-butoxyethanol	0.83		
Mobility in soil	No data available.		
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.		

13. Disposal considerations

Hazardous waste code	Not regulated.
Disposal instructions	The dispensed liquid product is not a RCRA hazardous waste (See 40 CFR Part 261.20 - 261.33). Empty container can be recycled. Consult authorities before disposal. Contents under pressure. Do not puncture, incinerate or crush. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national regulations.
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.


14. Transport information

DOT

UN number	UN1950
UN proper shipping name	Aerosols, non-flammable, Limited Quantity
Transport hazard class(es)	
Class	2.2
Subsidiary risk	-
Label(s)	2.2
Packing group	Not applicable.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Packaging exceptions	306
Packaging non bulk	None
Packaging bulk	None

IATA

UN number	UN1950
UN proper shipping name	Aerosols, non-flammable, Limited Quantity

Transport hazard class(es)**Class** 2.2**Subsidiary risk** -**Packing group** Not applicable.**ERG Code** 2L**Special precautions for user** Read safety instructions, SDS and emergency procedures before handling.**Other information****Passenger and cargo aircraft** Allowed with restrictions.**Cargo aircraft only** Allowed with restrictions.**IMDG****UN number** UN1950**UN proper shipping name** AEROSOLS, Limited Quantity**Transport hazard class(es)****Class** 2.2**Subsidiary risk** -**Packing group** Not applicable.**Environmental hazards****Marine pollutant** No.**EmS** Not available.**Special precautions for user** Read safety instructions, SDS and emergency procedures before handling.**DOT; IMDG****IATA**

15. Regulatory information**US federal regulations**

This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

2-butoxyethanol (CAS 111-76-2)

CERCLA Hazardous Substance List (40 CFR 302.4)

2-butoxyethanol (CAS 111-76-2)

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Classified hazard categories Gas under pressure
Serious eye damage or eye irritation

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes

SARA 313 (TRI reporting)

Chemical name	CAS number	% by wt.
2-butoxyethanol	111-76-2	3 - 5

US state regulations

US. New Jersey Worker and Community Right-to-Know Act

2-butoxyethanol (CAS 111-76-2)

US. Massachusetts RTK - Substance List

2-butoxyethanol (CAS 111-76-2)

US. Pennsylvania Worker and Community Right-to-Know Law

2-butoxyethanol (CAS 111-76-2)

US. Rhode Island RTK

Not listed.

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 2016 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to www.P65Warnings.ca.gov.

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

2-butoxyethanol (CAS 111-76-2)

Volatile organic compounds (VOC) regulations

EPA

VOC content (40 CFR 51.100(s)) 9.7 %

Consumer products (40 CFR 59, Subpt. C) Not regulated

State

Consumer products This product is regulated as a General Purpose Degreaser (aerosol). This product is compliant for use in all 50 states.

VOC content (CA) 9.7 %

VOC content (OTC) 9.7 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes

Country(s) or region	Inventory name	On inventory (yes/no)*
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)
A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	09-12-2019
Prepared by	Allison Yoon
Version #	01
Further information	CRC # 692A/1002737
Disclaimer	The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..
Revision information	Product and Company Identification: Product and Company Identification Composition / Information on Ingredients: Ingredients Exposure controls/personal protection: Hand protection Physical & Chemical Properties: Multiple Properties Toxicological Information: Toxicological Data GHS: Classification