



SAFETY DATA SHEET

1. Identification

Product identifier TrueTap® Aqua Cutting Fluid - 5 gal

Other means of identification

Product Code No. 03442 (Item# 1003510)

Recommended use Cutting fluid

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Manufactured or sold by:

Company name CRC Industries, Inc.

Address 885 Louis Dr.
Warminster, PA 18974 US

Telephone

General Information 215-674-4300

Technical Assistance 800-521-3168

Customer Service 800-272-4620

**24-Hour Emergency
(CHEMTREC)** 800-424-9300 (US)

Website www.crcindustries.com

2. Hazard(s) identification

Physical hazards Not classified.

Health hazards Not classified.

Environmental hazards Not classified.

OSHA defined hazards Not classified.

Label elements

Hazard symbol None.

Signal word None.

Hazard statement The mixture does not meet the criteria for classification.

Precautionary statement

Prevention Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. Avoid release to the environment.

Response Wash hands after handling.

Storage Store away from incompatible materials.

Disposal Dispose of contents/container in accordance with local/regional/national regulations.

**Hazard(s) not otherwise
classified (HNOC)** None known.

Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
water		7732-18-5	70 - 80
organic phosphate ester		Proprietary	3 - 5
triethanolamine		102-71-6	3 - 5
polyalkylene glycol monobutyl ether		9038-95-3	1 - 3

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	If breathing is difficult, remove to fresh air and keep at rest in a position comfortable for breathing. If breathing stops, provide artificial respiration. Call a physician or poison control center immediately.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water. Get medical attention if irritation develops and persists. Wash contaminated clothing before reuse.
Eye contact	Immediately flush with plenty of water for at least 15 minutes. If easy to do, remove contact lenses. Hold eyelids apart during flushing to ensure complete rinsing of entire surface of eye and lids with water. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Do not induce vomiting without advice from poison control center.
Most important symptoms/effects, acute and delayed	Direct contact with eyes may cause temporary irritation.
Indication of immediate medical attention and special treatment needed	Treat symptomatically.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO ₂).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Fire-fighting equipment/instructions	Cool containers exposed to heat with water spray and remove container, if no risk is involved. Prevent fire extinguishing water from contaminating surface water or the ground water system.
General fire hazards	No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	In the event of a spill or accidental release, notify relevant authorities in accordance with all applicable regulations. Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Shovel up and place in a container for salvage or disposal. Following product recovery, flush area with water. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Sweep up and shovel into suitable containers for disposal. Clean surface thoroughly to remove residual contamination. Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid release to the environment. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground. Inform appropriate managerial or supervisory personnel of all environmental releases.

7. Handling and storage

Precautions for safe handling	Provide adequate ventilation. Avoid prolonged exposure. Avoid breathing vapors. Wear appropriate personal protective equipment. Observe good industrial hygiene practices. Wash hands thoroughly after handling. Wash contaminated clothing before reuse. Avoid release to the environment. Use care in handling/storage. For product usage instructions, see the product label.
Conditions for safe storage, including any incompatibilities	Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from heat and flame. Do not store container below 40 °F. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. ACGIH Threshold Limit Values

Components	Type	Value
triethanolamine (CAS 102-71-6)	TWA	5 mg/m3

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower should be available when handling this product.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection Wear protective gloves such as: Nitrile. Neoprene.

Other

Wear suitable protective clothing.

Respiratory protection

If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

Avoid contact with eyes, skin, and clothing. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state Liquid.

Form Liquid.

Color Blue

Odor Mild glycol.

Odor threshold Not available.

pH 7

Melting point/freezing point 32 °F (0 °C) estimated

Initial boiling point and boiling range 212 °F (100 °C) at 760 mmHg

Flash point None.

Evaporation rate Slow.

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) Not available.

Flammability limit - upper (%) Not available.

Vapor pressure < 1 mm Hg at 20 °C

Vapor density < 1 (air = 1)

Relative density 1.02

Solubility(ies)

Solubility (water) Soluble.

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature Not available.

Decomposition temperature	Not available.
Percent volatile	75 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Contact with incompatible materials.
Incompatible materials	Oxidizing agents.
Hazardous decomposition products	Carbon oxides.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful.
Skin contact	Prolonged skin contact may cause temporary irritation.
Eye contact	Direct contact with eyes may cause temporary irritation.
Ingestion	Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.

Symptoms related to the physical, chemical and toxicological characteristics	Direct contact with eyes may cause temporary irritation.
---	--

Information on toxicological effects

Acute toxicity

Components	Species	Test Results
organic phosphate ester		
<u>Acute</u>		
Oral		
LD50	Rat	> 2500 mg/kg
triethanolamine (CAS 102-71-6)		
<u>Acute</u>		
Dermal		
LD50	Rabbit	> 2000 mg/kg
Oral		
LD50	Rat	4190 mg/kg

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Prolonged skin contact may cause temporary irritation.
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.

Respiratory or skin sensitization

Respiratory sensitization	Not a respiratory sensitizer.
Skin sensitization	This product is not expected to cause skin sensitization.

Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
-------------------------------	--

Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
------------------------	---

IARC Monographs. Overall Evaluation of Carcinogenicity

triethanolamine (CAS 102-71-6) 3 Not classifiable as to carcinogenicity to humans.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
------------------------------	--

Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Not an aspiration hazard.
Chronic effects	Prolonged inhalation may be harmful. Prolonged exposure may cause chronic effects.

12. Ecological information

Ecotoxicity

Components		Species	Test Results
organic phosphate ester			
Aquatic			
<i>Acute</i>			
Crustacea	EC50	Daphnia	> 110 mg/l, 48 hours
Fish	LC50	Rainbow Trout	> 100 mg/l, 96 hours
triethanolamine (CAS 102-71-6)			
Aquatic			
<i>Acute</i>			
Fish	LC50	Bluegill (<i>Lepomis macrochirus</i>)	450 - 1000 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)

triethanolamine -1

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Hazardous waste code Not regulated.

Disposal instructions This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Dispose in accordance with all applicable regulations.

Contaminated packaging Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

15. Regulatory information

US federal regulations This product is not known to be a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Other federal regulations**Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List**

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)**SARA 302 Extremely hazardous substance**

Not listed.

SARA 311/312 Hazardous chemical No

SARA 313 (TRI reporting)
Not regulated.

US state regulations**US. New Jersey Worker and Community Right-to-Know Act**

triethanolamine (CAS 102-71-6)

US. Massachusetts RTK - Substance List

triethanolamine (CAS 102-71-6)

US. Pennsylvania Worker and Community Right-to-Know Law

triethanolamine (CAS 102-71-6)

US. Rhode Island RTK

triethanolamine (CAS 102-71-6)

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 2016 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

Volatile organic compounds (VOC) regulations**EPA**

VOC content (40 CFR 51.100(s)) Not determined

Consumer products (40 CFR 59, Subpt. C) Not regulated

State

Consumer products This product is regulated as a Cutting or Tapping Oil (non-aerosol). This product is compliant for use in all 50 states. *Local restriction: This product cannot be used in the South Coast Air Quality Management District of California.

VOC content (CA) 0 %

VOC content (OTC) 0 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	No
Canada	Domestic Substances List (DSL)	No
Canada	Non-Domestic Substances List (NDSL)	Yes
China	Inventory of Existing Chemical Substances in China (IECSC)	No
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No

Country(s) or region	Inventory name	On inventory (yes/no)*
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	No
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)
A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	07-22-2019
Prepared by	Dustin Kern
Version #	01
Disclaimer	The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..
Revision information	This document has undergone significant changes and should be reviewed in its entirety.