



A CSW Industrials Company

## SAFETY DATA SHEET

### RECTORSEAL® NO. 21

Slow-dry, soft-set pipe thread sealant

#### SECTION 1 – PRODUCT AND COMPANY INFORMATION

**Product Name**

Rectorseal® No.21 (Black Jack)

**Product Codes**

28541, 28651

**Chemical Family**

Organic

**Use**

Pipe thread sealant

**Manufacturer's Name**

RectorSeal, LLC

2601 Spenwick Drive

Houston, Texas 77055 USA

**Date of Validation**

July 27, 2020

**Date of Preparation**

July 10, 2012

**HMIS Codes**

Health 1

Flammability 2

Reactivity 0

PPI B

**Emergency Telephone No.**

Chemtrec 24 Hours

(800)-424-9300 USA

(703)-527-3887 International

**Technical Service Telephone No.**

(800)-231-3345 or (713)-263-8001

#### SECTION 2 – HAZARDS IDENTIFICATION

##### EMERGENCY OVERVIEW

**OSHA Hazards**

Combustable

**Target Organs**

Not Classified

##### GHS CLASSIFICATION

**Physical Hazards**

Combustable liquid (Category 4)

**Health Hazards**

**Acute Toxicity:**

Oral: Not Classified

Dermal: Not Classified

Inhalation: Not Classified

Skin Corrosion/Irritation: Not Classified

Serious Eye Damage/Eye Irritation: Not Classified  
Skin Sensitization: Not Classified  
Respiratory Sensitization: Not Classified  
Germ Cell Mutagenicity: Not Classified  
Carcinogenicity: See Section 11  
Reproductive Toxicology: Not Classified  
Target Organ Systemic Toxicity - Single Exposure: Not Classified  
Target Organ Systemic Toxicity - Repeated Exposure: Not Classified

Aspiration Toxicity: Not Classified

## GHS Label elements, including precautionary statements



GHS07: Exclamation Mark/Harmful

Signal Word: **Warning**

### Hazard Statements

H303 - May be harmful if swallowed.  
H313 - May be harmful in contact with skin.  
H335 + H336 - May cause respiratory irritation, and drowsiness or dizziness.

### Precautionary Statements

P102 - Keep out of reach of children.  
P210 - Keep away from heat/sparks/open flames/hot surfaces - no smoking.  
P240 - Ground/Bond container and receiving equipment.  
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray.  
P262 - Do not get in eyes, on skin, or on clothing.  
P264 - Wash hands thoroughly after handling.  
P280 - Wear protective gloves/protective clothing/eye protection/face protection.  
P301 + P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P362 - Take off contaminated clothing and wash before reuse.

EUH066 - Repeated exposure may cause skin dryness or cracking

Precautionary Statements - EU No. 1272/2008

## Summary Of Acute Hazards

Irritation to eyes, nose and throat; drowsiness, narcosis, tremors and other CNS effects at high concentration.

## Route Of Exposure, Signs And Symptoms

### INHALATION

Nasal and respiratory irritation, dizziness, narcosis, headache, nausea, CNS depression and unconsciousness.

### EYE CONTACT

Watering, blurred vision, inflammation and irritation which can result in corneal injury.

### SKIN CONTACT

Irritation, dermatitis.

## INGESTION

Nausea, vomiting; CNS depression; irritation of gastrointestinal tract, liver and peritoneal wall; lung congestion.

## SUMMARY OF CHRONIC HAZARDS

Skin irritation and dermatitis. Possible liver and kidney damage.

## MEDICAL CONDITIONS AGGRAVATED BY EXPOSURE

Individuals with pre-existing or chronic diseases of the eyes, skin, respiratory system, cardiovascular system, gastrointestinal system, liver or kidneys may have increased susceptibility to excessive exposures.

## SECTION 3 – COMPOSITION/INFORMATION ON INGREDIENTS

|                       |                   |
|-----------------------|-------------------|
| Ingredient:           | Diacetone Alcohol |
| Percentage By Weight: | 20-30             |
| CAS Number:           | 123-42-2          |
| EC#:                  | 204-626-7         |

## SECTION 4 – FIRST AID MEASURES

|               |                                                                                                                                                                                   |
|---------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| If inhaled:   | If overcome by exposure, remove victim to fresh air immediately. Give oxygen or artificial respiration as needed. Obtain emergency medical attention. Prompt action is essential. |
| If on skin:   | Wash with soap and water. If irritation occurs, seek medical attention.                                                                                                           |
| If in eyes:   | Flush eyes with large amounts of water for 15 minutes. Get medical attention.                                                                                                     |
| If swallowed: | If swallowed, call a physician immediately. Only induce vomiting at the instruction of a physician. Never give anything by mouth to an unconscious person.                        |

## SECTION 5 – FIRE FIGHTING MEASURES

### Extinguishing Media

Foam, dry chemical, carbon dioxide or water fog.

**Special Fire Fighting Procedures:** Wear self-contained breathing apparatus (SCBA) and other protective clothing. Hazardous decomposition products possible (see Section 10).

**Unusual Fire And Explosion Hazards:** Combustible – moderate flash point. Vapors heavier than air and may travel along the ground or to low spots at considerable distances to a source of ignition resulting in potential flashback. Burning liquid may float on water. Heat may build up pressure and rupture containers.

## SECTION 6 – ACCIDENTAL RELEASE MEASURES

**Steps To Be Taken In Case Material Is Released Or Spilled:** Remove all sources of ignition. Use absorbent materials to prevent footing hazard and to contain. Ventilate area with natural or explosion-proof, forced air ventilation. Avoid flushing into sewers, drains, waterways, and soil. Wear protective clothing and respiratory protection during cleanup.

## SECTION 7 – HANDLING AND STORAGE

**Precautions To Be Taken In Handling And Storing:** Keep container closed and upright when not in use. Do not store near heat, sparks, or open flames.

**Other Precautions:** Avoid prolonged or repeated contact with skin or clothing. Empty containers may contain residues; treat as if full and observe all products precautions. Do not reuse empty containers.

KEEP OUT OF REACH OF CHILDREN.

## SECTION 8 – EXPOSURE CONTROLS/PERSONAL PROTECTION

| Ingredient | Units |
|------------|-------|
|------------|-------|

**Diacetone Alcohol**

|            |        |
|------------|--------|
| ACGIH TLV: | 50 ppm |
|------------|--------|

|           |        |
|-----------|--------|
| OSHA PEL: | 50 ppm |
|-----------|--------|

**Respiratory Protection (Specify Type):** In confined poorly ventilated areas, use NIOSH/MSHA approved air purifying or supplied air purifying or supplied air respirators.

**Ventilation – Local Exhaust:** Acceptable

**Special:** Explosion-proof equipment.

**Mechanical (General):** Preferable

**Other:** N/A

**Protective Gloves:** Wear rubber gloves.

**Eye Protection:** Chemical splash goggles (ANSI Z-87.1 or equivalent)

**Other Protective Clothing Or Equipment:** Coveralls recommended.

**Work/Hygienic Practices:** Where use can result in skin contact, wash exposed areas thoroughly before eating, drinking, smoking, or leaving work area. Launder contaminated clothing before reuse.

## SECTION 9 – PHYSICAL AND CHEMICAL PROPERTIES

|                                                                                 |                          |
|---------------------------------------------------------------------------------|--------------------------|
| Boiling point:                                                                  | 322°F (161°C) @ 760 mmHg |
| Specific gravity (H2O = 1):                                                     | 1.38                     |
| Vapor pressure (mmHg):                                                          | 0.3 @ 68°F (20°C)        |
| Melting point:                                                                  | N/A                      |
| Vapor Density (Air = 1):                                                        | 1.1                      |
| Evaporation rate (Ethyl Acetate = 1):                                           | 0.14                     |
| Appearance/Odor:                                                                | Black paste/Mild odor    |
| Solubility in water:                                                            | 23%                      |
| Volatile Organic Compounds (VOC) Content<br>(theoretical percentage by weight): | 23% or (230 g/L)         |
| Flash point:                                                                    | 150°F (65°C) SETA CC     |
| Lower explosion limit:                                                          | N/D                      |
| Upper explosion limit:                                                          | N/D                      |

## SECTION 10 – STABILITY AND REACTIVITY

**Stability:** Stable

**Conditions To Avoid:** Heat, sparks, open flames, and strong oxidizing. Temperatures above 500°F (260°C).

**Incompatibility (Materials To Avoid):** Gaseous oxygen, strong oxidizing materials, molten alkali metals.

**Hazardous Decomposition Products:** CO, CO<sub>2</sub> and fragmented hydrocarbons.

**Hazardous Polymerization:** Will not occur.

## SECTION 11 – TOXICOLOGY INFORMATION

### Chronic Health Hazards

No ingredient in this product is an IARC, NTP or OSHA Listed carcinogen.

### Toxicology Data

#### Ingredient Name

##### Diacetone Alcohol

|                        |            |
|------------------------|------------|
| Oral-Rat LD50:         | 4000 mg/kg |
| Inhalation-Human TCLo: | 100 ppm    |

## SECTION 12 – ECOLOGICAL INFORMATION

### Ecological Data

|                                    |                   |
|------------------------------------|-------------------|
| Ingredient Name:                   | Diacetone Alcohol |
| Food Chain Concentration Potential | N/A               |
| Waterfowl Toxicity                 | N/A               |
| BOD                                | N/A               |
| Aquatic Toxicity                   | N/A               |

## SECTION 13 – DISPOSAL CONSIDERATIONS

**Waste Classification:** Non-regulated solid waste

**Disposal Method:** Approved landfill

Waste from this product is not considered hazardous as defined under the Resource Conservation and Recovery Act (RCRA) 40 CFR 261. Dispose of in accordance with federal, state, and local regulation regarding pollution.

## SECTION 14 – TRANSPORTATION INFORMATION

|                 |               |
|-----------------|---------------|
| DOT:            | Non-regulated |
| Ocean (IMDG):   | Non-regulated |
| Air (IATA):     | Non-regulated |
| WHMIS (Canada): | Non-regulated |

## SECTION 15 – REGULATORY INFORMATION

### Regulatory Data

|                  |                   |
|------------------|-------------------|
| Ingredient Name: | Diacetone Alcohol |
| SARA 313         | N/A               |
| TSCA Inventory   | Yes               |
| CERCLA RQ        | N/A               |
| RCRA Code        | N/A               |

## SECTION 16 – OTHER INFORMATION

This document is prepared pursuant to the OSHA Hazard Communication Standard (29 CFR 1910.1200). The information herein is given in good faith, but no warranty, expressed or implied is made.

Consult RectorSeal for further information: (713) 263-8001