



NOVAX®

Class 2 Rubber Insulating Glove with Bell Cuff - 16"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Bell cuff increases comfort on the job
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection

Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

Technical Data

Color	Black
Sizes Available	8-12
Packaging	Boxed
Packed	6 Pair/Case
Case Dimensions (in)	21.14 x 18.15 x 11.89
Case Weight (lbs)	13.67
Country of Origin	Malaysia
Material	Rubber
Length	16"
Cuff Color	Red
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

Performance Data

Electrical Class	Class 2
------------------	---------

Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
161-2-16/8	Black	8	616314121128	01616314121127	02616314121126
161-2-16/8.5	Black	8.5	616314125621	01616314125620	02616314125629
161-2-16/9	Black	9	616314121135	01616314121134	02616314121133
161-2-16/9.5	Black	9.5	616314125645	01616314125644	02616314125643
161-2-16/10	Black	10	616314121098	01616314121097	02616314121096
161-2-16/10.5	Black	10.5	616314125577	01616314125576	02616314125575
161-2-16/11	Black	11	616314121104	01616314121103	02616314121102
161-2-16/11.5	Black	11.5	616314125591	01616314125590	02616314125599
161-2-16/12	Black	12	616314121111	01616314121110	02616314121119