



SAFETY DATA SHEET

1. Identification

Product identifier	Quick Clean™ Safety Solvent and Degreaser
Other means of identification	
Product Code	No. 03184 (Item# 1003439)
Recommended use	General Purpose Degreaser
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
Manufactured or sold by:	
Company name	CRC Industries, Inc.
Address	885 Louis Dr. Warminster, PA 18974 US
Telephone	
General Information	215-674-4300
Technical Assistance	800-521-3168
Customer Service	800-272-4620
24-Hour Emergency	800-424-9300 (US)
(CHEMTREC)	703-527-3887 (International)
Website	www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Not classified.	
Health hazards	Skin corrosion/irritation	Category 2
	Serious eye damage/eye irritation	Category 2B
	Sensitization, skin	Category 1B
	Carcinogenicity	Category 1B
	Specific target organ toxicity, single exposure	Category 3 narcotic effects
Environmental hazards	Hazardous to the aquatic environment, acute hazard	Category 2
	Hazardous to the aquatic environment, long-term hazard	Category 2
OSHA defined hazards	Not classified.	
Label elements		



Signal word Danger

Hazard statement Causes skin irritation. May cause an allergic skin reaction. Causes eye irritation. May cause drowsiness or dizziness. May cause cancer. Toxic to aquatic life. Toxic to aquatic life with long lasting effects.

Precautionary statement

Prevention

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing mist or vapor. Wash thoroughly after handling. Contaminated work clothing must not be allowed out of the workplace. Wear protective gloves/protective clothing/eye protection/face protection. Avoid release to the environment.

Response	If on skin: Wash with plenty of water. If skin irritation or rash occurs: Get medical advice/attention. Take off contaminated clothing and wash before reuse. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. If exposed or concerned: Get medical advice/attention. Collect spillage.
Storage	Store in a well-ventilated place. Keep container tightly closed. Store locked up.
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	When exposed to extreme heat or hot surfaces, vapors may decompose to harmful or fatal corrosive gases such as hydrogen chloride and possibly phosgene.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
tetrachloroethylene	perchloroethylene	127-18-4	90 - 100

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water. In case of eczema or other skin disorders: Seek medical attention and take along these instructions. If skin irritation or rash occurs: Get medical advice/attention.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Ingestion	In the unlikely event of swallowing contact a physician or poison control center. Rinse mouth. Get medical attention if symptoms occur.
Most important symptoms/effects, acute and delayed	May cause drowsiness and dizziness. Headache. Nausea, vomiting. Irritation of eyes and mucous membranes. Exposed individuals may experience eye tearing, redness, and discomfort. Irritation of nose and throat. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Dermatitis. Rash.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	IF exposed or concerned: Get medical advice/attention. Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Wash contaminated clothing before reuse.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed. When exposed to extreme heat or hot surfaces, vapors may decompose to harmful or fatal corrosive gases such as hydrogen chloride and possibly phosgene.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	Move containers from fire area if you can do so without risk.
General fire hazards	No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Avoid breathing mist or vapor. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
--	---

Methods and materials for containment and cleaning up

This material is classified as a water pollutant under the Clean Water Act and should be prevented from contaminating soil or from entering sewage and drainage systems which lead to waterways.

Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use. Put material in suitable, covered, labeled containers. For waste disposal, see section 13 of the SDS.

Environmental precautions

Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage**Precautions for safe handling**

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Avoid breathing mist or vapor. Avoid contact with eyes, skin, and clothing. Avoid prolonged exposure. Should be handled in closed systems, if possible. Provide adequate ventilation. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.

Conditions for safe storage, including any incompatibilities

Store in a cool, dry place out of direct sunlight. Keep container tightly closed. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection**Occupational exposure limits**

The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit. At this time, the other constituents have no known exposure limits.

US. OSHA Table Z-2 (29 CFR 1910.1000)

Components	Type	Value
tetrachloroethylene (CAS 127-18-4)	Ceiling	200 ppm
	TWA	100 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
tetrachloroethylene (CAS 127-18-4)	STEL	100 ppm
	TWA	25 ppm

Biological limit values**ACGIH Biological Exposure Indices**

Components	Value	Determinant	Specimen	Sampling Time
tetrachloroethylene (CAS 127-18-4)	0.5 mg/l	Tetrachloroethylene	Blood	*
	3 ppm	Tetrachloroethylene	End-exhaled air	*

* - For sampling details, please see the source document.

Exposure guidelines**US - Minnesota Haz Subs: Skin designation applies**

tetrachloroethylene (CAS 127-18-4)

Skin designation applies.

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower should be available when handling this product. Provide eyewash station.

Individual protection measures, such as personal protective equipment**Eye/face protection**

Wear safety glasses with side shields (or goggles).

Skin protection**Hand protection**

Wear protective gloves such as: Nitrile. Viton/butyl. Polyvinyl alcohol (PVA). Silver Shield®

Other	Wear appropriate chemical resistant clothing.
Respiratory protection	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
General hygiene considerations	Observe any medical surveillance requirements. When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Contaminated work clothing should not be allowed out of the workplace.

9. Physical and chemical properties

Appearance

Physical state	Liquid.
Form	Liquid.
Color	Colorless.
Odor	Irritating.
Odor threshold	50 ppm
pH	Not available.
Melting point/freezing point	-8.1 °F (-22.3 °C) estimated
Initial boiling point and boiling range	250.3 °F (121.3 °C) estimated
Flash point	None (Tag Closed Cup)
Evaporation rate	Very fast.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Vapor pressure	13 mm Hg (68 °F (20 °C))
Vapor density	5.76 (air = 1)
Relative density	1.62
Solubility(ies)	
Solubility (water)	0.02 % (77 °F (25 °C))
Partition coefficient (n-octanol/water)	2.88
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Percent volatile	100 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Heat, flames and sparks. Contact with incompatible materials. When exposed to extreme heat or hot surfaces, vapors may decompose to harmful or fatal corrosive gases such as hydrogen chloride and possibly phosgene.
Incompatible materials	Strong oxidizing agents. Strong acids. Strong bases.
Hazardous decomposition products	Hydrogen chloride. Trace amounts of chlorine and phosgene. Carbon oxides. Halogenated materials. Carbonyl halides.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful. May cause drowsiness and dizziness. Headache. Nausea, vomiting.
Skin contact	Causes skin irritation. May cause an allergic skin reaction.
Eye contact	Causes eye irritation.
Ingestion	Ingestion of large amounts may produce gastrointestinal disturbances including irritation, nausea, and diarrhea.

Symptoms related to the physical, chemical and toxicological characteristics

May cause drowsiness and dizziness. Headache. Nausea, vomiting. Irritation of eyes and mucous membranes. Exposed individuals may experience eye tearing, redness, and discomfort. Irritation of nose and throat. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Dermatitis. Rash.

Information on toxicological effects

Acute toxicity None known.

Product	Species	Test Results
Quick Clean™ Safety Solvent and Degreaser		
Acute		
Dermal		
ATEmix		3228.0974 mg/kg
Oral		
ATEmix		2629.0191 mg/kg

Components	Species	Test Results
tetrachloroethylene (CAS 127-18-4)		
Acute		
Dermal		
LD50	Rabbit	> 3228 mg/kg
Oral		
LD50	Rat	2629 mg/kg

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation Causes skin irritation.

Serious eye damage/eye irritation Causes eye irritation.

Respiratory or skin sensitization

Respiratory sensitization Not a respiratory sensitizer.

Skin sensitization May cause an allergic skin reaction.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity May cause cancer.

IARC Monographs. Overall Evaluation of Carcinogenicity

tetrachloroethylene (CAS 127-18-4) 2A Probably carcinogenic to humans.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

tetrachloroethylene (CAS 127-18-4) Reasonably Anticipated to be a Human Carcinogen.

Reproductive toxicity This product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity - single exposure May cause drowsiness and dizziness.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard Not an aspiration hazard.

Chronic effects Prolonged inhalation may be harmful. Prolonged exposure may cause chronic effects.

12. Ecological information

Ecotoxicity Toxic to aquatic life with long lasting effects.

Components	Species	Test Results
tetrachloroethylene (CAS 127-18-4)		
Aquatic		
Fish	LC50 Rainbow trout,donaldson trout (Oncorhynchus mykiss)	4.73 - 5.27 mg/l, 96 hours

Persistence and degradability No data is available on the degradability of any ingredients in the mixture.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)	
Quick Clean™ Safety Solvent and Degreaser	2.88
tetrachloroethylene	2.88

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions This material and its container must be disposed of as hazardous waste. Consult authorities before disposal. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.

Hazardous waste code D039: Waste Tetrachloroethylene
F001: Waste Tetrachloroethylene - Spent halogenated solvent used in degreasing
F002: Waste Tetrachloroethylene - Spent halogenated solvent

US RCRA Hazardous Waste U List: Reference

tetrachloroethylene (CAS 127-18-4) U210

Contaminated packaging Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

UN number	UN1897
UN proper shipping name	Tetrachloroethylene (RQ = 100 LBS), MARINE POLLUTANT
Transport hazard class(es)	
Class	6.1(PGIII)
Subsidiary risk	-
Label(s)	6.1
Packing group	III
Environmental hazards	
Marine pollutant	Yes.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Special provisions	IB3, N36, T4, TP1
Packaging exceptions	153
Packaging non bulk	203
Packaging bulk	241

IATA

UN number	UN1897
UN proper shipping name	Tetrachloroethylene
Transport hazard class(es)	
Class	6.1(PGIII)
Subsidiary risk	-
Packing group	III
ERG Code	6L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Other information	
Passenger and cargo aircraft	Allowed with restrictions.

Cargo aircraft only	Allowed with restrictions.
IMDG	
UN number	UN1897
UN proper shipping name	TETRACHLOROETHYLENE, MARINE POLLUTANT
Transport hazard class(es)	
Class	6.1(PGIII)
Subsidiary risk	-
Packing group	III
Environmental hazards	
Marine pollutant	Yes.
EmS	F-A, S-A
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
All components are on the U.S. EPA TSCA Inventory List.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

tetrachloroethylene (CAS 127-18-4)

CERCLA Hazardous Substance List (40 CFR 302.4)

tetrachloroethylene (CAS 127-18-4) Listed.

CERCLA Hazardous Substances: Reportable quantity

tetrachloroethylene (CAS 127-18-4) 100 LBS

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

tetrachloroethylene (CAS 127-18-4)

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Classified hazard categories
Acute toxicity (any route of exposure)
Skin corrosion or irritation
Serious eye damage or eye irritation
Respiratory or skin sensitization
Carcinogenicity
Specific target organ toxicity (single or repeated exposure)

SARA 302 Extremely hazardous substance

Not listed.

SARA 313 (TRI reporting)

Chemical name	CAS number	% by wt.
tetrachloroethylene	127-18-4	90 - 100

US state regulations

US. New Jersey Worker and Community Right-to-Know Act

tetrachloroethylene (CAS 127-18-4)

US. Massachusetts RTK - Substance List

tetrachloroethylene (CAS 127-18-4)

US. Pennsylvania Worker and Community Right-to-Know Law

tetrachloroethylene (CAS 127-18-4)

US. Rhode Island RTK

tetrachloroethylene (CAS 127-18-4)

California Proposition 65**WARNING:** Cancer - www.P65Warnings.ca.gov**California Proposition 65 - CRT: Listed date/Carcinogenic substance**

tetrachloroethylene (CAS 127-18-4)

Listed: April 1, 1988

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

tetrachloroethylene (CAS 127-18-4)

Volatile organic compounds (VOC) regulations**EPA****VOC content (40 CFR 51.100(s))** 0 %**Consumer products (40 CFR 59, Subpt. C)** Not regulated**State****Consumer products** This product is not for retail sale. It is for use in the manufacturing process only.**VOC content (CA)** 0 %**VOC content (OTC)** 0 %**International Inventories**

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	Yes
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Toxic Chemical Substances (TCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	01-26-2018
Revision date	01-26-2018
Prepared by	Allison Yoon
Version #	03
Further information	CRC # 491G/1002481
HMIS® ratings	Health: 2* Flammability: 0 Physical hazard: 0 Personal protection: B

NFPA ratings

Health: 2
Flammability: 0
Instability: 0

NFPA ratings**Disclaimer**

The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..