



SAFETY DATA SHEET

1. Identification

Product identifier	3-36® Multi-Purpose Lubricant & Corrosion Inhibitor - 55 gal
Other means of identification	
Product Code	No. 03011 (Item# 1003262)
Recommended use	Multi-purpose lubricant
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
Manufactured or sold by:	
Company name	CRC Industries, Inc.
Address	885 Louis Dr. Warminster, PA 18974 US
Telephone	
General Information	215-674-4300
Technical Assistance	800-521-3168
Customer Service	800-272-4620
24-Hour Emergency (CHEMTREC)	800-424-9300 (US)
Website	www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Flammable liquids	Category 4
Health hazards	Sensitization, skin	Category 1
	Aspiration hazard	Category 1
Environmental hazards	Not classified.	
OSHA defined hazards	Not classified.	
Label elements		



Signal word	Danger
Hazard statement	Combustible liquid. May be fatal if swallowed and enters airways. May cause an allergic skin reaction.
Precautionary statement	
Prevention	Keep away from flames and hot surfaces. - No smoking. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing mist/vapors. Contaminated work clothing must not be allowed out of the workplace. Wear protective gloves/eye protection/face protection.
Response	If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting. If on skin: Wash with plenty of water. If skin irritation or rash occurs: Get medical advice/attention. Wash contaminated clothing before reuse. In case of fire: Do not use water jet as an extinguisher, as this will spread the fire.
Storage	Store in a well-ventilated place. Keep cool. Store locked up.
Disposal	Dispose of contents/container in accordance with local/regional/national/international regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
distillates (petroleum), hydrotreated light		64742-47-8	60 - 70
distillates (petroleum), hydrotreated heavy paraffinic		64742-54-7	5 - 10
paraffin oils (petroleum), catalytic dewaxed heavy		64742-70-7	5 - 10
paraffin oils (petroleum), catalytic dewaxed light		64742-71-8	5 - 10
butyl stearate		123-95-5	1 - 5
dipropylene glycol methyl ether acetate		88917-22-0	1 - 5
petrolatum		8009-03-8	1 - 5

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water. In case of eczema or other skin disorders: Seek medical attention and take along these instructions.
Eye contact	Rinse with water. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	Aspiration may cause pulmonary edema and pneumonitis. Headache. Nausea, vomiting. Diarrhea. Direct contact with eyes may cause temporary irritation. May cause an allergic skin reaction. Dermatitis. Rash.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Wash contaminated clothing before reuse.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Alcohol resistant foam. Dry chemical powder. Dry chemicals. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	The product is combustible, and heating may generate vapors which may form explosive vapor/air mixtures. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire-fighting equipment/instructions	In case of fire and/or explosion do not breathe fumes. Move containers from fire area if you can do so without risk. Cool containers exposed to heat with water spray and remove container, if no risk is involved. Use standard firefighting procedures and consider the hazards of other involved materials.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	Combustible liquid. Will burn if involved in a fire.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Wear appropriate protective equipment and clothing during clean-up. Avoid breathing mist/vapors. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
--	---

Methods and materials for containment and cleaning up

Use water spray to reduce vapors or divert vapor cloud drift. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material.

Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Use a non-combustible material like vermiculite, sand or earth to soak up the product and place into a container for later disposal. Following product recovery, flush area with water.

Small Spills: Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS. Avoid discharge into drains, water courses or onto the ground.

Environmental precautions

7. Handling and storage**Precautions for safe handling**

Keep away from open flames, hot surfaces and sources of ignition. When using do not smoke. Avoid breathing mist/vapors. Avoid contact with eyes, skin, and clothing. Avoid prolonged or repeated contact with skin. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Observe good industrial hygiene practices. For product usage instructions, see the product label.

Conditions for safe storage, including any incompatibilities

Keep away from heat and sources of ignition. Store in a cool, dry place out of direct sunlight. Store in tightly closed container. Store in a well-ventilated place. Keep in an area equipped with sprinklers. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection**Occupational exposure limits**

The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit. At this time, the other constituents have no known exposure limits.

**U.S. - OSHA
Components**

Components	Type	Value
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	TWA	5 mg/m3

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value	Form
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	PEL	5 mg/m3	Mist.
paraffin oils (petroleum), catalytic dewaxed heavy (CAS 64742-70-7)	PEL	5 mg/m3	Mist.
paraffin oils (petroleum), catalytic dewaxed light (CAS 64742-71-8)	PEL	5 mg/m3	Mist.
petrolatum (CAS 8009-03-8)	PEL	5 mg/m3	Mist.

ACGIH**Components**

Components	Type	Value	Form
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	TWA	5 mg/m3	Inhalable fraction

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
butyl stearate (CAS 123-95-5)	TWA	3 mg/m3	Respirable fraction.
		10 mg/m3	Inhalable fraction.
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	TWA	5 mg/m3	Inhalable fraction.

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
paraffin oils (petroleum), catalytic dewaxed heavy (CAS 64742-70-7)	TWA	5 mg/m3	Inhalable fraction.
paraffin oils (petroleum), catalytic dewaxed light (CAS 64742-71-8)	TWA	5 mg/m3	Inhalable fraction.
petrolatum (CAS 8009-03-8)	TWA	5 mg/m3	Inhalable fraction.

U.S. - NIOSH

Components	Type	Value	Form
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	STEL	10 mg/m3	Mist
	TWA	5 mg/m3	Mist

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value	Form
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	STEL	10 mg/m3	Mist.
	TWA	5 mg/m3	Mist.
distillates (petroleum), hydrotreated light (CAS 64742-47-8)	TWA	100 mg/m3	
paraffin oils (petroleum), catalytic dewaxed heavy (CAS 64742-70-7)	STEL	10 mg/m3	Mist.
	TWA	5 mg/m3	Mist.
paraffin oils (petroleum), catalytic dewaxed light (CAS 64742-71-8)	STEL	10 mg/m3	Mist.
	TWA	5 mg/m3	Mist.
petrolatum (CAS 8009-03-8)	STEL	10 mg/m3	Mist.
	TWA	5 mg/m3	Mist.

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

Eye/face protection	Wear safety glasses with side shields (or goggles).
Skin protection	
Hand protection	Wear protective gloves such as: Neoprene. Nitrile.
Other	Wear appropriate chemical resistant clothing. Use of an impervious apron is recommended.
Respiratory protection	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
General hygiene considerations	When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Contaminated work clothing should not be allowed out of the workplace.

9. Physical and chemical properties

Appearance

Physical state	Liquid.
Form	Liquid.
Color	Blue green

Odor Pleasant.

Odor threshold Not available.

pH Not available.

Melting point/freezing point Not available.

Initial boiling point and boiling range 380 °F (193.3 °C) estimated

Flash point 192 °F (88.9 °C) Setflash

Evaporation rate Slow.

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) 0.5 % estimated

Flammability limit - upper (%) 5.5 % estimated

Vapor pressure 0.2 hPa estimated

Vapor density > 1 (air = 1)

Relative density 0.83

Solubility(ies)

Solubility (water) Not available.

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature 410 °F (210 °C) estimated

Decomposition temperature Not available.

Viscosity Not available.

Percent volatile 78.5 % estimated

10. Stability and reactivity

Reactivity The product is stable and non-reactive under normal conditions of use, storage and transport.

Chemical stability Material is stable under normal conditions.

Possibility of hazardous reactions No dangerous reaction known under conditions of normal use.

Conditions to avoid Avoid heat, sparks, open flames and other ignition sources. Avoid temperatures exceeding the flash point. Contact with incompatible materials.

Incompatible materials Strong oxidizing agents.

Hazardous decomposition products Carbon oxides. Sulfur oxides. Hydrogen sulfide. Mercaptans. Sulfides.

11. Toxicological information

Information on likely routes of exposure

Inhalation Prolonged inhalation may be harmful.

Skin contact May cause an allergic skin reaction.

Eye contact Based on available data, the classification criteria are not met.

Ingestion Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.

Symptoms related to the physical, chemical and toxicological characteristics Aspiration may cause pulmonary edema and pneumonitis. Headache. Nausea, vomiting. Diarrhea. May cause an allergic skin reaction. Dermatitis. Rash.

Information on toxicological effects

Acute toxicity		May be fatal if swallowed and enters airways.
Components	Species	Test Results
distillates (petroleum), hydrotreated light (CAS 64742-47-8)		
<u>Acute</u>		
Dermal		
LD50	Rat	> 2000 mg/kg
Inhalation		
LC50	Rat	> 5 mg/l, 4 hours
Oral		
LD50	Rat	> 5000 mg/kg, 2.5 hours
paraffin oils (petroleum), catalytic dewaxed heavy (CAS 64742-70-7)		
<u>Acute</u>		
Dermal		
LD50	Rabbit	> 2000 mg/kg
Oral		
LD50	Rat	> 5000 mg/kg
paraffin oils (petroleum), catalytic dewaxed light (CAS 64742-71-8)		
<u>Acute</u>		
Dermal		
LD50	Rabbit	> 2000 mg/kg
Oral		
LD50	Rat	> 5000 mg/kg
Skin corrosion/irritation		Prolonged skin contact may cause temporary irritation.
Serious eye damage/eye irritation		Direct contact with eyes may cause temporary irritation.
Respiratory or skin sensitization		
Respiratory sensitization		Not a respiratory sensitizer.
Skin sensitization		May cause an allergic skin reaction.
Germ cell mutagenicity		No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity		Not classifiable as to carcinogenicity to humans.
IARC Monographs. Overall Evaluation of Carcinogenicity		
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)		3 Not classifiable as to carcinogenicity to humans.
paraffin oils (petroleum), catalytic dewaxed light (CAS 64742-71-8)		3 Not classifiable as to carcinogenicity to humans.
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)		
Not listed.		
US. National Toxicology Program (NTP) Report on Carcinogens		
Not listed.		
Reproductive toxicity		This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure		Not classified.
Specific target organ toxicity - repeated exposure		Not classified.
Aspiration hazard		May be fatal if swallowed and enters airways.
Chronic effects		Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity	The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
--------------------	--

Components	Species		Test Results
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)			
Aquatic			
Acute			
Crustacea	EC50	Water flea (Daphnia magna)	> 10000 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas)	> 100 mg/l, 96 hours
distillates (petroleum), hydrotreated light (CAS 64742-47-8)			
Aquatic			
Fish	LC50	Rainbow trout,donaldson trout (Oncorhynchus mykiss)	2.9 mg/l, 96 hours
paraffin oils (petroleum), catalytic dewaxed light (CAS 64742-71-8)			
Aquatic			
Acute			
Crustacea	EC50	Daphnia	> 100 mg/l, 48 hours
Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.		
Bioaccumulative potential			
Mobility in soil	No data available.		
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.		

13. Disposal considerations

Disposal instructions	This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.
Hazardous waste code	Not regulated.
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information

DOT	Not regulated as dangerous goods.
IATA	Not regulated as dangerous goods.
IMDG	Not regulated as dangerous goods.

15. Regulatory information

US federal regulations	This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)	Not regulated.
SARA 304 Emergency release notification	Not regulated.
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)	Not listed.
CERCLA Hazardous Substance List (40 CFR 302.4)	Not listed.
CERCLA Hazardous Substances: Reportable quantity	Not listed.
Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.	

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Classified hazard categories Flammable (gases, aerosols, liquids, or solids)
Respiratory or skin sensitization
Aspiration hazard

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes

SARA 313 (TRI reporting)

Not regulated.

US state regulations

US. New Jersey Worker and Community Right-to-Know Act

Not listed.

US. Massachusetts RTK - Substance List

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)
paraffin oils (petroleum), catalytic dewaxed heavy (CAS 64742-70-7)
paraffin oils (petroleum), catalytic dewaxed light (CAS 64742-71-8)
petrolatum (CAS 8009-03-8)

US. Pennsylvania Worker and Community Right-to-Know Law

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)
distillates (petroleum), hydrotreated light (CAS 64742-47-8)
paraffin oils (petroleum), catalytic dewaxed heavy (CAS 64742-70-7)
paraffin oils (petroleum), catalytic dewaxed light (CAS 64742-71-8)
petrolatum (CAS 8009-03-8)

US. Rhode Island RTK

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)
distillates (petroleum), hydrotreated light (CAS 64742-47-8)
paraffin oils (petroleum), catalytic dewaxed heavy (CAS 64742-70-7)
paraffin oils (petroleum), catalytic dewaxed light (CAS 64742-71-8)
petrolatum (CAS 8009-03-8)

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 2016 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to www.P65Warnings.ca.gov.

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)
distillates (petroleum), hydrotreated light (CAS 64742-47-8)
paraffin oils (petroleum), catalytic dewaxed heavy (CAS 64742-70-7)
paraffin oils (petroleum), catalytic dewaxed light (CAS 64742-71-8)
petrolatum (CAS 8009-03-8)

Volatile organic compounds (VOC) regulations

EPA

VOC content (40 CFR 51.100(s)) 100 %

Consumer products (40 CFR 59, Subpt. C) Not regulated

State**Consumer products**

This product is regulated as a Multi-Purpose Lubricant. This product is compliant for use in all 50 states.

VOC content (CA)

0 %

VOC content (OTC)

0 %

International Inventories**Country(s) or region****Inventory name****On inventory (yes/no)***

Australia

Australian Inventory of Chemical Substances (AICS)

Yes

Canada

Domestic Substances List (DSL)

Yes

Canada

Non-Domestic Substances List (NDSL)

No

China

Inventory of Existing Chemical Substances in China (IECSC)

Yes

Europe

European Inventory of Existing Commercial Chemical Substances (EINECS)

No

Europe

European List of Notified Chemical Substances (ELINCS)

No

Japan

Inventory of Existing and New Chemical Substances (ENCS)

No

Korea

Existing Chemicals List (ECL)

Yes

New Zealand

New Zealand Inventory

No

Philippines

Philippine Inventory of Chemicals and Chemical Substances (PICCS)

No

Taiwan

Taiwan Chemical Substance Inventory (TCSI)

Yes

United States & Puerto Rico

Toxic Substances Control Act (TSCA) Inventory

Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision**Issue date**

03-28-2020

Prepared by

Allison Yoon

Version #

01

Further information

CRC # 510F/1002511

Disclaimer

The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..

Revision information

This document has undergone significant changes and should be reviewed in its entirety.