



SAFETY DATA SHEET

1. Identification

| | |
|---|--|
| Product identifier | Ultra-Lite 3-36® - 1 gallon |
| Other means of identification | |
| Product Code | No. 03161 (Item# 1003429) |
| Recommended use | Dry film lubricant |
| Recommended restrictions | None known. |
| Manufacturer/Importer/Supplier/Distributor information | |
| Manufactured or sold by: | |
| Company name | CRC Industries, Inc. |
| Address | 885 Louis Dr. Warminster, PA 18974 US |
| Telephone | |
| General Information | 215-674-4300 |
| Technical Assistance | 800-521-3168 |
| Customer Service | 800-272-4620 |
| 24-Hour Emergency (CHEMTREC) | 800-424-9300 (US) |
| Website | www.crcindustries.com |

2. Hazard(s) identification

| | | |
|------------------------------|--|-----------------------------|
| Physical hazards | Flammable liquids | Category 4 |
| Health hazards | Skin corrosion/irritation | Category 2 |
| | Sensitization, skin | Category 1 |
| | Specific target organ toxicity, single exposure | Category 3 narcotic effects |
| | Aspiration hazard | Category 1 |
| Environmental hazards | Hazardous to the aquatic environment, acute hazard | Category 2 |
| | Hazardous to the aquatic environment, long-term hazard | Category 2 |
| OSHA defined hazards | Not classified. | |

Label elements



| | |
|--------------------------------|---|
| Signal word | Danger |
| Hazard statement | Combustible liquid. May be fatal if swallowed and enters airways. Causes skin irritation. May cause an allergic skin reaction. May cause drowsiness or dizziness. Toxic to aquatic life. Toxic to aquatic life with long lasting effects. |
| Precautionary statement | |
| Prevention | Keep away from flames and hot surfaces-No smoking. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing vapors. Wash thoroughly after handling. Contaminated work clothing must not be allowed out of the workplace. Wear protective gloves/eye protection/face protection. Avoid release to the environment. |
| Response | If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting. If on skin: Wash with plenty of water. If skin irritation or rash occurs: Get medical advice/attention. Take off contaminated clothing and wash it before reuse. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell. In case of fire: Do not use water jet as an extinguisher, as this will spread the fire. Collect spillage. |

| | |
|--|--|
| Storage | Keep cool. Store in a well-ventilated place. Keep container tightly closed. Store locked up. |
| Disposal | Dispose of contents/container in accordance with local/regional/national regulations. |
| Hazard(s) not otherwise classified (HNOC) | None known. |
| Supplemental information | None. |

3. Composition/information on ingredients

Mixtures

| Chemical name | Common name and synonyms | CAS number | % |
|---|--------------------------|-------------|---------|
| distillates (petroleum), hydrotreated light | | 64742-47-8 | 80 - 90 |
| calcium bis(dinonylnaphthalenesulphonate) | | 57855-77-3 | < 1 |
| calcium carbonate | | 471-34-1 | < 0.3 |
| Vanilla fragrances | | Proprietary | < 0.3 |

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

| | |
|---|--|
| Inhalation | Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a poison center or doctor/physician if you feel unwell. |
| Skin contact | Remove contaminated clothing immediately and wash skin with soap and water. In case of eczema or other skin disorders: Seek medical attention and take along these instructions. Wash contaminated clothing before reuse. |
| Eye contact | Rinse with water. Get medical attention if irritation develops and persists. |
| Ingestion | Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs. |
| Most important symptoms/effects, acute and delayed | Aspiration may cause pulmonary edema and pneumonitis. May cause drowsiness and dizziness. Headache. Nausea, vomiting. Diarrhea. Direct contact with eyes may cause temporary irritation. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Dermatitis. Rash. |
| Indication of immediate medical attention and special treatment needed | Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed. |
| General information | Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Wash contaminated clothing before reuse. |

5. Fire-fighting measures

| | |
|--|--|
| Suitable extinguishing media | Water fog. Alcohol resistant foam. Dry chemical powder. Dry chemicals. Carbon dioxide (CO ₂). |
| Unsuitable extinguishing media | Do not use water jet as an extinguisher, as this will spread the fire. |
| Specific hazards arising from the chemical | The product is combustible, and heating may generate vapors which may form explosive vapor/air mixtures. During fire, gases hazardous to health may be formed. |
| Special protective equipment and precautions for firefighters | Self-contained breathing apparatus and full protective clothing must be worn in case of fire. |
| Fire-fighting equipment/instructions | In case of fire and/or explosion do not breathe fumes. Move containers from fire area if you can do so without risk. Cool containers exposed to heat with water spray and remove container, if no risk is involved. Use standard firefighting procedures and consider the hazards of other involved materials. |
| General fire hazards | Combustible liquid. Will burn if involved in a fire. |

6. Accidental release measures

| | |
|--|---|
| Personal precautions, protective equipment and emergency procedures | Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Wear appropriate protective equipment and clothing during clean-up. Avoid breathing mist/vapors. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS. |
|--|---|

Methods and materials for containment and cleaning up

Use water spray to reduce vapors or divert vapor cloud drift. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. This product is miscible in water. Prevent product from entering drains.

Small Spills: Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.

Environmental precautions

Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage**Precautions for safe handling**

Keep away from open flames, hot surfaces and sources of ignition. When using do not smoke. Avoid breathing mist/vapors. Avoid contact with eyes, skin, and clothing. Avoid prolonged or repeated contact with skin. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.

Conditions for safe storage, including any incompatibilities

Keep away from heat and sources of ignition. Store in a cool, dry place out of direct sunlight. Store in tightly closed container. Store in a well-ventilated place. Keep in an area equipped with sprinklers. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection**Occupational exposure limits****US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)**

| Components | Type | Value | Form |
|----------------------------------|------|----------|----------------------|
| calcium carbonate (CAS 471-34-1) | PEL | 5 mg/m3 | Respirable fraction. |
| | | 15 mg/m3 | Total dust. |

US. NIOSH: Pocket Guide to Chemical Hazards

| Components | Type | Value | Form |
|--|------|-----------|-------------|
| calcium carbonate (CAS 471-34-1) | TWA | 5 mg/m3 | Respirable. |
| | | 10 mg/m3 | Total |
| distillates (petroleum), hydrotreated light (CAS 64742-47-8) | TWA | 100 mg/m3 | |

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower should be available when handling this product.

Individual protection measures, such as personal protective equipment**Eye/face protection**

Wear safety glasses with side shields (or goggles).

Skin protection**Hand protection**

Wear protective gloves such as: Nitrile. Neoprene.

Other

Wear appropriate chemical resistant clothing. Use of an impervious apron is recommended.

Respiratory protection

If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

When using, do not eat, drink or smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Contaminated work clothing should not be allowed out of the workplace.

9. Physical and chemical properties

Appearance

| | |
|----------------|---------|
| Physical state | Liquid. |
| Form | Liquid. |
| Color | Amber. |

Odor Petroleum.

Odor threshold Not available.

pH Not available.

Melting point/freezing point -56.2 °F (-49 °C) estimated

Initial boiling point and boiling range 360 °F (182.2 °C) estimated

Flash point 172 °F (77.8 °C) Setflash

Evaporation rate Slow.

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) 0.6 % estimated

Flammability limit - upper (%) 5.5 % estimated

Vapor pressure 0.5 hPa estimated

Vapor density > 1 (air = 1)

Relative density 0.8

Solubility(ies)

Solubility (water) Negligible.

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature 428 °F (220 °C) estimated

Decomposition temperature Not available.

Viscosity Not available.

Percent volatile 90.1 % estimated

10. Stability and reactivity

Reactivity The product is stable and non-reactive under normal conditions of use, storage and transport.

Chemical stability Material is stable under normal conditions.

Possibility of hazardous reactions No dangerous reaction known under conditions of normal use.

Conditions to avoid Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. Avoid temperatures exceeding the flash point. Contact with incompatible materials.

Incompatible materials Strong oxidizing agents.

Hazardous decomposition products Carbon oxides.

11. Toxicological information

Information on likely routes of exposure

Inhalation May cause drowsiness and dizziness. Headache. Nausea, vomiting. Prolonged inhalation may be harmful.

Skin contact Causes skin irritation. May cause an allergic skin reaction.

Eye contact Direct contact with eyes may cause temporary irritation.

Ingestion Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.

Symptoms related to the physical, chemical and toxicological characteristics Aspiration may cause pulmonary edema and pneumonitis. May cause drowsiness and dizziness. Headache. Nausea, vomiting. Diarrhea. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Dermatitis. Rash.

Information on toxicological effects

Acute toxicity May be fatal if swallowed and enters airways.

| Components | Species | Test Results |
|---|--|-------------------------|
| calcium bis(dinonylnaphthalenesulphonate) (CAS 57855-77-3) | | |
| Acute | | |
| Dermal | | |
| LD50 | Rabbit | > 20 g/kg |
| Oral | | |
| LD50 | Rat | > 5000 mg/kg |
| calcium carbonate (CAS 471-34-1) | | |
| Acute | | |
| Dermal | | |
| LD50 | Rabbit | > 2000 mg/kg |
| Inhalation | | |
| LC50 | Rat | > 3 mg/l |
| Oral | | |
| LD50 | Rat | 6450 mg/kg |
| distillates (petroleum), hydrotreated light (CAS 64742-47-8) | | |
| Acute | | |
| Dermal | | |
| LD50 | Rat | > 2000 mg/kg |
| Inhalation | | |
| LC50 | Rat | > 5.2 mg/l, 4 hours |
| Oral | | |
| LD50 | Rat | > 5000 mg/kg, 2.5 hours |
| Skin corrosion/irritation | Causes skin irritation. | |
| Serious eye damage/eye irritation | Direct contact with eyes may cause temporary irritation. | |
| Respiratory or skin sensitization | | |
| Respiratory sensitization | Not a respiratory sensitizer. | |
| Skin sensitization | May cause an allergic skin reaction. | |
| Germ cell mutagenicity | No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic. | |
| Carcinogenicity | Not classifiable as to carcinogenicity to humans. | |
| IARC Monographs. Overall Evaluation of Carcinogenicity | | |
| Not listed. | | |
| OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052) | | |
| Not regulated. | | |
| US. National Toxicology Program (NTP) Report on Carcinogens | | |
| Not listed. | | |
| Reproductive toxicity | This product is not expected to cause reproductive or developmental effects. | |
| Specific target organ toxicity - single exposure | May cause drowsiness and dizziness. | |
| Specific target organ toxicity - repeated exposure | Not classified. | |
| Aspiration hazard | May be fatal if swallowed and enters airways. | |
| Chronic effects | Prolonged inhalation may be harmful. | |

12. Ecological information

Ecotoxicity Toxic to aquatic life with long lasting effects.

| Components | Species | Test Results |
|--|--|--|
| calcium carbonate (CAS 471-34-1) | | |
| Aquatic | | |
| <i>Acute</i> | | |
| Fish | LC50 | Western mosquitofish (<i>Gambusia affinis</i>) > 56000 mg/l, 96 hours |
| distillates (petroleum), hydrotreated light (CAS 64742-47-8) | | |
| Aquatic | | |
| <i>Acute</i> | | |
| Crustacea | EC50 | Water flea (<i>Daphnia magna</i>) > 1000 mg/l, 48 hours |
| Fish | LC50 | Rainbow trout, donaldson trout > 1000 mg/l, 96 hours (<i>Oncorhynchus mykiss</i>) |
| Persistence and degradability | No data is available on the degradability of any ingredients in the mixture. | |
| Bioaccumulative potential | No data available. | |
| Mobility in soil | No data available. | |
| Other adverse effects | The product contains volatile organic compounds which have a photochemical ozone creation potential. | |

13. Disposal considerations

| | |
|-------------------------------|---|
| Disposal instructions | This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Dispose in accordance with all applicable regulations. |
| Hazardous waste code | Not regulated. |
| Contaminated packaging | Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied. |

14. Transport information

| | |
|-------------|-----------------------------------|
| DOT | Not regulated as dangerous goods. |
| IATA | Not regulated as dangerous goods. |
| IMDG | Not regulated as dangerous goods. |

15. Regulatory information

| | |
|---|--|
| US federal regulations | This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200. |
| TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D) | Not regulated. |
| SARA 304 Emergency release notification | Not regulated. |
| OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052) | Not regulated. |
| CERCLA Hazardous Substance List (40 CFR 302.4) | Not listed. |
| CERCLA Hazardous Substances: Reportable quantity | Not listed. |
| Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee. | |
| Other federal regulations | |
| Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List | Not regulated. |
| Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130) | Not regulated. |
| Safe Drinking Water Act (SDWA) | Not regulated. |

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Classified hazard categories Flammable (gases, aerosols, liquids, or solids)
Skin corrosion or irritation
Respiratory or skin sensitization
Specific target organ toxicity (single or repeated exposure)
Aspiration hazard

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes

SARA 313 (TRI reporting)

Not regulated.

US state regulations

US. New Jersey Worker and Community Right-to-Know Act

calcium carbonate (CAS 471-34-1)

US. Massachusetts RTK - Substance List

calcium carbonate (CAS 471-34-1)

US. Pennsylvania Worker and Community Right-to-Know Law

calcium carbonate (CAS 471-34-1)

distillates (petroleum), hydrotreated light (CAS 64742-47-8)

US. Rhode Island RTK

calcium carbonate (CAS 471-34-1)

distillates (petroleum), hydrotreated light (CAS 64742-47-8)

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 2016 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to www.P65Warnings.ca.gov.

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

distillates (petroleum), hydrotreated light (CAS 64742-47-8)

Volatile organic compounds (VOC) regulations

EPA

VOC content (40 CFR 51.100(s)) 90.1 %

Consumer products (40 CFR 59, Subpt. C) Not regulated

State

Consumer products Not regulated

VOC content (CA) 45.1 %

VOC content (OTC) 45.1 %

International Inventories

| Country(s) or region | Inventory name | On inventory (yes/no)* |
|----------------------|--|------------------------|
| Australia | Australian Inventory of Chemical Substances (AICS) | Yes |
| Canada | Domestic Substances List (DSL) | Yes |
| Canada | Non-Domestic Substances List (NDSL) | No |
| China | Inventory of Existing Chemical Substances in China (IECSC) | Yes |
| Europe | European Inventory of Existing Commercial Chemical Substances (EINECS) | Yes |
| Europe | European List of Notified Chemical Substances (ELINCS) | No |
| Japan | Inventory of Existing and New Chemical Substances (ENCS) | No |
| Korea | Existing Chemicals List (ECL) | Yes |
| New Zealand | New Zealand Inventory | Yes |

| Country(s) or region | Inventory name | On inventory (yes/no)* |
|-----------------------------|---|------------------------|
| Philippines | Philippine Inventory of Chemicals and Chemical Substances (PICCS) | Yes |
| Taiwan | Taiwan Chemical Substance Inventory (TCSI) | No |
| United States & Puerto Rico | Toxic Substances Control Act (TSCA) Inventory | Yes |

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)
A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

| | |
|-----------------------------|--|
| Issue date | 04-22-2019 |
| Prepared by | Allison Yoon |
| Version # | 01 |
| Further information | CRC # 559A/1002577 |
| Disclaimer | The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc.. |
| Revision information | Hazard(s) identification: Prevention |