



SAFETY DATA SHEET

1. Identification

Product identifier Natural Degreaser™ Citrus-Based Degreaser

Other means of identification

Product code 14007, 14008

Recommended use General purpose degreaser

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Manufactured or sold by:

Company name CRC Industries, Inc.

Address 885 Louis Dr.
Warminster, PA 18974 US

Telephone

General Information 215-674-4300

Technical Assistance 800-521-3168

Customer Service 800-272-4620

24-Hour Emergency (CHEMTREC) 800-424-9300 (US)
703-527-3887 (International)

Website www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Flammable liquids	Category 4
Health hazards	Acute toxicity, inhalation	Category 4
	Skin corrosion/irritation	Category 2
	Sensitization, skin	Category 1
	Specific target organ toxicity, single exposure	Category 3 narcotic effects
	Aspiration hazard	Category 1
Environmental hazards	Hazardous to the aquatic environment, acute hazard	Category 2
	Hazardous to the aquatic environment, long-term hazard	Category 3
OSHA defined hazards	Not classified.	

Label elements



Signal word Danger

Hazard statement Combustible liquid. May be fatal if swallowed and enters airways. Causes skin irritation. May cause an allergic skin reaction. Harmful if inhaled. May cause drowsiness or dizziness. Toxic to aquatic life. Harmful to aquatic life with long lasting effects.

Precautionary statement

Prevention Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing mist or vapor. Wash thoroughly after handling. Contaminated work clothing must not be allowed out of the workplace. Wear protective gloves/eye protection/face protection. Avoid release to the environment.

Response	If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting. If on skin: Wash with plenty of water. If skin irritation or rash occurs: Get medical attention. Take off contaminated clothing and wash before reuse. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell. In case of fire: Do not use water jet as an extinguisher, as this will spread the fire.
Storage	Keep cool. Store in a well-ventilated place. Keep container tightly closed. Store locked up.
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	16% of the mixture consists of component(s) of unknown acute inhalation toxicity.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Dipropylene glycol monomethyl ether acetate		88917-22-0	50 - 60
Distillates (petroleum), hydrotreated light		64742-47-8	30 - 40
Soybean oil, Methyl ester		67784-80-9	10 - 20
d-Limonene		5989-27-5	1 - 3
Dipentene		68956-56-9	< 1

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Oxygen or artificial respiration if needed. Call a POISON CENTER or doctor/physician if you feel unwell.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water. In case of eczema or other skin disorders: Seek medical attention and take along these instructions. Wash contaminated clothing before reuse.
Eye contact	Rinse with water. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	Diarrhea. May cause drowsiness and dizziness. Headache. Nausea, vomiting. Irritation of eyes and mucous membranes. Irritation of nose and throat. Aspiration may cause pulmonary edema and pneumonitis. Rash. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Dermatitis.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim warm. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Wash contaminated clothing before reuse.

5. Fire-fighting measures

Suitable extinguishing media	Alcohol resistant foam. Water fog. Dry chemical powder. Dry chemicals. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	The product is combustible, and heating may generate vapors which may form explosive vapor/air mixtures. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire-fighting equipment/instructions	In case of fire and/or explosion do not breathe fumes. Move containers from fire area if you can do so without risk. Cool containers exposed to heat with water spray and remove container, if no risk is involved.
General fire hazards	Combustible liquid.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Wear appropriate protective equipment and clothing during clean-up. Avoid inhalation of vapors and spray mists. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.

Methods and materials for containment and cleaning up

Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. This material is classified as a water pollutant under the Clean Water Act and should be prevented from contaminating soil or from entering sewage and drainage systems which lead to waterways.

Large Spills: Stop the flow of material, if this is without risk. Use water spray to reduce vapors or divert vapor cloud drift. Dike the spilled material, where this is possible. Cover with plastic sheet to prevent spreading. Use a non-combustible material like vermiculite, sand or earth to soak up the product and place into a container for later disposal. Following product recovery, flush area with water.

Small Spills: Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Clean surface thoroughly to remove residual contamination.

Environmental precautions

Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.

Avoid release to the environment. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground. Inform appropriate managerial or supervisory personnel of all environmental releases.

7. Handling and storage

Precautions for safe handling

Keep away from open flames, hot surfaces and sources of ignition. When using do not smoke. Avoid breathing vapor. Avoid contact with eyes, skin, and clothing. Avoid prolonged or repeated contact with skin. Use only outdoors or in a well-ventilated area. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, please see the product label.

Conditions for safe storage, including any incompatibilities

Keep away from heat and sources of ignition. Store in a cool, dry place out of direct sunlight. Store in original tightly closed container. Store in a well-ventilated place. Keep in an area equipped with sprinklers. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Distillates (petroleum), hydrotreated light (CAS 64742-47-8)	TWA	100 mg/m3

US. AIHA Workplace Environmental Exposure Level (WEEL) Guides

Components	Type	Value
d-Limonene (CAS 5989-27-5)	TWA	165.5 mg/m3
		30 ppm

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower must be available when handling this product.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection Wear protective gloves such as: Nitrile. Neoprene.

Other Wear appropriate chemical resistant clothing.

Respiratory protection	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
General hygiene considerations	When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Contaminated work clothing should not be allowed out of the workplace.

9. Physical and chemical properties

Appearance

Physical state	Liquid.
Form	Liquid.
Color	Clear.
Odor	Citrus.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	-139.9 °F (-95.5 °C) estimated
Initial boiling point and boiling range	304 °F (151.1 °C) estimated
Flash point	172 °F (77.8 °C) Tag Closed Cup
Evaporation rate	Slow.
Flammability (solid, gas)	Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%)	0.6 % estimated
Flammability limit - upper (%)	5.5 % estimated
Vapor pressure	0.4 hPa estimated
Vapor density	> 1 (air = 1)
Relative density	0.88
Solubility (water)	Slightly soluble.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	456.8 °F (236 °C) estimated
Decomposition temperature	Not available.
Viscosity (kinematic)	Not available.
Percent volatile	100 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Avoid heat, sparks, open flames and other ignition sources. Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	Carbon oxides.

11. Toxicological information

Information on likely routes of exposure

Ingestion	Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.
------------------	--

Inhalation	Harmful if inhaled. May cause drowsiness and dizziness. Headache. Nausea, vomiting.
Skin contact	Causes skin irritation. May cause an allergic skin reaction.
Eye contact	Direct contact with eyes may cause temporary irritation.
Symptoms related to the physical, chemical and toxicological characteristics	Diarrhea. May cause drowsiness and dizziness. Headache. Nausea, vomiting. Irritation of nose and throat. Aspiration may cause pulmonary edema and pneumonitis. Rash. Irritation of eyes and mucous membranes. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Dermatitis.

Information on toxicological effects

Acute toxicity	May be fatal if swallowed and enters airways. Harmful if inhaled. Narcotic effects. May cause an allergic skin reaction.
-----------------------	--

Product	Species	Test Results
Natural Degreaser™ Citrus-Based Degreaser		
Acute		
<i>Dermal</i>		
LD50	Rabbit	2072.5388 mg/kg estimated
<i>Inhalation</i>		
LC50	Rat	6.5315 mg/l, 4 Hours estimated
<i>Oral</i>		
LD50	Rat	5181.3472 mg/kg estimated

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Causes skin irritation.
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.
Respiratory sensitization	Not available.
Skin sensitization	May cause an allergic skin reaction.
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
IARC Monographs. Overall Evaluation of Carcinogenicity	
d-Limonene (CAS 5989-27-5)	3 Not classifiable as to carcinogenicity to humans.
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	May cause drowsiness and dizziness.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	May be fatal if swallowed and enters airways. If aspirated into lungs during swallowing or vomiting, may cause chemical pneumonia, pulmonary injury or death.

12. Ecological information

Ecotoxicity		Toxic to aquatic life. Harmful to aquatic life with long lasting effects.	
Product	Species		Test Results
Natural Degreaser™ Citrus-Based Degreaser			
Aquatic			
Crustacea	EC50	Daphnia	2651.4287 mg/l, 48 hours estimated
Acute			
Fish	LC50	Fish	6.3146 mg/l, 96 hours estimated
Components	Species		Test Results
Dipropylene glycol monomethyl ether acetate (CAS 88917-22-0)			
Aquatic			
Acute			
Crustacea	LC50	Water flea (Daphnia magna)	2701 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas)	151 mg/l, 96 hours

Components		Species	Test Results
		Rainbow trout,donaldson trout (Oncorhynchus mykiss)	111 mg/l, 96 hours
Distillates (petroleum), hydrotreated light (CAS 64742-47-8)			
Aquatic			
<i>Acute</i>			
Fish	LC50	Bluegill (Lepomis macrochirus)	2.2 mg/l, 96 hours
d-Limonene (CAS 5989-27-5)			
Aquatic			
Crustacea	EC50	Water flea (Daphnia pulex)	69.6 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas)	0.619 - 0.796 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential No data available.

Partition coefficient n-octanol / water (log Kow)

Dipropylene glycol monomethyl ether acetate 0.61 OECD 107

d-Limonene 4.232

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal of waste from residues / unused products This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.

Hazardous waste code Not regulated.

Contaminated packaging Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
All components are on the U.S. EPA TSCA Inventory List.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

Not listed.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Section 311/312 Hazard categories
Immediate Hazard - Yes
Delayed Hazard - No
Fire Hazard - Yes
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance No

US state regulations

US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)

Not listed.

US. New Jersey Worker and Community Right-to-Know Act

Distillates (petroleum), hydrotreated light (CAS 64742-47-8)

US. Massachusetts RTK - Substance List

None.

US. Pennsylvania Worker and Community Right-to-Know Law

Distillates (petroleum), hydrotreated light (CAS 64742-47-8)

US. Rhode Island RTK

None.

US. California Proposition 65

WARNING: This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

US - California Proposition 65 - CRT: Listed date/Developmental toxin

Methanol (CAS 67-56-1)

Listed: March 16, 2012

Volatile organic compounds (VOC) regulations

EPA

VOC content (40 CFR 51.100(s)) 100 %

Consumer products (40 CFR 59, Subpt. C) Not regulated

State

Consumer products This product is regulated as a General Purpose Degreaser (non-aerosol). This product is not compliant to be sold for use in California. This product is compliant in all other states.

VOC content (CA) 4 %

VOC content (OTC) 4 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	Yes
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes

Country(s) or region	Inventory name	On inventory (yes/no)*
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)
A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	12-01-2014
Prepared by	Allison Cho
Version #	01
Further information	CRC # 695
HMIS® ratings	Health: 1 Flammability: 2 Physical hazard: 0 Personal protection: B
NFPA ratings	Health: 1 Flammability: 2 Instability: 0
NFPA ratings	



Disclaimer	CRC cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC Industries' knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries.
------------	--