



SAFETY DATA SHEET

1. Identification

Product identifier	Water Based Silicone
Other means of identification	
Product code	03035
Recommended use	Silicone-based multi-purpose lubricant
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
Manufactured or sold by:	
Company name	CRC Industries, Inc.
Address	885 Louis Dr. Warminster, PA 18974 US
Telephone	
General Information	215-674-4300
Technical Assistance	800-521-3168
Customer Service	800-272-4620
24-Hour Emergency (CHEMTREC)	800-424-9300 (US) 703-527-3887 (International)
Website	www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Gases under pressure	Liquefied gas
Health hazards	Not classified.	
Environmental hazards	Not classified.	
OSHA defined hazards	Not classified.	

Label elements



Signal word	Warning
Hazard statement	Contains gas under pressure; may explode if heated.
Precautionary statement	
Prevention	Observe good industrial hygiene practices. Do not puncture or incinerate container. Do not expose to heat or store at temperatures above 49°C/120°F. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area.
Response	Wash hands after handling.
Storage	Protect from sunlight. Store in a well-ventilated place. Exposure to high temperature may cause can to burst.
Disposal	Dispose of waste and residues in accordance with local authority requirements.
Hazard(s) not otherwise classified (HNOC)	None known.

Supplemental information

When heated to temperature above 300°F/150°C in the presence of air, product may form formaldehyde vapors.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Water		7732-18-5	70 - 80
Liquefied Petroleum Gas		68476-86-8	10 - 20
White mineral oil (petroleum)		8042-47-5	10 - 20

Chemical name	Common name and synonyms	CAS number	%
Polydimethylsiloxane		63148-62-9	1 - 3
Ammonia		7664-41-7	< 0.2
Sodium nitrite		7632-00-0	< 0.2

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	If symptoms develop move victim to fresh air. Get medical attention if symptoms persist.
Skin contact	Rinse skin with water/shower. Get medical attention if irritation develops and persists.
Eye contact	Rinse with water. Get medical attention if irritation develops and persists.
Ingestion	In the unlikely event of swallowing contact a physician or poison control center. Rinse mouth. Do not induce vomiting without advice from poison control center. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	Direct contact with eyes may cause temporary irritation.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Water. Foam. Dry chemicals. Carbon dioxide (CO ₂).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	Contents under pressure.
Special protective equipment and precautions for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Fire-fighting equipment/instructions	In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Cool containers exposed to heat with water spray and remove container, if no risk is involved. Containers should be cooled with water to prevent vapor pressure build up. In the event of fire, cool tanks with water spray.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Wear appropriate personal protective equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. This product is miscible in water. Stop the flow of material, if this is without risk. Dike far ahead of spill for later disposal. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. Prevent entry into waterways, sewer, basements or confined areas. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling	Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Avoid contact with eyes. Avoid prolonged or repeated contact with skin. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Observe good industrial hygiene practices. For product usage instructions, please see the product label.
Conditions for safe storage, including any incompatibilities	Level 1 Aerosol. Contents under pressure. Do not expose to heat or store at temperatures above 120°F/49°C as can may burst. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. Store in a well-ventilated place. Store away from incompatible materials (see Section 10 of the SDS). Keep out of the reach of children.

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value	Form
Ammonia (CAS 7664-41-7)	PEL	35 mg/m3 50 ppm	Mist.
White mineral oil (petroleum) (CAS 8042-47-5)	PEL	5 mg/m3	

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Ammonia (CAS 7664-41-7)	STEL	35 ppm	Inhalable fraction.
	TWA	25 ppm	
White mineral oil (petroleum) (CAS 8042-47-5)	TWA	5 mg/m3	

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value	Form
Ammonia (CAS 7664-41-7)	STEL	27 mg/m3 35 ppm	Mist.
	TWA	18 mg/m3 25 ppm	
White mineral oil (petroleum) (CAS 8042-47-5)	STEL	10 mg/m3	
	TWA	5 mg/m3	Mist.

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection Wear protective gloves such as: Butyl rubber. Neoprene.

Other Wear appropriate chemical resistant clothing.

Respiratory protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. Air monitoring is needed to determine actual employee exposure levels.

Thermal hazards Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state Liquid.

Form Aerosol.

Color Creamy white.

Odor Mild. Mineral oil.

Odor threshold Not available.

pH 9.7

Melting point/freezing point 32 °F (0 °C) estimated

Initial boiling point and boiling range 212 °F (100 °C) estimated

Flash point None (Tag Closed Cup)

Evaporation rate Slow.

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%)	16 % estimated
Flammability limit - upper (%)	25 % estimated
Vapor pressure	521.3 hPa estimated
Vapor density	Not available.
Relative density	0.94 estimated
Solubility (water)	Dispersible.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	500 °F (260 °C) estimated
Decomposition temperature	Not available.
Viscosity (kinematic)	Not available.
Percent volatile	97.2 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Heat, flames and sparks. When heated to temperature above 300°F/150°C in the presence of air, product may form formaldehyde vapors. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	Carbon oxides. Sulfur oxides. Nitrogen oxides (NOx). Silica. Formaldehyde.

11. Toxicological information**Information on likely routes of exposure**

Ingestion	Expected to be a low ingestion hazard. If swallowed, mild irritation to mouth, throat and other tissues of gastrointestinal system may result.
Inhalation	Prolonged or excessive inhalation may cause respiratory tract irritation.
Skin contact	Frequent or prolonged contact may defat and dry the skin, leading to discomfort and dermatitis.
Eye contact	Direct contact with eyes may cause temporary irritation.
Symptoms related to the physical, chemical and toxicological characteristics	Direct contact with eyes may cause temporary irritation.

Information on toxicological effects

Acute toxicity	Expected to be a low hazard for usual industrial or commercial handling by trained personnel.
-----------------------	---

Product	Species	Test Results
Water Based Silicone		
Acute		
<i>Dermal</i>		
LD50	Rabbit	14836.7949 mg/kg estimated
<i>Inhalation</i>		
LC50	Rat	6117.9087 mg/m³, 4 hours estimated 6040.5669 mg/l, 2 Hours estimated
LCL0	Rat	1112.7361 mg/l, 1 Hours estimated
<i>Oral</i>		
LD50	Rat	24527.4473 mg/kg estimated

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Prolonged skin contact may cause temporary irritation. Repeated exposure may cause skin dryness or cracking.
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.
Respiratory sensitization	Not available.
Skin sensitization	This product is not expected to cause skin sensitization.

Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
IARC Monographs. Overall Evaluation of Carcinogenicity	
White mineral oil (petroleum) (CAS 8042-47-5)	3 Not classifiable as to carcinogenicity to humans.
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Based on available data, the classification criteria are not met.
Chronic effects	Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Product		Species	Test Results
Water Based Silicone			
Fish	LC50	Fish	515.3261 mg/l, 96 hours estimated
<i>Acute</i>			
Crustacea	EC50	Daphnia	1068.0908 ppm, 48 hours estimated
Components		Species	Test Results
Ammonia (CAS 7664-41-7)			
Aquatic			
Fish	LC50	Chinook salmon (Oncorhynchus tshawytscha)	0.43 - 0.47 mg/l, 96 hours
Polydimethylsiloxane (CAS 63148-62-9)			
Aquatic			
Fish	LC50	Channel catfish (Ictalurus punctatus)	2.36 - 4.15 mg/l, 96 hours
Sodium nitrite (CAS 7632-00-0)			
Aquatic			
Crustacea	EC50	Greasyback shrimp (Metapenaeus ensis)	16.14 - 26.61 mg/l, 48 hours
Fish	LC50	Rainbow trout, donaldson trout (Oncorhynchus mykiss)	0.19 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability	No data is available on the degradability of this product.
Bioaccumulative potential	No data available.
Partition coefficient n-octanol / water (log Kow)	
Sodium nitrite	-3.7
Mobility in soil	No data available.
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal of waste from residues / unused products	The dispensed liquid product is not a RCRA hazardous waste (See 40 CFR Part 261.20 - 261.33). Empty container can be recycled. Consult authorities before disposal. Contents under pressure. Do not puncture, incinerate or crush. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.
Hazardous waste code	Not regulated.
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT	
UN number	UN1950
UN proper shipping name	Aerosols, non-flammable, Limited Quantity

Transport hazard class(es)	
Class	2.2
Subsidiary risk	-
Label(s)	2.2
Packing group	Not applicable.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Packaging exceptions	306
Packaging non bulk	None
Packaging bulk	None

IATA

UN number	UN1950
UN proper shipping name	Aerosols, non-flammable, Limited Quantity
Transport hazard class(es)	
Class	2.2
Subsidiary risk	-
Packing group	Not applicable.
Environmental hazards	No.
ERG Code	2L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Other information	
Passenger and cargo aircraft	Allowed.
Cargo aircraft only	Allowed.

IMDG

UN number	UN1950
UN proper shipping name	AEROSOLS, LIMITED QUANTITY
Transport hazard class(es)	
Class	2
Subsidiary risk	-
Packing group	Not applicable.
Environmental hazards	
Marine pollutant	No.
EmS	Not available.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

15. Regulatory information

US federal regulations	This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200. All components are on the U.S. EPA TSCA Inventory List.
TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)	
Sodium nitrite (CAS 7632-00-0)	1.0 % One-Time Export Notification only.
SARA 304 Emergency release notification	
Not regulated.	
US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)	
Not listed.	
US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance	
Not listed.	
CERCLA Hazardous Substance List (40 CFR 302.4)	
Not listed.	
CERCLA Hazardous Substances: Reportable quantity	
Not listed.	
Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.	
Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List	
Not regulated.	
Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)	
Not regulated.	
Safe Drinking Water Act (SDWA)	Not regulated.
Food and Drug Administration (FDA)	Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Section 311/312 Immediate Hazard - No
Hazard categories Delayed Hazard - No
Fire Hazard - No
Pressure Hazard - Yes
Reactivity Hazard - No

SARA 302 Extremely hazardous substance No

US state regulations**US. New Jersey RTK - Substances: Listed substance**

Ammonia (CAS 7664-41-7)
Sodium nitrite (CAS 7632-00-0)

US. Massachusetts RTK - Substance List

White mineral oil (petroleum) (CAS 8042-47-5)

US. Pennsylvania RTK - Hazardous Substances

Ammonia (CAS 7664-41-7)
Sodium nitrite (CAS 7632-00-0)
White mineral oil (petroleum) (CAS 8042-47-5)

US. Rhode Island RTK

Ammonia (CAS 7664-41-7)
Sodium nitrite (CAS 7632-00-0)

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

Volatile organic compounds (VOC) regulations**EPA**

VOC content (40 CFR 51.100(s)) 23.6 %

Consumer products (40 CFR 59, Subpt. C) Not regulated

State

Consumer products This product is regulated as a Silicone Based Multi-Purpose Lubricant. This product is compliant for use in all 50 states.

VOC content (CA) 10.1 %

VOC content (OTC) 10.1 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 01-30-2014
Prepared by Allison Cho
Version # 01
Further information CRC # 696A

HMIS® ratings

Health: 1
Flammability: 1
Physical hazard: 0
Personal protection: B

NFPA ratings

Health: 1
Flammability: 1
Instability: 0

Disclaimer

The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC Industries' knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries.