





Note that all unique customer requirements (i.e tolerance) need to be verified thru Alfa Laval.



HEATING SURFACE ft²
 NETWEIGHT 46.8 lb
 OPERATING WEIGHT lb
 PLATE MATERIAL ALLOY 316
 PLATE GROUPING 1*14H/1*15H

T1 T2 T3 T4 locations on back side correspond to S1 S2 S3 S4 on front side

ALL DIMENSIONS IN INCHES

SIDE	MEDIA	INLET	TEMP.	OUTLET	TEMP.	FLOW RATE	PRESSURE DROP	LIQUID VOL.
1	Water	S1	°F	S2	°F	lb/h	psi	0.13 ft ³
2	Water	S3	°F	S4	°F	lb/h	psi	0.12 ft ³

PRESSURE VESSEL APPROVAL

PED/CRN



AlfaNova 76-30H (3287000887)

www.alfalaval.com

CUSTOMER NAME / REF. NO.

TOTAL LENGTH 6.3 in
 TOTAL WIDTH 7.5 in
 TOTAL HEIGHT 24.3 in

COMPANY / REF.
 Alfa Laval Nordic AB
 Alfa Laval Inc.



8/25/2021
 REV 0