



SAFETY DATA SHEET

1. Identification

Product identifier Air Brake Anti-Freeze & Conditioner

Other means of identification

Product Code No. 05555 (Item# 1003823)

Recommended use Air brake anti-freeze

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Manufactured or sold by:

Company name CRC Industries, Inc.

Address 885 Louis Dr.
Warminster, PA 18974 US

Telephone

General Information 215-674-4300

Technical Assistance 800-521-3168

Customer Service 800-272-4620

24-Hour Emergency 800-424-9300 (US)

(CHEMTREC) 703-527-3887 (International)

Website www.crcindustries.com

2. Hazard(s) identification

Physical hazards Flammable liquids Category 2

Health hazards Acute toxicity, oral Category 3

Acute toxicity, dermal Category 3

Acute toxicity, inhalation Category 3

Reproductive toxicity (fertility) Category 2

Specific target organ toxicity, single exposure Category 1 (central nervous system, eyes)

Environmental hazards Not classified.

OSHA defined hazards Not classified.

Label elements



Signal word Danger

Hazard statement Highly flammable liquid and vapor. Toxic if swallowed. Toxic in contact with skin. Toxic if inhaled. Suspected of damaging fertility. Causes damage to organs (central nervous system, eyes).

Precautionary statement

Prevention

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Keep container tightly closed. Ground/bond container and receiving equipment. Use explosion-proof electrical/ventilating/lighting equipment. Use only non-sparking tools. Take precautionary measures against static discharge. Do not breathe vapors. Use only with adequate ventilation; maintain ventilation during use and until all vapors are gone. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Wash thoroughly after handling. Do not eat, drink or smoke when using this product. Wear protective gloves/protective clothing/eye protection/face protection.

Response	If swallowed: Immediately call a poison center/doctor. Rinse mouth. If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower. Call a poison center/doctor if you feel unwell. Wash contaminated clothing before reuse. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor. If exposed: Call a poison center/doctor. In case of fire: Do not use water jet as an extinguisher, as this will spread the fire.
Storage	Keep cool. Store in a well-ventilated place. Keep container tightly closed. Store locked up.
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	Static accumulating flammable liquid can become electrostatically charged even in bonded and grounded equipment. Sparks may ignite liquid and vapor. May cause flash fire or explosion.
Supplemental information	None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
methanol		67-56-1	90 - 100

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Oxygen or artificial respiration if needed. Do not use mouth-to-mouth method if victim inhaled the substance. Induce artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Call a POISON CENTER or doctor/physician.
Skin contact	Take off immediately all contaminated clothing. Rinse skin with water/shower. Get medical advice/attention if you feel unwell. Get medical attention if irritation develops and persists. Wash contaminated clothing before reuse.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting without advice from poison control center. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs. Do not use mouth-to-mouth method if victim ingested the substance. Induce artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device.
Most important symptoms/effects, acute and delayed	Narcosis. Headache. Dizziness. Nausea, vomiting. Behavioral changes. Decrease in motor functions. Direct contact with eyes may cause temporary irritation.
Indication of immediate medical attention and special treatment needed	Methanol is metabolized to formic acid and formaldehyde. These metabolites can cause metabolic acidosis, visual disturbances and blindness. Since metabolism is required for these toxic symptoms, their onset may be delayed from 6 to 30 hours following ingestion. Ethanol competes for the same metabolic pathway and has been used to prevent methanol metabolism. Ethanol administration is indicated in symptomatic patients or at blood methanol concentrations above 20 µg/dl. Methanol is effectively removed by hemodialysis. Fomepizole (4-methylpyrazole) is an effective antagonist of alcohol dehydrogenase, and may be used as an antidote in the treatment of methanol poisoning.
General information	Provide general supportive measures and treat symptomatically. Thermal burns: Flush with water immediately. While flushing, remove clothes which do not adhere to affected area. Call an ambulance. Continue flushing during transport to hospital. Keep victim warm. Keep victim under observation. Symptoms may be delayed. Take off immediately all contaminated clothing. IF exposed or concerned: Get medical advice/attention. Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Show this safety data sheet to the doctor in attendance. Wash contaminated clothing before reuse.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Alcohol resistant foam. Carbon dioxide (CO ₂). Dry chemical powder, carbon dioxide, sand or earth may be used for small fires only.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

Specific hazards arising from the chemical	Vapors may form explosive mixtures with air. Vapors may travel considerable distance to a source of ignition and flash back. This product is a poor conductor of electricity and can become electrostatically charged. If sufficient charge is accumulated, ignition of flammable mixtures can occur. To reduce potential for static discharge, use proper bonding and grounding procedures. This liquid may accumulate static electricity when filling properly grounded containers. Static electricity accumulation may be significantly increased by the presence of small quantities of water or other contaminants. Material will float and may ignite on surface of water. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire-fighting equipment/instructions	In case of fire and/or explosion do not breathe fumes. Move containers from fire area if you can do so without risk. Use standard firefighting procedures and consider the hazards of other involved materials.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	Highly flammable liquid and vapor.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Wear appropriate protective equipment and clothing during clean-up. Do not breathe vapor. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Use appropriate containment to avoid environmental contamination. Transfer by mechanical means such as vacuum truck to a salvage tank or other suitable container for recovery or safe disposal. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. Take precautionary measures against static discharge. Use only non-sparking tools. This product is miscible in water. Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Use a non-combustible material like vermiculite, sand or earth to soak up the product and place into a container for later disposal. Following product recovery, flush area with water. Small Spills: Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid discharge into drains, water courses or onto the ground. Use appropriate containment to avoid environmental contamination.

7. Handling and storage

Precautions for safe handling	Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Do not handle, store or open near an open flame, sources of heat or sources of ignition. Protect material from direct sunlight. Explosion-proof general and local exhaust ventilation. Minimize fire risks from flammable and combustible materials (including combustible dust and static accumulating liquids) or dangerous reactions with incompatible materials. Handling operations that can promote accumulation of static charges include but are not limited to: mixing, filtering, pumping at high flow rates, splash filling, creating mists or sprays, tank and container filling, tank cleaning, sampling, gauging, switch loading, vacuum truck operations. Take precautionary measures against static discharges. All equipment used when handling the product must be grounded. Use non-sparking tools and explosion-proof equipment. Do not breathe vapor. Do not taste or swallow. Avoid contact with eyes, skin, and clothing. Avoid prolonged exposure. When using, do not eat, drink or smoke. Pregnant or breastfeeding women must not handle this product. Should be handled in closed systems, if possible. Use only outdoors or in a well-ventilated area. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Wash contaminated clothing before reuse. Observe good industrial hygiene practices. For product usage instructions, see the product label.
Conditions for safe storage, including any incompatibilities	Keep away from heat, sparks and open flame. Prevent electrostatic charge build-up by using common bonding and grounding techniques. Eliminate sources of ignition. Avoid spark promoters. Ground/bond container and equipment. These alone may be insufficient to remove static electricity. Store in a cool, dry place out of direct sunlight. Keep container tightly closed. Store in a well-ventilated place. Keep in an area equipped with sprinklers. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
methanol (CAS 67-56-1)	PEL	260 mg/m3 200 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
methanol (CAS 67-56-1)	STEL	250 ppm
	TWA	200 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
methanol (CAS 67-56-1)	STEL	325 mg/m3 250 ppm
	TWA	260 mg/m3 200 ppm

Biological limit values

ACGIH Biological Exposure Indices

Components	Value	Determinant	Specimen	Sampling Time
methanol (CAS 67-56-1)	15 mg/l	Methanol	Urine	*

* - For sampling details, please see the source document.

Exposure guidelines

US - California OELs: Skin designation

methanol (CAS 67-56-1) Can be absorbed through the skin.

US - Minnesota Haz Subs: Skin designation applies

methanol (CAS 67-56-1) Skin designation applies.

US - Tennessee OELs: Skin designation

methanol (CAS 67-56-1) Can be absorbed through the skin.

US ACGIH Threshold Limit Values: Skin designation

methanol (CAS 67-56-1) Can be absorbed through the skin.

US NIOSH Pocket Guide to Chemical Hazards: Skin designation

methanol (CAS 67-56-1) Can be absorbed through the skin.

Appropriate engineering controls

Explosion-proof general and local exhaust ventilation. Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection Wear protective gloves such as: Nitrile. Rubber.

Other

Wear appropriate chemical resistant clothing. Use of an impervious apron is recommended.

Respiratory protection

If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

When using, do not eat, drink or smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state Liquid.

Form	Liquid.
Color	Colorless.
Odor	Pungent. Alcoholic.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	-144 °F (-97.8 °C) estimated
Initial boiling point and boiling range	148.5 °F (64.7 °C) estimated
Flash point	54 °F (12.2 °C) Setaflash
Evaporation rate	Fast.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	2.6 % estimated
Flammability limit - upper (%)	36 % estimated
Vapor pressure	133.2 hPa estimated
Vapor density	1.1 (air = 1)
Relative density	0.79
Solubility(ies)	
Solubility (water)	Completely soluble.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	725 °F (385 °C) estimated
Decomposition temperature	Not available.
Percent volatile	99.9 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Avoid heat, sparks, open flames and other ignition sources. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	Carbon oxides. Formaldehyde.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Toxic if inhaled. May cause damage to organs by inhalation.
Skin contact	Toxic in contact with skin.
Eye contact	Direct contact with eyes may cause temporary irritation.
Ingestion	Toxic if swallowed. Even small amounts (30-250 ml methanol) may be fatal. Symptoms are stomach ache, nausea, vomiting, dullness, visual disorder and blindness.

Symptoms related to the physical, chemical and toxicological characteristics	Narcosis. Headache. Dizziness. Nausea, vomiting. Behavioral changes. Decrease in motor functions.
---	---

Information on toxicological effects

Acute toxicity	Toxic if inhaled. Toxic in contact with skin. Toxic if swallowed.
Skin corrosion/irritation	Prolonged skin contact may cause temporary irritation.
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.

Respiratory or skin sensitization

Respiratory sensitization Not a respiratory sensitizer.

Skin sensitization This product is not expected to cause skin sensitization.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity Not classifiable as to carcinogenicity to humans.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity Suspected of damaging fertility.

Specific target organ toxicity - single exposure Causes damage to organs (central nervous system, eyes). Even small amounts (30-250 ml methanol) may be fatal. Symptoms are stomach ache, nausea, vomiting, dullness, visual disorder and blindness.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard Not an aspiration hazard.

Chronic effects Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Components		Species	Test Results
methanol (CAS 67-56-1)			
Aquatic			
Fish	LC50	Rainbow trout,donaldson trout (Oncorhynchus mykiss)	18000 - 20000 mg/l, 96 hours
Acute			
Crustacea	EC50	Water flea (Daphnia magna)	> 10000 mg/l, 48 hours
Fish	LC50	Rainbow trout,donaldson trout (Oncorhynchus mykiss)	18000 - 20000 mg/l, 96 hours

Persistence and degradability No data is available on the degradability of any ingredients in the mixture.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)

methanol -0.77

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Hazardous waste code D001: Waste Flammable material with a flash point <140 F
F003: Waste Non-halogenated Solvent - Spent Non-halogenated Solvent

US RCRA Hazardous Waste U List: Reference

methanol (CAS 67-56-1) U154

Contaminated packaging Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

Disposal instructions This material and its container must be disposed of as hazardous waste. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Dispose in accordance with all applicable regulations.

14. Transport information

DOT

UN number UN1230

UN proper shipping name	Methanol, solution (methanol RQ = 5007 LBS)
Transport hazard class(es)	
Class	3
Subsidiary risk	-
Label(s)	3
Packing group	II
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Special provisions	IB2, T7, TP2
Packaging exceptions	150
Packaging non bulk	202
Packaging bulk	242

IATA

UN number	UN1230
UN proper shipping name	Methanol
Transport hazard class(es)	
Class	3
Subsidiary risk	6.1
Packing group	II
ERG Code	3L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Other information	
Passenger and cargo aircraft	Allowed with restrictions.
Cargo aircraft only	Allowed with restrictions.

IMDG

UN number	UN1230
UN proper shipping name	METHANOL
Transport hazard class(es)	
Class	3
Subsidiary risk	6.1
Packing group	II
Environmental hazards	
Marine pollutant	No.
EmS	F-E, S-D
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
All components are on the U.S. EPA TSCA Inventory List.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

methanol (CAS 67-56-1)

CERCLA Hazardous Substance List (40 CFR 302.4)

methanol (CAS 67-56-1) Listed.

CERCLA Hazardous Substances: Reportable quantity

methanol (CAS 67-56-1) 5000 LBS

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

methanol (CAS 67-56-1)

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.**Food and Drug Administration (FDA)** Not regulated.**Superfund Amendments and Reauthorization Act of 1986 (SARA)**

Classified hazard categories Flammable (gases, aerosols, liquids, or solids)
 Acute toxicity (any route of exposure)
 Reproductive toxicity
 Specific target organ toxicity (single or repeated exposure)
 Hazard not otherwise classified (HNOC)

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes**SARA 313 (TRI reporting)**

Chemical name	CAS number	% by wt.
methanol	67-56-1	90 - 100

US state regulations**US. New Jersey Worker and Community Right-to-Know Act**

methanol (CAS 67-56-1)

US. Massachusetts RTK - Substance List

methanol (CAS 67-56-1)

US. Pennsylvania Worker and Community Right-to-Know Law

methanol (CAS 67-56-1)

US. Rhode Island RTK

methanol (CAS 67-56-1)

California Proposition 65**WARNING:** Reproductive Harm - www.P65Warnings.ca.gov**California Proposition 65 - CRT: Listed date/Developmental toxin**

methanol (CAS 67-56-1)

Listed: March 16, 2012

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

methanol (CAS 67-56-1)

Volatile organic compounds (VOC) regulations**EPA****VOC content (40 CFR 51.100(s))** 100 %**Consumer products (40 CFR 59, Subpt. C)** Not regulated**State****Consumer products** Not regulated**VOC content (CA)** 100 %**VOC content (OTC)** 100 %**International Inventories**

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes

Country(s) or region	Inventory name	On inventory (yes/no)*
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	Yes
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Toxic Chemical Substances (TCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)
A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	03-24-2015
Revision date	04-09-2018
Prepared by	Allison Yoon
Version #	02
Further information	CRC # 620B/1002661
Disclaimer	The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..
Revision information	This document has undergone significant changes and should be reviewed in its entirety.