



SAFETY DATA SHEET

1. Identification

Product identifier Premium Fuel Injector Cleaner

Other means of identification

Product Code No. 05062 (Item# 1003677)

Recommended use Pour-in fuel additive

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Manufactured or sold by:

Company name CRC Industries, Inc.

Address 885 Louis Dr.
Warminster, PA 18974 US

Telephone

General Information 215-674-4300

Technical Assistance 800-521-3168

Customer Service 800-272-4620

24-Hour Emergency 800-424-9300 (US)

(CHEMTREC) 703-527-3887 (International)

Website www.crcindustries.com

2. Hazard(s) identification

Physical hazards Flammable liquids Category 4

Health hazards Acute toxicity, inhalation Category 4

Skin corrosion/irritation Category 2

Germ cell mutagenicity Category 2

Carcinogenicity Category 2

Aspiration hazard Category 1

Environmental hazards Hazardous to the aquatic environment, acute hazard Category 2

Hazardous to the aquatic environment, long-term hazard Category 2

OSHA defined hazards Not classified.

Label elements



Signal word Danger

Hazard statement Combustible liquid. May be fatal if swallowed and enters airways. Causes skin irritation. Harmful if inhaled. Suspected of causing genetic defects. Suspected of causing cancer. Toxic to aquatic life with long lasting effects.

Precautionary statement

Prevention Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Keep away from flames and hot surfaces-No smoking. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing vapors. Wash thoroughly after handling. Wear protective gloves/protective clothing/eye protection/face protection. Avoid release to the environment.

Response	If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting. If on skin: Wash with plenty of water. If skin irritation occurs: Get medical advice/attention. Take off contaminated clothing and wash before reuse. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell. If exposed or concerned: Get medical advice/attention. In case of fire: Do not use water jet as an extinguisher, as this will spread the fire. Collect spillage.
Storage	Store in a well-ventilated place. Keep cool. Store locked up.
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
distillates (petroleum), hydrodesulfurized middle		64742-80-9	90 - 100
hydrocarbyl amine		Proprietary	1 - 3

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Oxygen or artificial respiration if needed. Call a POISON CENTER or doctor/physician if you feel unwell.
Skin contact	Remove contaminated clothing. Rinse skin with water/shower. If skin irritation occurs: Get medical advice/attention. Wash contaminated clothing before reuse.
Eye contact	Rinse with water. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	Aspiration may cause pulmonary edema and pneumonitis. Dizziness. Direct contact with eyes may cause temporary irritation. Skin irritation. May cause redness and pain.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim warm. Keep victim under observation. Symptoms may be delayed.
General information	IF exposed or concerned: Get medical advice/attention. Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Show this safety data sheet to the doctor in attendance.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	The product is combustible, and heating may generate vapors which may form explosive vapor/air mixtures. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	In case of fire and/or explosion do not breathe fumes. Move containers from fire area if you can do so without risk.
General fire hazards	Combustible liquid.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Wear appropriate protective equipment and clothing during clean-up. Avoid inhalation of vapors and spray mists. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained.
--	---

Methods and materials for containment and cleaning up

Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. This product is miscible in water. Prevent product from entering drains.

Small Spills: Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use. Put material in suitable, covered, labeled containers.

Environmental precautions

Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage**Precautions for safe handling**

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Keep away from open flames, hot surfaces and sources of ignition. When using do not smoke. Avoid breathing vapor. Avoid contact with eyes, skin, and clothing. Avoid prolonged exposure. Should be handled in closed systems, if possible. Use only outdoors or in a well-ventilated area. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.

Conditions for safe storage, including any incompatibilities

Keep away from heat, sparks and open flame. Store in a cool, dry place out of direct sunlight. Keep container tightly closed. Store in a well-ventilated place. Keep in an area equipped with sprinklers.

8. Exposure controls/personal protection**Occupational exposure limits****US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)**

Components	Type	Value
distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)	PEL	400 mg/m3
		100 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)	TWA	5 mg/m3	Inhalable fraction.

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)	TWA	400 mg/m3
		100 ppm

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower should be available when handling this product.

Individual protection measures, such as personal protective equipment**Eye/face protection**

Wear safety glasses with side shields (or goggles).

Skin protection**Hand protection**

Wear protective gloves such as: Nitrile. Neoprene. Polyvinyl chloride (PVC).

Other

Wear appropriate chemical resistant clothing.

Respiratory protection

If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state Liquid.

Form Liquid.

Color Light amber.

Odor Petroleum.

Odor threshold Not available.

pH Not available.

Melting point/freezing point Not available.

Initial boiling point and boiling range 320 °F (160 °C) estimated

Flash point 170 °F (76.7 °C) Setaflash

Evaporation rate Moderate.

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) 0.5 % estimated

Flammability limit - upper (%) 7.5 % estimated

Vapor pressure 0.6 hPa estimated

Vapor density > 1 (air = 1)

Relative density 0.85

Solubility(ies)

Solubility (water) Negligible.

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature 494 °F (256.7 °C) estimated

Decomposition temperature Not available.

Percent volatile 98.6 % estimated

10. Stability and reactivity

Reactivity The product is stable and non-reactive under normal conditions of use, storage and transport.

Chemical stability Material is stable under normal conditions.

Possibility of hazardous reactions No dangerous reaction known under conditions of normal use.

Conditions to avoid Avoid heat, sparks, open flames and other ignition sources. Avoid temperatures exceeding the flash point. Contact with incompatible materials.

Incompatible materials Strong oxidizing agents.

Hazardous decomposition products Carbon oxides. Hydrocarbon fumes and smoke.

11. Toxicological information

Information on likely routes of exposure

Inhalation Harmful if inhaled.

Skin contact Causes skin irritation.

Eye contact Direct contact with eyes may cause temporary irritation.

Ingestion Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.

Symptoms related to the physical, chemical and toxicological characteristics

Aspiration may cause pulmonary edema and pneumonitis. Dizziness. Skin irritation. May cause redness and pain.

Information on toxicological effects**Acute toxicity**

May be fatal if swallowed and enters airways. Harmful if inhaled.

Components**Species****Test Results**

distillates (petroleum), hydrosulfurized middle (CAS 64742-80-9)

Acute**Dermal**

LD50

Rabbit

> 2000 mg/kg

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation

Causes skin irritation.

Serious eye damage/eye irritation

Direct contact with eyes may cause temporary irritation.

Respiratory or skin sensitization**Respiratory sensitization**

Not a respiratory sensitizer.

Skin sensitization

This product is not expected to cause skin sensitization.

Germ cell mutagenicity

Suspected of causing genetic defects.

Carcinogenicity

Suspected of causing cancer.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity

This product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity - single exposure

Not classified.

Specific target organ toxicity - repeated exposure

Not classified.

Aspiration hazard

May be fatal if swallowed and enters airways. If aspirated into lungs during swallowing or vomiting, may cause chemical pneumonia, pulmonary injury or death.

Chronic effects

Prolonged inhalation may be harmful.

12. Ecological information**Ecotoxicity**

Toxic to aquatic life with long lasting effects.

Components**Species****Test Results**

distillates (petroleum), hydrosulfurized middle (CAS 64742-80-9)

Aquatic

Fish

LC50

Rainbow trout, donaldson trout
(Oncorhynchus mykiss)

8.8 mg/l, 96 hours

8.8 mg/l, 96 hours

Acute

Crustacea

EC50

Water flea (Daphnia magna)

1.09 - 3.4 mg/l, 48 hours

hydrocarbyl amine

Acute

Other

EC50

Activated sludge, industrial

> 1000 mg/l, 2.4 hours

Aquatic**Acute**

Algae

EC50

Green algae (Selenastrum
capricornutum)

> 450 mg/l, 96 hours

Crustacea

EC50

Water flea (Daphnia magna)

> 100 mg/l, 48 hours

Components	Species	Test Results
Fish	LC50	Fathead minnow (Pimephales promelas) 31 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability

Bioaccumulative potential

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.

Hazardous waste code Not regulated.

Contaminated packaging Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Classified hazard categories	Flammable (gases, aerosols, liquids, or solids) Acute toxicity (any route of exposure) Skin corrosion or irritation Germ cell mutagenicity Carcinogenicity Aspiration hazard
-------------------------------------	---

SARA 302 Extremely hazardous substance

Not listed.

SARA 313 (TRI reporting)

Not regulated.

US state regulations**US. New Jersey Worker and Community Right-to-Know Act**

distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)

US. Massachusetts RTK - Substance List

distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)

US. Pennsylvania Worker and Community Right-to-Know Law

distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)

US. Rhode Island RTK

distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)

California Proposition 65**WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov**California Proposition 65 - CRT: Listed date/Carcinogenic substance**

benzene (CAS 71-43-2)	Listed: February 27, 1987
naphthalene (CAS 91-20-3)	Listed: April 19, 2002

California Proposition 65 - CRT: Listed date/Developmental toxin

benzene (CAS 71-43-2)	Listed: December 26, 1997
-----------------------	---------------------------

California Proposition 65 - CRT: Listed date/Male reproductive toxin

benzene (CAS 71-43-2)	Listed: December 26, 1997
-----------------------	---------------------------

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)

Volatile organic compounds (VOC) regulations**EPA**

VOC content (40 CFR 51.100(s))	97.9 %
Consumer products (40 CFR 59, Subpt. C)	Not regulated

State

Consumer products	Not regulated
VOC content (CA)	97.9 %
VOC content (OTC)	97.9 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	No
Canada	Non-Domestic Substances List (NDSL)	Yes
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No

Country(s) or region	Inventory name	On inventory (yes/no)*
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Toxic Chemical Substances (TCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)
A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	05-21-2015
Revision date	01-19-2018
Prepared by	Allison Yoon
Version #	02
Further information	CRC # 593E/1002619
HMIS® ratings	Health: 2* Flammability: 2 Physical hazard: 0 Personal protection: B
NFPA ratings	Health: 2 Flammability: 2 Instability: 0

NFPA ratings



Disclaimer

The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..

Revision information

This document has undergone significant changes and should be reviewed in its entirety.