



Technical Data

| | |
|----------------------|-----------------------|
| Color | Natural |
| Sizes Available | S-XL |
| Packaging | Bulk Pack |
| Packed | 10 Dozen/Case |
| Case Dimensions (in) | 25.98 x 10.51 x 10.51 |
| Case Weight (lbs) | 35.27 |
| Country of Origin | India |
| Hide | Top Grain Cowhide |
| Grade | Regular |
| Cuff | Slip-on |
| Stitching | Nylon |
| Thumb | Keystone |
| Construction | Cut-and-Sewn |
| Certifications | Chromium VI Free |
| Product Circularity | -- |

PIP®

Regular Grade Top Grain Leather Drivers Glove with Split Cowhide Back - Keystone Thumb

- Top Grain/Shoulder Split Cowhide leather construction provides comfort, durability, excellent abrasion resistance, and breathability
- Top Grain leather palm is smooth, provides durability and dexterity
- Shoulder Split Cowhide leather back provides comfort, durability, excellent abrasion resistance, and breathability
- Shoulder Split Cowhide leather back makes this glove more economical than full top grain construction
- Drivers gloves feature slip-on styling to provide good fit and comfort
- Keystone thumb is ergonomic, reduces hand fatigue, offers superior dexterity and durability

Applications

- General Applications
- Construction Applications
- Roofing
- Farming
- Utility Work
- Roping

Performance Data

| | |
|-----------------------|----|
| ANSI Cut Level (2016) | -- |
| ANSI Puncture Level | -- |
| EN 388 | -- |

Care Instructions



Do Not Wash



SKU Information

| SKU | COLOR | SIZE | UPC | UPC (INNER) | UPC (CASE) |
|-------------|---------|------|--------------|----------------|----------------|
| 68-161SB/S | Natural | S | 616314015489 | 01616314015489 | 02616314015489 |
| 68-161SB/M | Natural | M | 616314015496 | 01616314015496 | 02616314015496 |
| 68-161SB/L | Natural | L | 616314015502 | 01616314015502 | 02616314015502 |
| 68-161SB/XL | Natural | XL | 616314015519 | 01616314015519 | 02616314015519 |