



NOVAX®

Class 00 Rubber Insulating Glove with Straight Cuff - 11"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection

Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

Technical Data

Color	Black
Sizes Available	6-12
Packaging	Boxed
Packed	12 Pair/Case
Case Dimensions (in)	16.93 x 16.93 x 12.80
Case Weight (lbs)	9.72
Country of Origin	Malaysia
Material	Rubber
Length	11"
Cuff	Straight
Cuff Color	Black
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

Performance Data

Electrical Class	Class 00
------------------	----------

Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
150-00-11/6	Black	6	616314770104	10616314770101	20616314770108
150-00-11/7	Black	7	616314051173	01616314051172	02616314051171
150-00-11/8	Black	8	616314050794	01616314050793	02616314050792
150-00-11/8.5	Black	8.5	616314705939	10616314705936	20616314705933
150-00-11/9	Black	9	616314050800	01616314050809	02616314050808
150-00-11/9.5	Black	9.5	616314704413	10616314704410	20616314704417
150-00-11/10	Black	10	616314050817	01616314050816	02616314050815
150-00-11/10.5	Black	10.5	616314702358	10616314702355	20616314702352
150-00-11/11	Black	11	616314050824	01616314050823	02616314050822
150-00-11/12	Black	12	616314058721	01616314058546	02616314058545