





Note that all unique customer requirements (i.e tolerance) need to be verified thru Alfa Laval.



HEATING SURFACE  
 NETWEIGHT 1.23 kg  
 OPERATING WEIGHT  
 PLATE MATERIAL Alloy 316  
 PLATE GROUPING 1\*8H/1\*8H

T1 T2 T3 T4 locations on back side correspond to S1 S2 S3 S4 on front side

ALL DIMENSIONS IN MILLIMETERS

| SIDE | MEDIA | INLET | TEMP. | OUTLET | TEMP. | FLOW RATE | PRESSURE DROP | LIQUID VOL.          |
|------|-------|-------|-------|--------|-------|-----------|---------------|----------------------|
| 1    |       |       |       |        |       |           |               | 0.22 dm <sup>3</sup> |
| 2    |       |       |       |        |       |           |               | 0.22 dm <sup>3</sup> |

PRESSURE VESSEL APPROVAL

UL/CRN

CBH16-17H T05 (3287119754)

[www.alfalaval.com](http://www.alfalaval.com)

CUSTOMER NAME / REF. NO.

TOTAL LENGTH 62.7 mm  
 TOTAL WIDTH 73.5 mm  
 TOTAL HEIGHT 209.5 mm

COMPANY / REF.

8/24/2017  
 REV 0