



NOVAX®

Class 2 Rubber Insulating Glove with Straight Cuff - 14"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection

Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

Technical Data

Color	Black
Sizes Available	7-12
Packaging	Boxed
Packed	12 Pair/Case
Case Dimensions (in)	16.93 x 16.93 x 19.80
Case Weight (lbs)	21.12
Country of Origin	Malaysia
Material	Rubber
Length	14"
Cuff	Straight
Cuff Color	Black
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

Performance Data

Electrical Class	Class 2
------------------	---------

Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
150-2-14/7	Black	7	616314051203	01616314051202	02616314051201
150-2-14/8	Black	8	616314050916	01616314050915	02616314050914
150-2-14/9	Black	9	616314050923	01616314050922	02616314050921
150-2-14/10	Black	10	616314050930	01616314050939	02616314050938
150-2-14/11	Black	11	616314050947	01616314050946	02616314050945
150-2-14/12	Black	12	616314057922	01616314057884	02616314057883