



SAFETY DATA SHEET

1. Identification

Product identifier Diesel 1-Tank Power Renew®

Other means of identification

Product Code No. 05816 (Item# 1003862)

Recommended use Diesel fuel additive

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Manufactured or sold by:

Company name CRC Industries, Inc.
Address 885 Louis Dr.
Warminster, PA 18974 US

Telephone

General Information 215-674-4300
Technical Assistance 800-521-3168
Customer Service 800-272-4620
24-Hour Emergency 800-424-9300 (US)
(CHEMTREC) 703-527-3887 (International)
Website www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Flammable liquids	Category 4
Health hazards	Acute toxicity, inhalation	Category 4
	Skin corrosion/irritation	Category 2
	Serious eye damage/eye irritation	Category 2A
	Germ cell mutagenicity	Category 2
	Carcinogenicity	Category 2
	Aspiration hazard	Category 1
Environmental hazards	Hazardous to the aquatic environment, acute hazard	Category 2
	Hazardous to the aquatic environment, long-term hazard	Category 2
OSHA defined hazards	Not classified.	
Label elements		



Signal word Danger

Hazard statement Combustible liquid. May be fatal if swallowed and enters airways. Causes skin irritation. Causes serious eye irritation. Harmful if inhaled. Suspected of causing genetic defects. Suspected of causing cancer. Toxic to aquatic life. Toxic to aquatic life with long lasting effects.

Precautionary statement

Prevention

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Keep away from flames and hot surfaces-No smoking. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing vapors. Wash thoroughly after handling. Wear protective gloves/protective clothing/eye protection/face protection. Avoid release to the environment.

Response	If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting. If on skin: Wash with plenty of water. If skin irritation occurs: Get medical advice/attention. Take off contaminated clothing and wash before reuse. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. If exposed or concerned: Get medical advice/attention. In case of fire: Do not use water jet as an extinguisher, as this will spread the fire. Collect spillage.
Storage	Store in a well-ventilated place. Keep cool. Store locked up.
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
distillates (petroleum), hydrosulfurized middle		64742-80-9	40 - 50
2-ethylhexyl nitrate		27247-96-7	20 - 30
naphtha (petroleum), hydrotreated heavy		64742-48-9	5 - 10
2-ethylhexanol		104-76-7	3 - 5
distillates (petroleum), hydrotreated heavy paraffinic		64742-54-7	1 - 3

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Oxygen or artificial respiration if needed. Call a POISON CENTER or doctor/physician if you feel unwell.
Skin contact	Remove contaminated clothing. Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention. Wash contaminated clothing before reuse.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	Aspiration may cause pulmonary edema and pneumonitis. Dizziness. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause redness and pain.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim warm. Keep victim under observation. Symptoms may be delayed.
General information	IF exposed or concerned: Get medical advice/attention. Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Show this safety data sheet to the doctor in attendance.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	The product is combustible, and heating may generate vapors which may form explosive vapor/air mixtures. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	In case of fire and/or explosion do not breathe fumes. Move containers from fire area if you can do so without risk.
General fire hazards	Combustible liquid.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Wear appropriate protective equipment and clothing during clean-up. Avoid inhalation of vapors and spray mists. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. The product is immiscible with water and will spread on the water surface. Prevent product from entering drains. Small Spills: Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. Never return spills to original containers for re-use. Put material in suitable, covered, labeled containers. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling	Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Keep away from open flames, hot surfaces and sources of ignition. When using do not smoke. Avoid inhalation of vapors and spray mists. Avoid contact with eyes, skin, and clothing. Avoid prolonged exposure. Should be handled in closed systems, if possible. Use only outdoors or in a well-ventilated area. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.
Conditions for safe storage, including any incompatibilities	Keep away from heat, sparks and open flame. Store in a cool, dry place out of direct sunlight. Store in original tightly closed container. Store in a well-ventilated place. Keep in an area equipped with sprinklers. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

U.S. - OSHA Components

distillates (petroleum),
hydrotreated heavy
paraffinic (CAS 64742-54-7)

Type

TWA

Value

5 mg/m3

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components

Type

Value

Form

distillates (petroleum),
hydrodesulfurized middle
(CAS 64742-80-9)

PEL

400 mg/m3

distillates (petroleum),
hydrotreated heavy
paraffinic (CAS 64742-54-7)

PEL

100 ppm

5 mg/m3

Mist.

naphtha (petroleum),
hydrotreated heavy (CAS
64742-48-9)

PEL

400 mg/m3

100 ppm

ACGIH

Components

Type

Value

Form

distillates (petroleum),
hydrotreated heavy
paraffinic (CAS 64742-54-7)

TWA

5 mg/m3

Inhalable fraction

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)	TWA	5 mg/m3	Inhalable fraction.
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	TWA	5 mg/m3	Inhalable fraction.

U.S. - NIOSH

Components	Type	Value	Form
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	STEL	10 mg/m3	Mist
	TWA	5 mg/m3	Mist

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value	Form
distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)	TWA	400 mg/m3	
		100 ppm	
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	STEL	10 mg/m3	Mist.
	TWA	5 mg/m3	Mist.
naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)	TWA	400 mg/m3	
		100 ppm	

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower should be available when handling this product.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection Wear protective gloves such as: Nitrile. Neoprene.

Other

Wear appropriate chemical resistant clothing.

Respiratory protection

If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

Observe any medical surveillance requirements. When using do not smoke.

9. Physical and chemical properties**Appearance**

Physical state Liquid.

Form Liquid.

Color Dark brown.

Odor Mild petroleum.

Odor threshold Not available.

pH Not available.

Melting point/freezing point -104.8 °F (-76 °C) estimated

Initial boiling point and boiling range Not available.

Flash point	153 °F (67.2 °C) Setflash
Evaporation rate	Slow.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	0.6 % estimated
Flammability limit - upper (%)	7.5 % estimated
Vapor pressure	0.6 hPa estimated
Vapor density	> 1 (air = 1)
Relative density	0.89
Solubility(ies)	
Solubility (water)	Insoluble.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	419 °F (215 °C) estimated
Decomposition temperature	Not available.
Percent volatile	Not available.

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Avoid heat, sparks, open flames and other ignition sources. Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	Carbon oxides. Nitrogen oxides (NOx). Hydrocarbons.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Harmful if inhaled.
Skin contact	Causes skin irritation.
Eye contact	Causes serious eye irritation.
Ingestion	Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.

Symptoms related to the physical, chemical and toxicological characteristics	Aspiration may cause pulmonary edema and pneumonitis. Dizziness. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause redness and pain.
---	---

Information on toxicological effects

Acute toxicity	May be fatal if swallowed and enters airways. Harmful if inhaled.
-----------------------	---

Components	Species	Test Results
------------	---------	--------------

2-ethylhexanol (CAS 104-76-7)

Acute

Dermal

LD50	Rabbit	1986 mg/kg
------	--------	------------

Oral

LD50	Rat	2053 mg/kg
------	-----	------------

2-ethylhexyl nitrate (CAS 27247-96-7)

Acute

Inhalation

LC50	Rat	10 - 20 mg/l, 4 hours
------	-----	-----------------------

Components	Species	Test Results
distillates (petroleum), hydrosulfurized middle (CAS 64742-80-9)		
<u>Acute</u>		
Dermal		
LD50	Rabbit	> 2000 mg/kg
naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)		
<u>Acute</u>		
Dermal		
LD50	Rabbit	> 2000 mg/kg
Skin corrosion/irritation	Causes skin irritation.	
Serious eye damage/eye irritation	Causes serious eye irritation.	
Respiratory or skin sensitization		
Respiratory sensitization	Not a respiratory sensitizer.	
Skin sensitization	This product is not expected to cause skin sensitization.	
Germ cell mutagenicity	Suspected of causing genetic defects.	
Carcinogenicity	Suspected of causing cancer.	
IARC Monographs. Overall Evaluation of Carcinogenicity		
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	3 Not classifiable as to carcinogenicity to humans.	
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)		
Not regulated.		
US. National Toxicology Program (NTP) Report on Carcinogens		
Not listed.		
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.	
Specific target organ toxicity - single exposure	Not classified.	
Specific target organ toxicity - repeated exposure	Not classified.	
Aspiration hazard	May be fatal if swallowed and enters airways. If aspirated into lungs during swallowing or vomiting, may cause chemical pneumonia, pulmonary injury or death.	
Chronic effects	Prolonged inhalation may be harmful.	

12. Ecological information

Ecotoxicity	Toxic to aquatic life with long lasting effects.		
Components		Species	Test Results
2-ethylhexanol (CAS 104-76-7)			
Aquatic			
Fish	LC50	Bluegill (Lepomis macrochirus)	10 - 33 mg/l, 96 hours
Acute			
Crustacea	EC50	Water flea (Daphnia magna)	39 mg/l, 48 hours
2-ethylhexyl nitrate (CAS 27247-96-7)			
Aquatic			
Acute			
Fish	LC50	Bluegill (Lepomis macrochirus)	4.5 mg/l, 96 hours
distillates (petroleum), hydrosulfurized middle (CAS 64742-80-9)			
Aquatic			
Fish	LC50	Rainbow trout,donaldson trout (Oncorhynchus mykiss)	8.8 mg/l, 96 hours
			8.8 mg/l, 96 hours
Acute			
Crustacea	EC50	Water flea (Daphnia magna)	1.09 - 3.4 mg/l, 48 hours

Components	Species		Test Results
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)			
Aquatic			
Acute			
Crustacea	EC50	Water flea (Daphnia magna)	> 10000 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas)	> 100 mg/l, 96 hours
naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)			
Aquatic			
Crustacea	EC50	Water flea (Daphnia pulex)	2.7 - 5.1 mg/l, 48 hours
Fish	LC50	Rainbow trout,donaldson trout (Oncorhynchus mykiss)	8.8 mg/l, 96 hours
			8.8 mg/l, 96 hours
Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.		
Bioaccumulative potential			
Mobility in soil	No data available.		
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.		

13. Disposal considerations

Hazardous waste code	Not regulated.
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.
Disposal instructions	This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.

14. Transport information

DOT	Not regulated as dangerous goods.
IATA	Not regulated as dangerous goods.
IMDG	Not regulated as dangerous goods.

15. Regulatory information

US federal regulations	This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)	Not regulated.
SARA 304 Emergency release notification	Not regulated.
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)	Not regulated.
US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance	Not regulated.
CERCLA Hazardous Substance List (40 CFR 302.4)	Not listed.
CERCLA Hazardous Substances: Reportable quantity	Not listed.
	Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA)

Not regulated.

Food and Drug Administration (FDA)

Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 313 (TRI reporting)

Not regulated.

US state regulations

US. New Jersey Worker and Community Right-to-Know Act

distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)

naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)

US. Massachusetts RTK - Substance List

2-ethylhexanol (CAS 104-76-7)

distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)

naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)

US. Pennsylvania Worker and Community Right-to-Know Law

2-ethylhexanol (CAS 104-76-7)

distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)

US. Rhode Island RTK

distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)

naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)

California Proposition 65



WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

California Proposition 65 - CRT: Listed date/Carcinogenic substance

ethylene oxide (CAS 75-21-8)

Listed: July 1, 1987

propylene oxide (CAS 75-56-9)

Listed: October 1, 1988

California Proposition 65 - CRT: Listed date/Developmental toxin

ethylene oxide (CAS 75-21-8)

Listed: August 7, 2009

methanol (CAS 67-56-1)

Listed: March 16, 2012

California Proposition 65 - CRT: Listed date/Female reproductive toxin

ethylene oxide (CAS 75-21-8)

Listed: February 27, 1987

California Proposition 65 - CRT: Listed date/Male reproductive toxin

ethylene oxide (CAS 75-21-8)

Listed: August 7, 2009

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

distillates (petroleum), hydrodesulfurized middle (CAS 64742-80-9)

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)

naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)

Volatile organic compounds (VOC) regulations

EPA

VOC content (40 CFR 51.100(s)) 97.3 %

Consumer products (40 CFR 59, Subpt. C) Not regulated

State	
Consumer products	Not regulated
VOC content (CA)	97.3 %
VOC content (OTC)	97.3 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	No
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	No
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Toxic Chemical Substances (TCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	05-22-2015
Revision date	02-21-2018
Prepared by	Allison Yoon
Version #	03
Further information	CRC # 885A/1002862

Disclaimer The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..

Revision information This document has undergone significant changes and should be reviewed in its entirety.