






Note that all unique customer requirements (i.e tolerance) need to be verified thru Alfa Laval.

Z80
Alloy 316
S3,S4



Z 25
Carbon Steel
S1,S2,T3,T4



T1 T2 T3 T4 locations on back side
correspond to S1 S2 S3 S4 on front side

HEATING SURFACE
NETWEIGHT 77.5 kg
OPERATING WEIGHT
PLATE MATERIAL Alloy 316
PLATE GROUPING 1*59H/1*60H

ALL DIMENSIONS IN MILLIMETERS

SIDE	MEDIA	INLET	TEMP.	OUTLET	TEMP.	FLOW RATE	PRESSURE DROP	LIQUID VOL.
1								14.8 dm ³
2								15 dm ³

PRESSURE VESSEL APPROVAL

ASME 302 degr F/CRN

AlfaNova HP 76-120H W65 ASME (3287131351)

www.alfalaval.com

CUSTOMER NAME / REF. NO.

TOTAL LENGTH 428.0 mm
TOTAL WIDTH 191.0 mm
TOTAL HEIGHT 699.0 mm

COMPANY / REF.

6/27/2017
REV 0