




This document and its contents are subject to copyrights and other intellectual property rights owned by Alfa Laval (publ) or any of its affiliates (Alfa Laval). No part of this document may be copied, reproduced or transmitted in any form or by any means, or for any purpose, without Alfa Laval's prior express written permission. Information and services provided in this document are made as a benefit and service to the user, and no representations or warranties are made about the accuracy or suitability of this information and these services for any purpose. All rights are reserved.

OPID 240 es 8240171385

PRESSURE PLATE
(MOVABLE)





Space between pressure plate and supporting column should be kept free from fixed installations!



ASME B1.20.1 - 1 1/4-11.5 NPT, ALLOY 316, 101 mm
S1, S2, S3, S4

A-A:




ASME B1.20.1 - 1 1/4-11.5 NPT

NO. OF UNITS

1


25.0 GPM
20.0 GPM

FRAME PLATE





*) Recommended free space for opening and closing to be applied on both sides

**) Free space can be reduced to this distance on one of the sides



All dimensions in inches



APPROX. OUTER DIMENSIONS
LENGTH 12.2 in
WIDTH 7.5 in
HEIGHT 19.3 in
APPROX. WEIGHTS
NET WEIGHT, EMPTY 72.5 lb
WEIGHT FULL OF WATER 78.2 lb
PLATE MATERIAL ALLOY 316
PLATE THICKNESS 0.5 mm
GASKET NBRP Clip-on

CHANNEL ARRANGEMENT 1*12 MH
/ 1*12 ML




www.alfalaval.com

DRAWING
GASKETED PLATE HEAT EXCHANGER
M3-FG

ASME
Code Section VIII Div.1

MAWP 145 psi at 150.1 °F
MDMT 32.0 °F at 145 psi
Designed and constructed in accordance with the 2019 ASME Code.



8240171385
M3-FG-25 Plates

Do not use this drawing for foundation bolting or piping layout

DATE 6/1/22
REVISION 0