


# CRAFTSMAN®

**1 YEAR LIMITED WARRANTY**  
WE BUILD PRIDE™

## 1.5 GALLON HOTDOG AIR COMPRESSOR

This CRAFTSMAN CMA0200141A 1.5 gallon air compressor has the power you need in the house and on the job site. An integrated control panel, two gauges, one large regulator knob and one quick coupler makes the operation of the CMA0200141A easy. Its Oil-free pump requires less maintenance for your convenience. It can do most any job you need it to do.

**Light compact** design with carrying handle for each move  
**LARGE REGULATOR KNOB** FOR EASY OPERATION



**HIGH PERFORMANCE MOTOR**  
EASILY STARTS IN COLD WEATHER  
**OIL-FREE PUMP**  
FOR LONG LIFE AND LITTLE MAINTENANCE  
**1.5 GAL TANK | 1.5 SCFM\* @ 90 PSI**  
**DRAIN VALVE**  
REMOVES DIRT EASILY LONG RUNTIME AND QUICK RECOVERY

### SPECIFICATIONS

- 1.5 Gallon\*
- 60 Hz
- 3/4 HP\*\*
- Airflow: 1.5CFM@90PSI, 2.2CFM@40PSI
- Ball Valve
- Handle Type: N/A
- Decibel Rating:  $\leq$  87 dBA
- Life Cycle:  $\geq$  150 Hours@ 50% Duty Cycle
- Working Pressure: 105-135 PSI (7-9 Bar)
- Produce Size (LxWxH): 16.48 x 15.55 x 10.43 inch  
41.8 x 39.5 x 26.5 cm
- Packing Size (LxWxH): 17.1 x 16.3 x 11.1 inch  
43.5 x 41.5 x 28.3 cm
- Gross Weight: 24.25 lbs / 11 kg  
Net Weight: 22.5 lbs / 10.2 kg
- UPC: 00810941030918\*\*\*



- \* Tank capacity refers to actual tank volume and does not reflect capacity available during operation.
- \*\* "Peak Horsepower" (PHP) is a term used in the wet/dry vacuum industry for consumer comparison purposes. It does not denote the operational horsepower of a wet/dry vacuum but rather the horsepower output of a motor, including the motor's inertial contribution, achieved in laboratory testing. In actual use, wet/dry vacuum motors do not operate at the peak horsepower shown.
- \*\*\* UPC Can vary by product or customer