



AMERICAN EAGLE[®]
FOOD MACHINERY, INC.

AE-10DCA
10 Quart Countertop
Planetary Mixer

773.376.0800 (P) • 773.376.2010 (F) • 3131 S. Canal St. Chicago, IL 60616

Lower Your Total Cost Of Ownership With American Eagle® Mixers! All-Inclusive Accessories, Competitive Pricing, And Reliability Make Us The Value Leader In The Industry.

Quality Design

- Powerful 7/8 HP Variable Speed DC Motor
- 100% Gear-Driven Transmission, Precision Milled, Heat Treated Steel Alloy Gears And Shafts
- Heavy Duty, Cast Iron and Steel Construction
- NSF Approved Heat Treated Enamel Paint Resists Rust, Scratches, And Dents
- Thermal Overload Protection With Reset
- Non-Skid Rubber Base
- ETL Certified To Conform To: NSF No. 8, CSA, CE Standards
- Heavy Duty, 6 Foot Power Cable And NEMA 5-15Plug



Standard Features

- Digital Control Panel with 30 Minute Timer
- 15 Fixed Speeds (3 Gear / 5 Motor)
- Safety Guard with Auto-Shutoff and Integrated Ingredient Pour Chute
- 1 Year Limited Warranty*

Standard Accessories

- High Polish 10 Quart Stainless Steel Bowl
- Aluminum Dough Hook
- Stainless Steel Wire Whip
- Aluminum Beater



Other Available Sizes

- AE-20GA 20 Quart Planetary Mixer
- AE-30GA 30 Quart Planetary Mixer
- AE-40PA 40 Quart Planetary Mixer
- AE-60N4A 60 Quart Planetary Mixer
- AE-80N4A 80 Quart Planetary Mixer (Special Order Only)

Proud Member of:

 North American Association of
 Food Equipment Manufacturers

Quality • Value • Reliability




AMERICAN EAGLE[®]
FOOD MACHINERY, INC.

AE-10DCA
10 Quart Countertop
Planetary Mixer

sales@ameagle.biz • www.americaneaglemachine.com

Machine Specifications

| Model | Capacity** | Motor | Voltage V/HZ/PH | Transmission | Total Speed Options** | Safety Guard | Power Bowl Lift | Timer |
|----------|----------------------------------|--------|-----------------|--------------|-----------------------|--------------|-----------------|--------|
| AE-10DCA | 10 Quart Bowl Max 5 lbs Dough | 7/8 HP | 115/60/1 | Gear Driven | 15 | Yes | No | 30 Min |



| Measurements | | |
|--------------|--------|-------------|
| Dimension | Inches | Centimeters |
| A | 13.4 | 34 |
| B | 11.8 | 30 |
| C | 13.4 | 34 |
| D | 12 | 30.5 |
| E | 15 | 38 |
| F | 21.5 | 54.5 |

| RPM Speeds | | DC Motor Speed Control Setting | | | | |
|-------------------------|---|--------------------------------|-----|-----|-----|-----|
| | | 1 | 2 | 3 | 4 | 5 |
| Gear Shifter Setting*** | 1 | 193 | 296 | 354 | 438 | 496 |
| | 2 | 206 | 315 | 378 | 468 | 529 |
| | 3 | 249 | 381 | 456 | 564 | 638 |

Dimensions and Shipping Information

| Model | Overall Dimensions | Foot Print | Net Weight | Shipping Dimensions | Ship Weight |
|----------|-----------------------------|---------------|------------|---------------------|-------------|
| AE-10DCA | 13.1" L x 17.7" W x 21.2" H | 11.8"L x 15"W | 52 lbs. | 21"W x 17"L x 25"H | 72 lbs. |

*Warranty must be registered. Use of high speed with dough will void warranty, changing speeds improperly will void warranty

**Capacity may be diminished depending on dough density and absorption ratio. Capacity listed is assuming a 60% absorption ratio.

***To change gear speeds, first turn off the machine. Move the lever into position so that the gears lock, then resume mixing.



Quality • Value • Reliability