



Technical Data

Color	Black
Sizes Available	9-12
Packaging	Boxed
Packed	6 Pair/Case
Case Dimensions (in)	21.14 x 18.15 x 11.89
Case Weight (lbs)	20.77
Country of Origin	Malaysia
Material	Rubber
Length	18"
Cuff Color	Orange
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

NOVAX®

Class 4 Rubber Insulating Glove with Bell Cuff - 18"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Bell cuff increases comfort on the job
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection
- **⚠️ WARNING:** Cancer - www.P65Warnings.ca.gov

Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

Performance Data

Electrical Class	Class 4
------------------	---------

Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
159-4-18/9	Black	9	616314094910	01616314094919	02616314094918
159-4-18/10	Black	10	616314094880	01616314094889	02616314094888
159-4-18/11	Black	11	616314094897	01616314094896	02616314094895
159-4-18/12	Black	12	616314094903	01616314094902	02616314094901