



MCR
SAFETY

HV200

ForceFlex Mechanics Gloves

Mechanics

PRODUCT DESCRIPTION:

The ForceFlex® mechanics gloves line provide the ultimate back of hand protection while providing full flexibility and range of motion. The HV200 full finger style features an ergonomically designed Clarino® synthetic leather palm pad with Rough reinforced palm with EVA Padding. The injection molded TPR padding on the back of hand and fingers provides full dorsal metacarpal protection. The HV200 also features a 40 gram Thinsulate® liner with pocket in the cuff for a heat pack. The water and wind resistant bladder provides additional protection from the wet and cold. The orange mesh fabric backing and yellow palm provide excellent contrast. The neoprene slip-on cuff w/side flex panels and Reflexite® retro-reflective material on both sides of cuff provide a comfortable fit and high visibility for low light environments. Great for impact resistant oilfield gloves. Looking for the best impact resistant work glove? Look no further than MCR Safety!



FEATURES:

- Injection Moded TPR Padding on the Back of Hand and Fingers
- Rough Kevlar® Palm w/EVA Padding Reinforced Palm
- Neoprene Slip-on Cuff w/Side Flex Panels
- Reflexite® Micro-Prismatic Retroreflective Material on Both Sides of Cuff
- 40 gram Thinsulate® insulated gloves with pocket in the cuff for heat pack
- Water/Wind Resistant bladder

APPLICATIONS:

Pipe fitting, Railroad, Automotive Assembly, Carpentry, Automotive

TECHNICAL DATA FOR: HV200

| | | | |
|----------------|----------------------------|-----------------------------|---|
| Series | ForceFlex Mechanics Gloves | EN 388: CE Score - Abrasion | 4 |
| Material Group | Multi-Task | EN 388 : CE Score - Cut | 2 |
| Product Type | Mechanics | EN 388 : CE Score - Tear | 2 |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved




MCR
SAFETY

HV200

ForceFlex Mechanics Gloves

Mechanics

| | | | |
|---------------------|-----------------|-------------------------------------|---|
| Glove Size | Large | EN 388 : CE Score - Puncture | 1 |
| Material | Synthetic | | |
| Leather Cut | Suede Synthetic | | |
| Leather Type | Synthetic | | |
| Grade | Premium | | |
| Features | Waterproof | | |
| Insulated | Yes | | |
| Lining | Thinsulate | | |
| Pattern | Gunn | | |
| Thumb Style | Wing | | |
| HI VIS | Yes | | |
| | | | |
| Made In | Vietnam | | |



| Item No: | Size: | A: | B: | C: | Case Weight | UOM Weight |
|-----------|-------------|--------|-------|-------|-------------|------------|
| HV200L | Large | 13.189 | 4.409 | 2.559 | 54.700 lb. | 0.760 |
| HV200XXXL | XXX - Large | 14.016 | 4.882 | 2.559 | 63.120 lb. | 0.877 |
| HV200XXL | XX - Large | 13.740 | 4.724 | 2.559 | 61.380 lb. | 0.853 |
| HV200XL | X - Large | 13.464 | 4.567 | 2.559 | 44.568 lb. | 0.619 |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved