



A CSW Industrials Company

# PRODUCT DATA SHEET

## SILICONE SEALANT

General purpose silicone sealant/caulk

### Description

General Purpose Silicone Sealant is a premium quality 100% RTV silicone caulk that remains permanently flexible. Ideal for sealing around electrical panels, windows, doors, pipes/vents, corner joints, aluminum siding and other interior/exterior building materials. Dry to touch in 30 minutes and fully cures in 24 hours. Silicone Sealant can be used indoors or outdoors, has excellent adhesion, and remains flexible when cured.

### Applications

General Purpose Silicone Sealant can be used to seal around bathtubs, shower stalls, bathroom vanities, kitchen counters, sinks, windows and doors. It can be used for replacing ceramic tiles and making new gaskets for dishwasher doors, sealing windshields in cars, vans and boats. Use it to repair or install body-side moulding, and any application that requires a permanently flexible waterproof seal that will withstand moisture, heat and vibration.



### DIRECTIONS FOR USE:

READ SDS, ALL DIRECTIONS AND WARNINGS ON LABEL BEFORE USING

1. Clean and dry all surfaces. Completely remove all dirt, grease, soap and previous caulk.
2. Cut nozzle at desired bead size
3. Apply a continuous bead of silicone.
4. Most paint will not adhere to silicone. Surface should be painted first then sealed. Excess, uncured sealant can be removed with solvents.
5. Silicone "skins" to become tack-free in 15 minutes, cures in 1 hour. Allow 24 hours for full cure and strength.

For additional technical information, call Toll Free 1-800-231-3345.

### Characteristics | Features

- -50° to +450°F Service Temp
- Insulates
- Vibration Resistant
- Bonds
- Remains Flexible
- Seals

### Packaging

Code	Size	Qty. per Case	Lbs. per Case	Cubic Feet per Case
57505	10.3 Fl. Oz. Tube - White	12	10	.42
57506	10.3 Fl. Oz. Tube - Clear	12	10	.42

# SILICONE SEALANT

General purpose silicone sealant/caulk

## Specifications

### Shelf Life and Storage:

Shelf Life is 12 months from date of manufacture when stored in clean, dry area with temperature between 40°F to 90°F (4°C to 32°C). For best results, keep the sealant in tightly closed containers when not in use.

General Purpose Contractor Grade Silicone Sealant meets the following specifications: CAN/CGSB-19.13- M87, Class MG-2-25 - A-L, ASTM C920, Type S, Grade NS, Class 25, use NT, G, A, O. U.S. Fed Specs TT-S-001543A and TT-S-00230C Type 2. Certified by NSF. Agricultural Canada Approved. After fully cured, RectorSeal Silicone Sealant meets the requirements of FDA Regulation No. 21 CFR 177.2600 subject to end use.

Suggestions and recommendations covering the use of our products are based on our past experience and laboratory findings. However, as we have no control as to the methods and conditions of application, we only assume responsibility for the uniformity of our products within manufacturing tolerances.

## Precautionary Statements

Refer to Safety Data Sheet (SDS).

### KEEP OUT OF REACH OF CHILDREN

**FOR CHEMICAL EMERGENCY, SPILL, LEAK, FIRE, EXPOSURE OR ACCIDENT, CALL CHEMTREC - DAY OR NIGHT 1-800-424-9300**

For additional Technical Information Call Toll Free 1-800-231-3345

## Limited Warranty

RectorSeal, LLC makes the Limited Express Warranty that when the instructions for storage and handling of our products are followed we warrant our products to be free from defects. THIS LIMITED EXPRESS WARRANTY IS EXPRESSLY IN LIEU OF ANY OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, AND OF ANY OTHER OBLIGATION ON THE PART OF RectorSeal, LLC. The sole remedy for breach of the Limited Express Warranty shall be the refund of the purchase price. All other liability is negated and disclaimed, and RectorSeal, LLC shall not be liable for incidental or consequential damages.

Manufactured by

**RectorSeal, LLC**

**2601 Spenwick Drive • Houston, TX 77055, USA • 800-231-3345 • Fax 800-441-0051 • [rectorseal.com](http://rectorseal.com)**

A CSW Industrials Company. RectorSeal, the logos and other trademarks are property of RectorSeal, LLC, its affiliates or its licensor's and are protected by copyright, trademark and other intellectual property laws, and may not be used without permission. RectorSeal reserves the right to change specifications without prior notice. ©2020 RectorSeal. All rights reserved. R50027-1220