



## NOVAX®

### Class 1 Rubber Insulating Glove with Straight Cuff - 16"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection
- **⚠️ WARNING:** Cancer - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing



## Technical Data

Color	Black
Sizes Available	8-12
Packaging	Boxed
Packed	6 Pair/Case
Case Dimensions (in)	21.14 x 18.15 x 11.89
Case Weight (lbs)	13.67
Country of Origin	Malaysia
Material	Rubber
Length	16"
Cuff	Straight
Cuff Color	Orange
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

## Performance Data

Electrical Class	Class 1
------------------	---------

## Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



## SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
155-1-16/8	Black	8	616314066603	01616314066602	02616314066601
155-1-16/9	Black	9	616314066597	01616314066596	02616314066595
155-1-16/10	Black	10	616314066610	01616314066619	02616314066618
155-1-16/11	Black	11	616314066627	01616314066626	02616314066625
155-1-16/12	Black	12	616314066634	01616314066633	02616314066632