



SAFETY DATA SHEET

Mo-Lith No. 2

According to Appendix D, OSHA Hazard Communication Standard 29 CFR §1910.1200

1. Identification

Product identifier

Product name Mo-Lith No. 2

Product number L0180-004, L0180-035, L0180-039, L0180-040, L0180-041, L0180-098, L0180-001, L0180-006, L0180-040B

Recommended use of the chemical and restrictions on use

Application Lubricating grease.

Uses advised against No specific uses advised against are identified.

Details of the supplier of the safety data sheet

Manufacturer Lubriplate Lubricants Co.
Corporate Headquarters
129 Lockwood Street
Newark, NJ 07105

Midwest Office & Plant
1500 Oakdale Ave.
Toledo, OH 43605
419-691-2491
419-693-3806

Emergency telephone number

Emergency telephone Chem-Tel: 1-800-255-3924 (US & Canada only)
01-813-248-0585 (Outside US & Canada)

2. Hazard(s) identification

Classification of the substance or mixture

Physical hazards Not Classified

Health hazards Not Classified

Environmental hazards Not Classified

Label elements

Hazard statements NC Not Classified

Other hazards

This product does not contain any substances classified as PBT or vPvB.

3. Composition/information on ingredients

Mixtures

Mo-Lith No. 2

Distillates (petroleum), hydrotreated heavy naphthenic	60-100%
CAS number: 64742-52-5	
Classification	
Not Classified	
Carbon graphite	1-5%
CAS number: 7782-42-5	
Classification	
Not Classified	

The full text for all hazard statements is displayed in Section 16.

Composition comments * The exact percentage withheld as a trade secret in accordance with 29 CFR 1910.1200.

4. First-aid measures

Description of first aid measures

General information	Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel.
Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt.
Ingestion	Rinse mouth thoroughly with water. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Do not induce vomiting unless under the direction of medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Never give anything by mouth to an unconscious person. Maintain an open airway. Loosen tight clothing such as collar, tie or belt.
Skin Contact	Remove affected person from source of contamination. Rinse immediately with plenty of water.
Eye contact	Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 10 minutes.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

Most important symptoms and effects, both acute and delayed

General information	See Section 11 for additional information on health hazards. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	A single exposure may cause the following adverse effects: Temporary irritation.
Ingestion	May cause discomfort if swallowed. May cause stomach pain or vomiting.
Skin contact	Prolonged contact may cause dryness of the skin.
Eye contact	May be slightly irritating to eyes.

Indication of immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
Specific treatments	No special treatment required.

5. Fire-fighting measures

Extinguishing media

Mo-Lith No. 2

Suitable extinguishing media	The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
<u>Special hazards arising from the substance or mixture</u>	
Specific hazards	None known.
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.
<u>Advice for firefighters</u>	
Protective actions during firefighting	Avoid breathing fire gases or vapors. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Standard Firefighter's clothing including helmets, protective boots and gloves will provide a basic level of protection for chemical incidents.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions	No action shall be taken without appropriate training or involving any personal risk. Keep unnecessary and unprotected personnel away from the spillage. Wear protective clothing as described in Section 8 of this safety data sheet. Follow precautions for safe handling described in this safety data sheet. Wash thoroughly after dealing with a spillage.
-----------------------------	---

Environmental precautions

Environmental precautions	Avoid discharge to the aquatic environment. Large Spillages: Inform the relevant authorities if environmental pollution occurs (sewers, waterways, soil or air).
----------------------------------	--

Methods and material for containment and cleaning up

Methods for cleaning up	Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Reuse or recycle products wherever possible. Approach the spillage from upwind. Collect spillage with a shovel and broom, or similar and reuse, if possible. Collect and place in suitable waste disposal containers and seal securely. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.
--------------------------------	---

Reference to other sections	For personal protection, see Section 8. For waste disposal, see Section 13.
------------------------------------	---

7. Handling and storage

Precautions for safe handling

Usage precautions	Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Keep container tightly sealed when not in use.
--------------------------	--

Advice on general occupational hygiene	Wash promptly if skin becomes contaminated. Take off contaminated clothing and wash before reuse. Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Wash at the end of each work shift and before eating, smoking and using the toilet. Change work clothing daily before leaving workplace.
---	---

Conditions for safe storage, including any incompatibilities

Mo-Lith No. 2

Storage precautions	Store away from incompatible materials (see Section 10). Store in accordance with local regulations.
Storage class	Unspecified storage.
<u>Specific end uses(s)</u>	
Specific end use(s)	The identified uses for this product are detailed in Section 1.

8. Exposure controls/Personal protection

Control parameters

Occupational exposure limits

Distillates (petroleum), hydrotreated heavy naphthenic

Mineral oil, excluding metal working fluids (pure, highly and severely refined)

ACGIH

Carbon graphite

Long-term exposure limit (8-hour TWA): ACGIH 2 mg/m³ respirable fraction

Long-term exposure limit (8-hour TWA): OSHA 15 particles/cc respirable dust

ACGIH = American Conference of Governmental Industrial Hygienists.

OSHA = Occupational Safety and Health Administration.

Carbon graphite (CAS: 7782-42-5)

Immediate danger to life and health 1250 mg/m³

Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation. Good general ventilation should be adequate to control worker exposure to airborne contaminants.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Personal protective equipment for eye and face protection should comply with OSHA 1910.133. No specific eye protection required during normal use.

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with OSHA 1910.138 and be demonstrated to be impervious to the chemical and resist degradation. Considering the data specified by the glove manufacturer, check during use that the gloves are retaining their protective properties and change them as soon as any deterioration is detected. Frequent changes are recommended.

Other skin and body protection

Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.

Hygiene measures

Provide eyewash station and safety shower. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reuse. Clean equipment and the work area every day. Good personal hygiene procedures should be implemented. Wash at the end of each work shift and before eating, smoking and using the toilet. When using do not eat, drink or smoke.

Mo-Lith No. 2

Respiratory protection	Respiratory protection complying with an approved standard should be worn if a risk assessment indicates inhalation of contaminants is possible. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.
Environmental exposure controls	Not regarded as dangerous for the environment.

9. Physical and chemical properties

Information on basic physical and chemical properties

Appearance	Solid.
Color	Black. Grey.
Odor	Mild.
Odor threshold	Not available.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	>288°C (>550.4°F)
Flash point	> 204°C/399.2°F Cleveland open cup.
Evaporation rate	< 0.01 (butyl acetate = 1)
Upper/lower flammability or explosive limits	Not available.
Vapor pressure	<0.0013 kPa @ 25°C
Vapor density	> 5
Relative density	0.94
Solubility(ies)	Insoluble in water.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Not available.
Explosive properties	Not applicable.
Oxidizing properties	Not available.
Other information	None.

10. Stability and reactivity

Reactivity	See the other subsections of this section for further details.
Stability	Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.
Possibility of hazardous reactions	No potentially hazardous reactions known.
Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.

Mo-Lith No. 2

Materials to avoid	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
Hazardous decomposition products	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

11. Toxicological information

Information on toxicological effects

Acute toxicity - oral

Summary Based on available data the classification criteria are not met.

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

ATE oral (mg/kg) 20,000.0

Acute toxicity - dermal

Summary Based on available data the classification criteria are not met.

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Summary Based on available data the classification criteria are not met.

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

ATE inhalation (vapours mg/l) 440.0

Skin corrosion/irritation

Summary Based on available data the classification criteria are not met.

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Summary Based on available data the classification criteria are not met.

Serious eye damage/irritation Based on available data the classification criteria are not met.

Respiratory sensitization

Summary Based on available data the classification criteria are not met.

Respiratory sensitization Based on available data the classification criteria are not met.

Skin sensitization

Summary Based on available data the classification criteria are not met.

Skin sensitization May cause skin sensitization or allergic reactions in sensitive individuals.

Germ cell mutagenicity

Summary Based on available data the classification criteria are not met.

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Summary Based on available data the classification criteria are not met.

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity None of the ingredients are listed or exempt.

Reproductive toxicity

Summary Based on available data the classification criteria are not met.

Mo-Lith No. 2

Reproductive toxicity - fertility	Based on available data the classification criteria are not met.
Reproductive toxicity - development	Based on available data the classification criteria are not met.
<u>Specific target organ toxicity - single exposure</u>	
Summary	Based on available data the classification criteria are not met.
STOT - single exposure	Not classified as a specific target organ toxicant after a single exposure.
<u>Specific target organ toxicity - repeated exposure</u>	
Summary	Based on available data the classification criteria are not met.
STOT - repeated exposure	Not classified as a specific target organ toxicant after repeated exposure.
<u>Aspiration hazard</u>	
Summary	Not relevant. Solid.
Aspiration hazard	Not relevant. Solid.
<u>General information</u>	
General information	No specific health hazards known. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	A single exposure may cause the following adverse effects: Temporary irritation.
Ingestion	May cause discomfort if swallowed. May cause stomach pain or vomiting.
Skin Contact	Prolonged contact may cause dryness of the skin.
Eye contact	May be slightly irritating to eyes.
Route of exposure	Ingestion Inhalation Skin and/or eye contact
Target Organs	No specific target organs known.
Medical considerations	Skin disorders and allergies.

12. Ecological information

Ecotoxicity	Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.
Toxicity	Aquatic Chronic 3 - H412 Harmful to aquatic life with long lasting effects.
<u>Acute aquatic toxicity</u>	
Summary	Based on available data the classification criteria are not met.
<u>Chronic aquatic toxicity</u>	
Summary	Based on available data the classification criteria are not met.
<u>Persistence and degradability</u>	
Persistence and degradability	The degradability of the product is not known.
<u>Bioaccumulative potential</u>	
Bio-Accumulative Potential	No data available on bioaccumulation.
Partition coefficient	Not available.
<u>Mobility in soil</u>	
Mobility	No data available.

Mo-Lith No. 2

Other adverse effects

Other adverse effects None known.

13. Disposal considerations

Waste treatment methods

General information

The generation of waste should be minimized or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. Disposal of this product, process solutions, residues and by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any local authority requirements.

Disposal methods

Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste packaging should be collected for reuse or recycling. Incineration or landfill should only be considered when recycling is not feasible. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of the local water authority.

14. Transport information

General

The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, DOT).

UN Number

UN No. (International) Not applicable.

UN No. (DOT) Not applicable.

UN proper shipping name

Proper shipping name (International) Not applicable.

Proper shipping name (DOT) Not applicable.

Transport hazard class(es)

Transport Labels (International) No transport warning sign required.

DOT transport labels

No transport warning sign required.

Packing group

Packing group (International) Not applicable.

DOT packing group Not applicable.

Environmental hazards

Environmentally Hazardous Substance

No.

Special precautions for user

Not applicable.

DOT reportable quantity Not applicable.

DOT TIH Zone Not applicable.

Mo-Lith No. 2

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

15. Regulatory information

Regulatory References OSHA Hazard Communication Standard 29 CFR §1910.1200

US Federal Regulations

SARA Section 302 Extremely Hazardous Substances Tier II Threshold Planning Quantities

None of the ingredients are listed or exempt.

CERCLA/Superfund, Hazardous Substances/Reportable Quantities (EPA)

None of the ingredients are listed or exempt.

SARA Extremely Hazardous Substances EPCRA Reportable Quantities

None of the ingredients are listed or exempt.

SARA 313 Emission Reporting

The following ingredients are listed or exempt:

Antimony tris[O,O-dipropyl] tris(dithiophosphate)

1.0 %

CAA Accidental Release Prevention

None of the ingredients are listed or exempt.

FDA - Essential Chemical

None of the ingredients are listed or exempt.

FDA - Precursor Chemical

None of the ingredients are listed or exempt.

SARA (311/312) Hazard Categories

None of the ingredients are listed or exempt.

OSHA Highly Hazardous Chemicals

None of the ingredients are listed or exempt.

US State Regulations

California Proposition 65 Carcinogens and Reproductive Toxins

None of the ingredients are listed or exempt.

California Air Toxics "Hot Spots" (A-I)

None of the ingredients are listed or exempt.

California Air Toxics "Hot Spots" (A-II)

None of the ingredients are listed or exempt.

California Directors List of Hazardous Substances

The following ingredients are listed or exempt:

Carbon graphite

Massachusetts "Right To Know" List

The following ingredients are listed or exempt:

Carbon graphite

Mo-Lith No. 2

Molybdenum disulfide

Rhode Island "Right To Know" List

The following ingredients are listed or exempt:

Carbon graphite

Minnesota "Right To Know" List

The following ingredients are listed or exempt:

Carbon graphite

New Jersey "Right To Know" List

The following ingredients are listed or exempt:

Carbon graphite

Pennsylvania "Right To Know" List

The following ingredients are listed or exempt:

Carbon graphite

Inventories

US - TSCA

All the ingredients are listed or exempt.

US - TSCA 12(b) Export Notification

None of the ingredients are listed or exempt.

16. Other information

Abbreviations and acronyms used in the safety data sheet

TDG: The transport of dangerous goods act

IATA: International air transport association.

ICAO: Technical instructions for the safe transport of dangerous goods by air.

IMDG: International maritime dangerous goods.

CAS: Chemical abstracts service.

ATE: Acute toxicity estimate.

LC₅₀: Lethal concentration to 50 % of a test population.

LD₅₀: Lethal dose to 50% of a test population (median lethal dose).

EC₅₀: 50% of maximal effective concentration.

PBT: Persistent, bioaccumulative and toxic substance.

vPvB: Very persistent and very bioaccumulative.

Training advice

Read and follow manufacturer's recommendations. Only trained personnel should use this material.

Revision comments

Revised classification.

Revision date

1/27/2020

Revision

6

Supersedes date

1/27/2020

SDS No.

4886

End of SDS

Mo-Lith No. 2

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.