



NOVAX®

Class 2 Rubber Insulating Glove with Contour Cuff - 18"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Contour cuff for increased mobility and comfort on the job
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date

Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

Technical Data

Color	Black
Sizes Available	8-11
Packaging	Boxed
Packed	6 Pair/Case
Case Dimensions (in)	21.14 x 18.15 x 11.89
Case Weight (lbs)	14.70
Country of Origin	Malaysia
Material	Rubber
Length	18"
Cuff	Contour
Cuff Color	Black
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

Performance Data

Electrical Class	Class 2
------------------	---------

Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
163-2-18/8	Black	8	616314154324	01616314154323	02616314154322
163-2-18/9	Black	9	616314154348	01616314154347	02616314154346
163-2-18/9.5	Black	9.5	616314154331	01616314154330	02616314154339
163-2-18/10	Black	10	616314154300	01616314154309	02616314154308
163-2-18/10.5	Black	10.5	616314154294	01616314154293	02616314154292
163-2-18/11	Black	11	616314154317	01616314154316	02616314154315