

Our thick latex gloves are designed to enhance safety by offering extra durability

- Three times thicker than standard latex gloves to prevent rips, snags and tears
- Soft, elastic fit and feel
- Textured fingertips provide secure grip
- Extended cuff for expanded protection over the wrist and forearm
- Double chlorinated for easy donning and a comfortable feel
- Certified to the Emergency Medical Glove Requirements of NFPA 1999



Industries

- Automotive
- Automotive Aftermarket
- Life Sciences
- Healthcare

Recommended For

- Inspection, selecting, checking parts
- Assembly and inspection of components
- Picking and fastening components
- Equipment repair and maintenance
- General Purpose Auto Aftermarket
- Body panel repair and replacement
- Tire rotation & changes
- Animal care feeding and cleanup
- Maintaining lab furniture and equipment
- Sample taking and processing
- Raw material sample collection
- Extra protection over the wrist and arm
- Higher-risk clinical applications
- Tested for use with chemotherapy drugs



TECHNICAL DATA SHEET

PRODUCT INFORMATION

	SafeGrip® SG-375
Material	Natural Rubber Latex
Color	Blue
Glove Design	Chlorinated, Powder-Free, Textured Fingers
Cuff	Beaded
Manufacturing/QMS Audit Standards	EN ISO 13485:2012
Regulatory	ASTM D3578, Food Type: Rubber, EN 420:2003 + A1:2009, FDA21 CFR 177-2600-US Food Contact Approved, NFPA 1999:2018, US QSR/FDA 510(k) Medical Examination Grade
Packaging	50 gloves per dispenser 10 dispensers per case 500 gloves per case
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country of Origin	Malaysia
User Needs Segment	High Risk
Available sizes	S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)
Anti-static	Not Tested

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	295 / 11.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.28 / 11		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.36 / 14.2		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 34	≥ 21	ASTM D412 & D573
Elongation at Break (%)	≥ 850	≥ 750	ASTM D412
Force at break (N)	≥ 15	≥ 10	EN 455-2

ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	SG-375-S	SG-375-M	SG-375-L	SG-375-XL

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.