



SAFETY DATA SHEET

1. Identification

Product identifier	HydroForce® Zero VOC General Purpose Cleaner - 55 gal	
Other means of identification		
Product Code	No. 14449 (Item# 1004993)	
Recommended use	General purpose cleaner	
Recommended restrictions	None known.	
Manufacturer/Importer/Supplier/Distributor information		
Manufactured or sold by:		
Company name	CRC Industries, Inc.	
Address	885 Louis Dr. Warminster, PA 18974 US	
Telephone		
General Information	215-674-4300	
Technical Assistance	800-521-3168	
Customer Service	800-272-4620	
24-Hour Emergency (CHEMTREC)	800-424-9300 (US)	
Website	www.crcindustries.com	

2. Hazard(s) identification

Physical hazards	Not classified.	
Health hazards	Serious eye damage/eye irritation	Category 2A
Environmental hazards	Hazardous to the aquatic environment, acute hazard	Category 3
	Hazardous to the aquatic environment, long-term hazard	Category 3
OSHA defined hazards	Not classified.	
Label elements		



Signal word	Warning	
Hazard statement	Causes serious eye irritation. Harmful to aquatic life. Harmful to aquatic life with long lasting effects.	
Precautionary statement		
Prevention	Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Wash thoroughly after handling. Wear eye protection/face protection. Avoid release to the environment.	
Response	If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.	
Storage	Store away from incompatible materials.	
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.	
Hazard(s) not otherwise classified (HNOC)	None known.	
Supplemental information	None.	

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
water		7732-18-5	80 - 90
alcohols, C9-11, ethoxylated		68439-46-3	3 - 5
quaternary coco alkylamine ethoxylate		61791-10-4	1 - 3

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Wash off with soap and water. Get medical attention if irritation develops and persists.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Ingestion	Rinse mouth. Get medical attention if symptoms occur.
Most important symptoms/effects, acute and delayed	Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire-fighting equipment/instructions	Move containers from fire area if you can do so without risk. Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	This product is miscible in water. Prevent product from entering drains. Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling	Avoid contact with eyes. Avoid prolonged exposure. Provide adequate ventilation. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.
--------------------------------------	--

Conditions for safe storage, including any incompatibilities Store in a cool, dry place out of direct sunlight. Store in tightly closed container. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Biological limit values	No biological exposure limits noted for the ingredient(s).
Appropriate engineering controls	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station.
Individual protection measures, such as personal protective equipment	
Eye/face protection	Wear safety glasses with side shields (or goggles).
Skin protection	
Hand protection	Wear protective gloves such as: Nitrile. Neoprene. Rubber gloves.
Other	Wear suitable protective clothing.
Respiratory protection	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
General hygiene considerations	Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance	
Physical state	Liquid.
Form	Liquid.
Color	Clear.
Odor	Mild detergent.
Odor threshold	Not available.
pH	10.3
Melting point/freezing point	32 °F (0 °C) estimated
Initial boiling point and boiling range	212 °F (100 °C) estimated
Flash point	None.
Evaporation rate	Slow.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	2.6 % estimated
Flammability limit - upper (%)	12.6 % estimated
Vapor pressure	20.9 hPa estimated
Vapor density	Not available.
Relative density	1.04
Solubility(ies)	
Solubility (water)	Appreciable.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	302 °F (150 °C) estimated
Decomposition temperature	Not available.
Percent volatile	87.2 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	Acrolein.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful.
Skin contact	No adverse effects due to skin contact are expected.
Eye contact	Causes serious eye irritation.
Ingestion	Expected to be a low ingestion hazard.

Symptoms related to the physical, chemical and toxicological characteristics Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.

Information on toxicological effects

Acute toxicity Not known.

Components	Species	Test Results
-------------------	----------------	---------------------

alcohols, C9-11, ethoxylated (CAS 68439-46-3)

Acute

Dermal

LD50 Rabbit 5000 mg/kg

Oral

LD50 Rat 1378 mg/kg

quaternary coco alkylamine ethoxylate (CAS 61791-10-4)

Acute

Oral

LD50 Rat 580 mg/kg

Skin corrosion/irritation Prolonged skin contact may cause temporary irritation.

Serious eye damage/eye irritation Causes serious eye irritation.

Respiratory or skin sensitization

Respiratory sensitization Not a respiratory sensitizer.

Skin sensitization This product is not expected to cause skin sensitization.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity Not classifiable as to carcinogenicity to humans.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity This product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity - single exposure Not classified.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard	Not an aspiration hazard.
Chronic effects	Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity Harmful to aquatic life with long lasting effects.

Components	Species	Test Results
alcohols, C9-11, ethoxylated (CAS 68439-46-3)		
Aquatic		
<i>Acute</i>		
Crustacea	EC50 Daphnia	1 - 10 mg/l, 48 hours
Fish	LC50 Fish	1 - 10 mg/l, 96 hours
quaternary coco alkylamine ethoxylate (CAS 61791-10-4)		
Aquatic		
<i>Acute</i>		
Fish	LC50 Trout family (Salmonidae)	24 mg/l, 96 hours

Persistence and degradability No data is available on the degradability of any ingredients in the mixture.

Bioaccumulative potential

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Hazardous waste code Not regulated.

Disposal instructions This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.

Contaminated packaging Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

15. Regulatory information

US federal regulations All components are on the U.S. EPA TSCA Inventory List. This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Classified hazard categories Serious eye damage or eye irritation

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes

SARA 313 (TRI reporting)

Not regulated.

US state regulations

US. New Jersey Worker and Community Right-to-Know Act

Not listed.

US. Massachusetts RTK - Substance List

Not listed.

US. Pennsylvania Worker and Community Right-to-Know Law

Not listed.

US. Rhode Island RTK

Not listed.

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 2016 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to www.P65Warnings.ca.gov.

Volatile organic compounds (VOC) regulations

EPA

VOC content (40 CFR 51.100(s)) 0 %

Consumer products (40 CFR 59, Subpt. C) Not regulated

State

Consumer products This product is regulated as a General Purpose Cleaner (non-aerosol). This product is compliant for use in all 50 states.

VOC content (CA) 0 %

VOC content (OTC) 0 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	Yes

Country(s) or region	Inventory name	On inventory (yes/no)*
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)
A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	08-21-2019
Prepared by	Allison Yoon
Version #	01
Further information	CRC # 686/1002733
Disclaimer	The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..
Revision information	This document has undergone significant changes and should be reviewed in its entirety.