

SECTION 1: IDENTIFICATION**1.1. PRODUCT IDENTIFIER**

Product name : 14A Redi-Bath

Product code : Not Available

1.2. RELEVANT IDENTIFIED USES OF THE SUBSTANCE OR MIXTURE AND USES ADVISED AGAINST

Use of the substance/mixture : Non-Destructive Testing

1.3. DETAILS OF THE SUPPLIER OF THE SAFETY DATA SHEET**Manufacturer**

Magnaflux
155 Harlem Ave.
Glenview, IL 60025 - USA
T: 847-657-5300

Distributor**1.4. EMERGENCY TELEPHONE NUMBER**

Emergency number : CHEMTREC 800-424-9300

SECTION 2: HAZARDS IDENTIFICATION**2.1. CLASSIFICATION OF THE SUBSTANCE OR MIXTURE**

The hazards given in this SDS apply to the product at full concentration. By diluting the product, the hazards will be reduced. It is up to the employer/user to determine the proper personal protection equipment and safety precautions when using diluted product.

GHS classification

Skin Irrit. 2

Eye Irrit. 2A

2.2. LABEL ELEMENTS**GHS labelling**

Hazard pictograms (GHS) :



GHS07

Signal word (GHS) :

: Warning

Hazard statements (GHS) :

: Causes skin irritation. Causes serious eye irritation.

Precautionary statements (GHS) :

: Wash hands thoroughly after handling. Wear eye protection/face protection/protective gloves. If on skin: Wash with plenty of water. Take off contaminated clothing and wash it before reuse. If skin irritation occurs: Get medical advice/attention. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

2.3. OTHER HAZARDS

No additional information available

2.4. UNKNOWN ACUTE TOXICITY (GHS)

Not applicable.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS**3.1. SUBSTANCE**

Not applicable

3.2. MIXTURE

Name	Product identifier	%
Alcohols, C6-12, ethoxylated propoxylated or Alcohols, C6-10, ethoxylated propoxylated	(CAS No) 68937-66-6 or (CAS No) 68987-81-5	4.54
Pentanedioic acid, 1,5-dimethyl ester	(CAS No) 1119-40-0	4.34
Dimethyl succinate	(CAS No) 106-65-0	1.54
2-Amino-2-methyl-1-propanol	(CAS No) 124-68-5	1.34
1-Naphthalenecarboxaldehyde, 2-hydroxy-, [(2-hydroxy-1-naphthalenyl)methylene]hydrazone	(CAS No) 2387-03-3	1.29
Fatty acids, C18-unsaturated, dimers, polymer with ethylenediamine and tall-oil fatty acids	(CAS No) 68139-80-0	0.67
Propanol, 2-(methylamino)-2-methyl-	(CAS No) 27646-80-6	0.11

SECTION 4: FIRST AID MEASURES

4.1. DESCRIPTION OF FIRST AID MEASURES

- First-aid measures after inhalation : If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical advice/attention if you feel unwell.
- First-aid measures after skin contact : In case of contact, immediately flush skin with plenty of water. Remove contaminated clothing and shoes. Wash clothing before reuse. Call a physician if irritation develops and persists.
- First-aid measures after eye contact : In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. If easy to do, remove contact lenses, if worn. If irritation persists, get medical attention.
- First-aid measures after ingestion : If swallowed, do NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical advice/attention if you feel unwell.

4.2. MOST IMPORTANT SYMPTOMS AND EFFECTS, BOTH ACUTE AND DELAYED

- Symptoms/injuries after inhalation : May cause respiratory tract irritation.
- Symptoms/injuries after skin contact : Causes skin irritation. Symptoms may include redness, edema, drying, defatting and cracking of the skin.
- Symptoms/injuries after eye contact : Causes serious eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with marked redness and swelling of the conjunctiva.
- Symptoms/injuries after ingestion : May be harmful if swallowed. May cause stomach distress, nausea or vomiting.

4.3. INDICATION OF ANY IMMEDIATE MEDICAL ATTENTION AND SPECIAL TREATMENT NEEDED

Symptoms may not appear immediately. In case of accident or if you feel unwell, seek medical advice immediately (show the label or SDS where possible).

SECTION 5: FIREFIGHTING MEASURES

5.1. EXTINGUISHING MEDIA

- Suitable extinguishing media : Treat for surrounding material.
- Unsuitable extinguishing media : None known.

5.2. SPECIAL HAZARDS ARISING FROM THE SUBSTANCE OR MIXTURE

- Fire hazard : Products of combustion may include, and are not limited to: oxides of carbon, nitrogen oxides, phosphorus oxides.

5.3. ADVICE FOR FIREFIGHTERS

- Protection during firefighting : Keep upwind of fire. Wear full fire fighting turn-out gear (full Bunker gear) and respiratory protection (SCBA).

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. PERSONAL PRECAUTIONS, PROTECTIVE EQUIPMENT AND EMERGENCY PROCEDURES

- General measures : Use personal protection recommended in Section 8. Isolate the hazard area and deny entry to unnecessary and unprotected personnel.

6.2. METHODS AND MATERIAL FOR CONTAINMENT AND CLEANING UP

- For containment : Contain and/or absorb spill with inert material (e.g. sand, vermiculite), then place in a suitable container. Do not flush to sewer or allow to enter waterways. Use appropriate Personal Protective Equipment (PPE).
- Methods for cleaning up : Scoop up material and place in a disposal container.

6.3. REFERENCE TO OTHER SECTIONS

See section 8 for further information on protective clothing and equipment and section 13 for advice on waste disposal.

SECTION 7: HANDLING AND STORAGE

7.1. PRECAUTIONS FOR SAFE HANDLING

Precautions for safe handling	: Avoid contact with skin and eyes. Avoid breathing dust/fume/gas/mist/vapours/spray. Do not swallow. Handle and open container with care. When using do not eat, drink or smoke.
Hygiene measures	: Launder contaminated clothing before reuse. Wash hands before eating, drinking, or smoking.

7.2. CONDITIONS FOR SAFE STORAGE, INCLUDING ANY INCOMPATIBILITIES

Storage conditions	: Keep out of the reach of children. Keep container tightly closed. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatibles.
--------------------	--

7.3. SPECIFIC END USE(S)

Not available.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. CONTROL PARAMETERS

Alcohols, C6-12, ethoxylated propoxylated (68937-66-6)	
ACGIH	Not applicable
OSHA	Not applicable
IDLH	Not applicable
NIOSH	Not applicable

Alcohols, C6-10, ethoxylated propoxylated (68987-81-5)	
ACGIH	Not applicable
OSHA	Not applicable
IDLH	Not applicable
NIOSH	Not applicable

Pentanedioic acid, 1,5-dimethyl ester (1119-40-0)	
ACGIH	Not applicable
OSHA	Not applicable
IDLH	Not applicable
NIOSH	Not applicable

Dimethyl succinate (106-65-0)	
ACGIH	Not applicable
OSHA	Not applicable
IDLH	Not applicable
NIOSH	Not applicable

2-Amino-2-methyl-1-propanol (124-68-5)	
ACGIH	Not applicable
OSHA	Not applicable
IDLH	Not applicable
NIOSH	Not applicable

1-Naphthalenecarboxaldehyde, 2-hydroxy-, [(2-hydroxy-1-naphthalenyl)methylene]hydrazone (2387-03-3)	
ACGIH	Not applicable
OSHA	Not applicable
IDLH	Not applicable
NIOSH	Not applicable

Fatty acids, C18-unsaturated, dimers, polymers with ethylenediamine and tall-oil fatty acids (68139-80-0)	
ACGIH	Not applicable
OSHA	Not applicable
IDLH	Not applicable
NIOSH	Not applicable

Propanol, 2-(methylamino)-2-methyl- (27646-80-6)	
ACGIH	Not applicable
OSHA	Not applicable
IDLH	Not applicable
NIOSH	Not applicable

8.2. EXPOSURE CONTROLS

Appropriate engineering controls	: Use ventilation adequate to keep exposures (airborne levels of dust, fume, vapor, etc.) below recommended exposure limits.
Hand protection	: Wear Nitrile or other chemically resistant protective gloves.
Eye protection	: Wear eye protection.
Skin and body protection	: Wear Tyvek disposable sleeves, jackets, and aprons that can be used to limit exposure or other suitable protective clothing.
Respiratory protection	: In case of insufficient ventilation, wear suitable respiratory equipment. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.
Environmental exposure controls	: Maintain levels below Community environmental protection thresholds.
Other information	: Do not eat, smoke or drink where material is handled, processed or stored. Wash hands carefully before eating or smoking. Handle according to established industrial hygiene and safety practices.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. INFORMATION ON BASIC PHYSICAL AND CHEMICAL PROPERTIES

Physical state	: Liquid
Appearance	: Oily
Colour	: Brown
Odour	: No data available
Odour threshold	: No data available
pH	: 8.5 - 10
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Flammability (solid, gas)	: Not flammable
Explosive limits	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Vapour pressure	: No data available
Relative density	: 1.075
Relative vapour density at 20 °C	: No data available
Solubility	: No data available
Partition coefficient: n-octanol/water	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available

9.2. OTHER INFORMATION

VOC content : 0 g/l

SECTION 10: STABILITY AND REACTIVITY
10.1. REACTIVITY

No dangerous reaction known under conditions of normal use.

10.2. CHEMICAL STABILITY

Stable under normal storage conditions.

10.3. POSSIBILITY OF HAZARDOUS REACTIONS

No dangerous reaction known under conditions of normal use.

10.4. CONDITIONS TO AVOID

Heat. Incompatible materials.

10.5. INCOMPATIBLE MATERIALS

Oxidizing materials, reducing agents.

10.6. HAZARDOUS DECOMPOSITION PRODUCTS

May include, and are not limited to: oxides of carbon.

SECTION 11: TOXICOLOGICAL INFORMATION
11.1. INFORMATION ON TOXICOLOGICAL EFFECTS

Acute toxicity : Not classified.

14A Redi-Bath	
LD50 oral rat	> 2000 mg/kg
LD50 dermal rabbit	> 2000 mg/kg
LC50 inhalation rat	> 20 mg/l/4h

Pentanedioic acid, 1,5-dimethyl ester (1119-40-0)	
LD50 oral rat	8191 mg/kg
LD50 dermal rabbit	> 2000 mg/kg
LC50 inhalation rat	> 5.6 mg/l/4h

Dimethyl succinate (106-65-0)	
LD50 oral rat	> 5 g/kg
LD50 dermal rabbit	> 5 g/kg

2-Amino-2-methyl-1-propanol (124-68-5)	
LD50 oral rat	2900 mg/kg
LD50 dermal rabbit	> 2000 mg/kg

Skin corrosion/irritation	: Causes skin irritation.
Serious eye damage/irritation	: Causes serious eye irritation.
Respiratory or skin sensitisation	: Based on available data, the classification criteria are not met.
Germ cell mutagenicity	: Based on available data, the classification criteria are not met.
Carcinogenicity	: Based on available data, the classification criteria are not met.
Reproductive toxicity	: Based on available data, the classification criteria are not met.
Specific target organ toxicity (single exposure)	: Based on available data, the classification criteria are not met.
Specific target organ toxicity (repeated exposure)	: Based on available data, the classification criteria are not met.
Aspiration hazard	: Based on available data, the classification criteria are not met.
Symptoms/injuries after inhalation	: May cause respiratory tract irritation.
Symptoms/injuries after skin contact	: Causes skin irritation. Symptoms may include redness, edema, drying, defatting and cracking of the skin.
Symptoms/injuries after eye contact	: Causes serious eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with marked redness and swelling of the conjunctiva.
Symptoms/injuries after ingestion	: May be harmful if swallowed. May cause stomach distress, nausea or vomiting.

SECTION 12: ECOLOGICAL INFORMATION

12.1. TOXICITY

Ecology - general : May cause long-term adverse effects in the aquatic environment.

12.2. PERSISTENCE AND DEGRADABILITY

14A Redi-Bath	
Persistence and degradability	Not established.

12.3. BIOACCUMULATIVE POTENTIAL

14A Redi-Bath	
Bioaccumulative potential	Not established.

12.4. MOBILITY IN SOIL

No additional information available

12.5. OTHER ADVERSE EFFECTS

Effect on the global warming : No known ecological damage caused by this product.

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. WASTE TREATMENT METHODS

Waste disposal recommendations : This material must be disposed of in accordance with all local, state, provincial, and federal regulations. The generation of waste should be avoided or minimized wherever possible.

SECTION 14: TRANSPORT INFORMATION

In accordance with DOT/TDG/IATA/IMDG

DOT (bulk)	: Not regulated
DOT (non-bulk)	: Not regulated
TDG	: Not regulated
IATA	: Not regulated
IMDG	: Not regulated

ADDITIONAL INFORMATION

Other information	: No supplementary information available.
Special transport precautions	: Do not handle until all safety precautions have been read and understood.

SECTION 15: REGULATORY INFORMATION


15.1. FEDERAL REGULATIONS

All components of this product are listed, or excluded from listing, on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory.

All components of this product are listed, or excluded from listing, on the Canadian DSL (Domestic Substances List) and NDSL (Non-Domestic Substances List) inventories, except for:

Propanol, 2-(methylamino)-2-methyl- (CAS No) 27646-80-6

NFPA health hazard	: 2
NFPA fire hazard	: 0
NFPA reactivity	: 0



15.2. US STATE REGULATIONS

14A Redi-Bath	
State or local regulations	This product contains chemicals known to the State of California to cause cancer, birth defects or other reproductive harm

SECTION 16: OTHER INFORMATION

Date of issue : 04/04/2016
Revision date : 07/12/2021
Other information : None.

Disclaimer: We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. It is the user's responsibility to satisfy oneself as to the suitability and completeness of this information for the user's own particular use.